


© COPYRIGHT 1976 BY AMP INCORPORATED, HARRISBURG, PA.  
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS  
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

UNPUBLISHED COPY NOT TO BE  
REPRODUCED NOR PUBLISHED  
WITHOUT WRITTEN PERMISSION  
OF AMP INCORPORATED.

|   |   | REVISIONS |     |                          |          |          |
|---|---|-----------|-----|--------------------------|----------|----------|
| P | F | ZONE      | LTR | DESCRIPTION              | DATE     | APPROVED |
| F | ✓ |           | F   | REVISED & REDRAWN DS     | 11-16-76 | WJH      |
|   |   |           | G   | REVISED PER OH14-0192-05 | 1-06     | PY       |



NOTE:  
1. THIS RECEPTACLE IS HERMETICALLY SEALED.  
2. SCREW THREAD MEASUREMENT IN ACCORDANCE WITH  
H2B HANDBOOK. (3 WIRE METHOD).  
USING WIRE .01804 DIA.- MEASUREMENT OVER  
WIRE SHALL BE .318 / .307.

|            |                                            |
|------------|--------------------------------------------|
| 5-861252-1 | AS SHOWN WITH TIN PLATED PIN & FLANGE      |
| 861252-1   | AS SHOWN WITH TIN-LEAD PLATED PIN & FLANGE |

|  |  |  |  |                                                |                        |
|--|--|--|--|------------------------------------------------|------------------------|
|  |  |  |  | PART NO                                        |                        |
|  |  |  |  | AMP INCORPORATED<br>Elizabethtown, Pa.         |                        |
|  |  |  |  | NAME<br>FLANGED RECEPTACLE<br>LGH - 1/2<br>WJH |                        |
|  |  |  |  | SIZE<br>C                                      | CODE IDENT NO<br>00779 |
|  |  |  |  | DRAWING NO<br>861252                           |                        |
|  |  |  |  | SHEET 1 OF 1                                   |                        |

|                     |  |            |  |
|---------------------|--|------------|--|
| CONTRACT NO         |  | DR         |  |
| DIGK STONE 11-16-76 |  | CHK        |  |
| APPD                |  | APPD       |  |
| DSGN APPD           |  | OTHER APPD |  |

|                                                      |  |
|------------------------------------------------------|--|
| UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. |  |
| TOLERANCES:                                          |  |
| .00 ± .01 .000 ± .005                                |  |
| ANGLES ±                                             |  |
| MATERIAL                                             |  |
| MOLDED GLASS EPOXY                                   |  |
| FINISH                                               |  |
| BLACK                                                |  |

|           |             |           |         |
|-----------|-------------|-----------|---------|
| NEXT ASSY | FINAL ASSY  | NEXT ASSY | USED ON |
| QTY REQD  | APPLICATION |           |         |