


REVISION J

DO NOT SCALE
FROM THIS PRINT

DIMENSIONS ARE IN INCHES		UNLESS OTHERWISE NOTED	TOLERANCES ARE:	TITLE:	DWG NO:
ONE PLACE DECIMALS $\pm .1$ [2.5mm]	THREE PLACE DECIMALS $\pm .005$ [.13mm]	ANGLES $\pm 2^\circ$		2mm TERMINAL STRIP ASSEMBLY (R/E)	TMM-1XX-XX-XX-X-RE-XX
TWO PLACE DECIMALS $\pm .010$ [.25mm]	FOUR PLACE DECIMALS $\pm .0020$ [.05mm]				SHEET 1 OF 1



NOTES:

- 1.) MAX. ALLOWABLE BOW: .005 IN/IN AFTER ASSEMBLY.
- 2.) MAX. PIN ROTATION IN BODY: 2°
- 3.) PUSHOUT FORCE SHALL BE 1 lb MIN.
- 4.) Δ REPRESENTS A CRITICAL DIMENSION FOR STATISTICAL PROCESS CONTROL USE.
- 5.) ALL DIMENSIONS IN BRACKETS [] TO BE MILLIMETERS.
- 6.) NO BANDOLIER MARKS ARE ALLOWED IN THE POST AREA.
- 7.) MAX CUT FLASH: .010[.25]

PROPRIETARY NOTE
 THIS DOCUMENT CONTAINS INFORMATION
 CONFIDENTIAL AND PROPRIETARY TO
 SAMTEC INC. AND SHALL NOT BE
 REPRODUCED OR TRANSFERRED TO
 OTHER DOCUMENTS OR DISCLOSED TO
 OTHERS OR USED FOR ANY PURPOSE
 OTHER THAN THAT FOR WHICH IT WAS
 OBTAINED WITHOUT THE EXPRESSED
 WRITTEN CONSENT OF SAMTEC INC.

samtec

EXISPROD\ASSEMBLY\2mm
TMM-RE

810 PROGRESS BLVD. NEW ALBANY, INDIANA 47150
 PHONE (812) 944-6733 P.O. BOX 1147
 CODE 55322

MADE BY: GARY PURVIS 3-10-93
 CHECKED BY:

ENG.
APPROVAL

TMM-1XX-XX-XX-X-RE-XX
 SHEET 1 OF 1

PLOT SCALE: 1=.