


**CMPZ4614
THRU
CMPZ4627**

**350mW LOW NOISE ZENER DIODE
5% TOLERANCE**



SOT-23 CASE

CentralTM
Semiconductor Corp.

DESCRIPTION:

The CENTRAL SEMIONDUCTOR CMPZ4614 Series Silicon Zener Diode is high quality voltage regulator designed for low leakage, low current and low noise applications.

ELECTRICAL CHARACTERISTICS

(T_A=25°C) V_F=1.0 MAX @ I_F=200mA FOR ALL TYPES.

TYPE NO.	ZENER VOLTAGE	TEST CURRENT	MAXIMUM ZENER IMPEDANCE	MAXIMUM REVERSE LEAKAGE CURRENT		MAXIMUM ZENER CURRENT	MAXIMUM NOISE DENSITY
	V _Z @ I _{ZT}	I _{ZT}	Z _{ZT} @ I _{ZT}	I _R @ V _R		I _{ZM}	N _D @ I _{ZT} =250μA
	VOLTS	μA	Ω	μA	VOLTS	mA	μV/√Hz
CMPZ4614*	1.8	250	1200	7.5	1.0	120	1.0
CMPZ4615*	2.0	250	1250	5.0	1.0	110	1.0
CMPZ4616*	2.2	250	1300	4.0	1.0	100	1.0
CMPZ4617*	2.4	250	1400	2.0	1.0	95	1.0
CMPZ4618*	2.7	250	1500	1.0	1.0	90	1.0
CMPZ4619*	3.0	250	1600	0.8	1.0	85	1.0
CMPZ4620*	3.3	250	1650	7.5	1.5	80	1.0
CMPZ4621*	3.6	250	1700	7.5	2.0	75	1.0
CMPZ4622*	3.9	250	1650	5.0	2.0	70	1.0
CMPZ4623*	4.3	250	1600	4.0	2.0	65	1.0
CMPZ4624*	4.7	250	1550	10	3.0	60	1.0
CMPZ4625*	5.1	250	1500	10	3.0	55	2.0
CMPZ4626*	5.6	250	1400	10	4.0	50	4.0
CMPZ4627*	6.2	250	1200	10	5.0	45	5.0

* Available on special order only, please consult factory.

All dimensions in inches (mm).

