




DRAWING MADE IN THIRD ANGLE PROJECTION

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 19
 © COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE
				RELEASE DRAWING PER T.T.I. 82-82	7-16-82
				REVISED M-7087	9-8-82
				REVISED NAME, M-7223	1/3/83
				RESTORATION	8-3-85
				REVISE PER CM-1282	10-20-87
				REVISE PER CM-1458	1-20-88
				REVISED PER CM 2704	1-30-90
				REV PER EC 0730-0054-95	3-30-95



- ASSEMBLY INSTRUCTION:
 SNAP MODULE ONTO HOUSING,
 FULLY INSERT CONTACTS THRU MODULE AND INTO HOUSING; (NOTE: SEVERAL CLICKS CAN
 BE HEARD AS THE CONTACT IS PUSHED IN PLACE),
 DISENGAGE LATCHES ON MODULE AND SLIDE BACK FROM END OF HOUSING,
 CHECK FOR ANY CONTACTS NOT FULLY INSERTED INTO HOUSING; INSERT ANY CONTACTS NOT
 LOCKED IN HOUSING,
 PUSH MODULE BACK AGAINST HOUSING UNTIL LATCHES ARE ENGAGED.
- MODULE WILL ACCEPT MAXIMUM WIRE OUTSIDE DIA. OF .160.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS .015 ANGLES 1°		CONTRACT NO.		643254-1	
MATERIAL NYLON 94V-0		DR m. Felen 7-16-82		PART NO	
FINISH		CHK P. High 1-2-1-		NAME ASSEMBLY MODULE, UNIVERSAL MATE-N-LOK™, 9 CIRCUIT	
OTHER APPD		APPD		SIZE C	
DSGN APPD		APPD		FSCM NO 00779	
SCALE 4-1		DRAWING NO 643254		SHEET	