



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETERIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
UINK2F**	.71 LB/10 PCS (324.0 g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PART INCLUDES:
 - 1- FACEPLATE
 - 1- CLEAR SCREW COVER
 - 1- COLOR COORDINATED SCREW COVER
 - 1- CLEAR LABEL COVER
 - 2- MOUNTING SCREW
5. LABELS SOLD SEPERATELY.



MODEL FILENAME	MO1703BB_UINK2F_00.PRT	SIZE
DRAWING FILENAME	MO1703BB_DC_00A.PRT	A

NETKEY™ ULTIMATE ID™ 2 POSITION
VERTICAL CLASSIC SERIES
FACEPLATE CUSTOMER DRAWING



PANDUIT TM
TINLEY PARK, ILL 60477

TM

I.I. NUMBER
N/A
PRODUCT SPEC
N/A
WORK INSTRUCTION
N/A
SCALE
NONE

ALL DIMENSIONS ARE GIVEN IN INCHES,
UNLESS OTHERWISE SPECIFIED.

DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ± .010 (.3)
(.XX) ± .031 (.8) ANGLES ±

DRAWN BY

JsP

REVIEW DRAWING NUMBERS

PART NO.

UINK2F**

DRAWING NO.

01703-03

DATE

5-12-03

CHK'D

MATERIAL: ABS

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	5-12-03	JsP		RELEASED TO PRODUCTION	01703-03				