



6RCC



Part No	Inductance (μ H)	f _L (MHz)	Tol $\pm$ (%)	DCI (A)	Temp. rise Δ ($^{\circ}$ C)	ISAT (A)	DCR (Ω)	Dimensions					
								$\varnothing d$	$\varnothing D1$	(A)	$\varnothing D$	F	F1
6RCC-4R0M-00	4.0	1	20	10	<15	22.0	0.005	1.32	6.0	25	8.9	18.7	7.4
6RCC-6R0M-00	6.0	1	20	7	<15	17.0	0.008	1.06	6.0	25	8.4	18.4	7.1
6RCC-100M-00	10.0	0.1	20	5	<15	14.0	0.013	0.95	6.0	25	8.2	22.4	7.0
6RCC-150M-00	15.0	0.1	20	2	<15	10.0	0.030	0.63	6.0	25	7.5	16.2	6.7
6RCC-220M-00	22.0	0.1	20	2	<15	7.8	0.034	0.63	6.0	30	7.5	18.2	6.7
6RCC-300M-00	30.0	0.1	20	2	<15	7.0	0.046	0.63	6.0	30	7.5	24.8	6.7

Material : Ferrite

SPQ : Loose / Box 500 [-00]

All dimensions in mm

Ring Core Chokes