



# NC6MP-BAG




Smallest available traditional style metal panel mount connector with large solder cups for ease hard wiring.

6 pole male receptacle, solder contacts, black metal housing, silver contacts

## Features & Benefits

- Smallest available hard wiring receptacles with large solder cups
- Compatible with switchcraft D\*M, D\*F; Cannon XLB2\*31, XLB2\*32
- 6 pole version available with Switchcraft contact arrangement (NC6FSP-1, NC6MSP)

*Panel cut out (rear side)*



					Werkstoff:	Massstab:		Datum	Name
					*Lieferant darf ohne Ruecksprache nicht geaendert werden	3:1	Gezeichnet	03.04.98	Alinjak
					Zeichnung urheberrechtlich geschuetzt (DIN 34) (C)		Geprueft		
					Benennung:		Gesehen		
					NC6MP-B		Ersetzt durch:		Blatt
							Ersatz fuer:		von Blatt
					<b>NEUTRIK AG</b> FL-9494 SCHAAN		Zeichn. Nr.		
Ind.	Aenderung	Datum	Name				3102 St 11 31		



# NEUTRI



## P Series

Audio

### NC6MP-BAG

There are no technical infos for this product.

Product	
Connector Type	XLR
Gender	male
Electrical	
Capacitance between contacts	$\leq 7 \text{ pF}$
Contact resistance	$\leq 5 \text{ m}\Omega$
Dielectric strength	1,5 kVdc
Insulation resistance	$> 2 \text{ G}\Omega$ (initial)
Insulation resistance	$> 1 \text{ G}\Omega$ (after damp heat test)
Rated current per contact	7,5 A
Rated voltage	50 V
Mechanical	
Insertion force	$\leq 20 \text{ N}$
Withdrawal force	$\leq 20 \text{ N}$
Lifetime	$> 1000$ mating cycles
Wire size	max. $1.0 \text{ mm}^2$
Wire size	max. 18 AWG
Wiring	Solder contacts
Locking device	latch lock
Mounting direction	front
Chassis shape	P
Material	
Contact plating	2 $\mu\text{m}$ Ag over 2 $\mu\text{m}$ Ni
Contacts	Brass (CuZn39Pb3)
Insert	Polyamide (PA 6.6 30 % GR)
Locking element	Steel Ck67
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Black chromium
Environmental	
Flammability	UL 94 HB
Standard compliance	IEC 61076-2-103
Solderability	Complies with IEC 68-2-20

Temperature range -30 °C to +80 °C

Optical
Mobile Cables