

HID & SYSTEM MANAGEMENT PRODUCTS, SYSTEM MANAGEMENT FAMILY

DESCRIPTION

The SH3301 USBAdapt™ is a single IC that converts PS/2 keyboard and mouse data to USB 1.1.

The SH3301 is ideal for system legacy support, enabling seamless connection of standard PS/2 devices (mice or keyboards) to USB.

The SH3301 offers two hot-pluggable and hot-swappable PS/2 ports; either port can accept a mouse or a keyboard. In addition, the SH3301 auto-detects and transparently supports the wheel function of wheel mice.


FEATURES

- Interfaces PS/2 devices to USB
- Complies with USB 1.1 specification
- Provides two PS/2 ports
- PS/2 ports support mouse wheel functionality
- Works with standard Windows keyboard and mouse drivers
- Devices are hot-pluggable
- PS/2 ports are auto-selectable and hot-swappable – a mouse or keyboard can be used in either port
- Easy to implement
- Few external components required

APPLICATIONS

- System legacy support

PIN ASSIGNMENTS






ORDERING CODE

Package options	Pitch	TA = -40°C to +85°C
44-pin QFP	0.8 mm	SH3301-FB
Other Materials	Type	Order number
USB-Adapt™ eval. kit	Evaluation kit	EVK-SH3301

BLOCK DIAGRAM





USB FUNCTIONALITY

The SH3301 is a low-speed composite USB 1.1 device that interfaces PS/2. It supports the USB Human Interface Devices (HID) class specification. It uses two interrupt endpoints for the PS/2 devices.


The SH3301 handles the merging of all this data, and sends the data to the host system.

PS/2 PORTS


The two PS/2 ports allow the user to connect legacy PS/2 devices to the USB host system. Standard 104-key keyboards and PS/2 mice, with support for wheel mouse functionality, can be hot-plugged at either of the PS/2 ports and immediately begin communicating with the host.

PIN DEFINITIONS

Mnemonic	QFP	Type	Name and Function
Power Supply			
VDD	5	PWR	Positive supply voltage
VSS	9	PWR	Ground: negative supply voltage
VSS1	6	PWR	Ground: negative supply voltage
Reset			
_RESET	12	I	Controller hardware reset pin: Active-low reset line
Oscillator pins			
XIN	8	I	Oscillator input: input signal from oscillator
XOUT	7	O	Oscillator output: output signal to oscillator
USB			
3.3V	34	O	USB reference voltage
D+	36	I/O	USB D+ line
D-	35	I/O	USB D- line
PS/2			
EPS2CLK0	10	I/O	Clock line for external PS/2 port 0
EPS2DAT0	11	I/O	Data line for external PS/2 port 0
EPS2CLK1	14	I/O	Clock line for external PS/2 port 1
EPS2DAT1	37	I/O	Data line for external PS/2 port 1
EPS2EN	13	O	Enable external PS/2 ports
Not connected			
	1-4, 15-33, 38-44		Not used



MECHANICAL INFORMATION FOR THE SH3301-FB PACKAGE



ELECTRICAL SPECIFICATIONS

Absolute Maximum Ratings

Ratings	Symbol	Value	Unit
Supply voltage	V _{DD}	-0.3 to 6.5	V
Input and output voltage	V _{IN} , V _{OUT}	-0.3 to V _{DD} +0.3	V
Current Drain per Pin (not including V _{SS} or V _{DD})	I	20	mA
Operating Temperature SH3301	T _A	T low to T high -40 to +85	°C
Storage Temperature Range	T _{STG}	-65 to +150	°C
ESD rating (human body model)	V _{ESD}	2.0	KV

DC Electrical Characteristics (T_A = -40°C to +85°C, V_{DD} = 4.0 V to 5.25V)

Characteristic	Symbol	Min	Typ	Max	Unit
Supply voltage	V _{DD}	4.0	5.0	5.25	V
Input high voltage					
■ high	V _{IH}	0.8 x V _{DD}		V _{DD}	V
■ low	V _{IL}	V _{SS}		0.2 x V _{DD}	V
Output voltage (except D-, D+)					
■ high (I _{OH} =-200μA)	V _{OH}	V _{DD} -1.0			V
■ low (I _{OL} =1mA)	V _{OL}			0.4	
Output low current (V _{OL} =3V, only pins38, 39, 67)	I _{OL}	8	15	23	mA
Input leakage current					
■ high (all inputs except XIN, XOUT, RESET, D+, D-)	I _{LIH1}			3	μA
■ high (XIN, XOUT, RESET)	I _{LIH2}			20	μA
■ low (all inputs except XIN, XOUT, RESET, D+, D-)	I _{LIL1}			-3	μA
■ low (XIN, XOUT, RESET)	I _{LIL2}			-20	μA
Output leakage current (all I/O pins and output pins except D+, D-)					
■ high	I _{LOH1}			3	μA
■ low	I _{LOL}			-3	μA
Supply current					
■ Normal operation mode	I _{DD1}		5.5	12	mA
■ Idle mode	I _{DD2}		2.2	5	mA
■ Stop mode	I _{DD3}		180	300	μA

Control Timing (T_A = -40°C to +85°C, V_{DD} = 4.0 V to 5.25V)

Characteristic	Symbol	Min	Typ	Max	Unit
Frequency of Operation					
■ Crystal Option	f _{osc}		6.0		MHz
■ External Clock Option	f _{osc}		6.0		MHz

This Page Left Intentionally Blank



**For sales information
and product literature,
contact:**

Semtech Corporation
Human Interface Device (HID)
and System Management Division
200 Flynn Road
Camarillo, CA 93012-8790
sales@semtech.com
<http://www.semtech.com/>
(805)498-2111 Telephone
(805)498-3804 Fax

Copyright ©1999-2004 Semtech Corporation. All rights reserved.
Semtech, the Semtech logo, and USBAdapt are marks of Semtech
Corporation. All other trademarks belong to their respective
owners.

LIMITED LICENSE GRANTED: NO WARRANTIES MADE
This specification is provided "as is" with no warranties whatsoever
including any warranty of merchantability, fitness for any particular
purpose, or any warranty otherwise arising out of any proposal,
specification or sample. Any suggestions or comments by Semtech
concerning use of this product are opinion only, and Semtech
makes no warranty as to results to be obtained in any specific
application. A license is hereby granted to reproduce and distribute
this specification for internal use only. No other license, expressed
or implied to any other intellectual property rights is granted or
intended hereby. Authors of this specification disclaim any liability,
including liability for infringement of proprietary rights, relating to
the implementation of information in this specification. Authors of
this specification also do not warrant or represent that such
implementation(s) will not infringe such rights.