

DE5SC6M

60V 5A


FEATURES

- SMT
- Tj150°C
- PRRSM avalanche guaranteed
- High current capacity with Small Package

APPLICATION

- Switching power supply
- DC/DC converter
- Home Appliances, Office Equipment
- Telecommunication

OUTLINE DIMENSIONS



RATINGS

● Absolute Maximum Ratings (If not specified Tc=25°C)


Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	Tstg		-40~150	°C
Operating Junction Temperature	Tj		150	°C
Maximum Reverse Voltage	VRM		60	V
Repetitive Peak Surge Reverse Voltage	VRSM	Pulse width 0.5ms, duty 1/40	65	V
Average Rectified Forward Current	Io	50Hz sine wave, R-load, Rating for each diode Io/2, Ta=42°C, On alumina substrate	2.5	A
		50Hz sine wave, R-load, Rating for each diode Io/2, Tc=92°C	5	
Peak Surge Forward Current	IFSM	50Hz sine wave, Non-repetitive 1 cycle peak value, Tj=125°C	80	A
Repetitive Peak Surge Reverse Power	PRSM	Pulse width 10 μ s, Rating of per diode, Tj=25°C	330	W

● Electrical Characteristics (If not specified Tc=25°C)


Item	Symbol	Conditions	Ratings	Unit
Forward Voltage	VF	IF=2.5A, Pulse measurement, Rating of per diode	Max.0.58	V
Reverse Current	IR	VR=VRM, Pulse measurement, Rating of per diode	Max.2.5	mA
Junction Capacitance	Cj	f=1MHz, VR=10V, Rating of per diode	Typ.130	pF
Thermal Resistance	θjc	junction to case	Max.12	°C/W
	θja	junction to ambient	Max.55	

DE5SC6M

Forward Voltage




DE5SC6M Junction Capacitance




DE5SC6M


Reverse Current




DE5SC6M Reverse Power Dissipation




$T_j = 150^\circ\text{C}$



DE5SC6M Forward Power Dissipation




$T_J = 150^\circ\text{C}$




DE5SC6M

Derating Curve




$V_R = 30V$




DE5SC6M


Derating Curve



$V_R = 30V$



DE5SC6M Peak Surge Forward Capability



SBD Repetitive Surge Reverse Power Derating Curve

