


[PRODUCTS](#)
[COMPANY](#)
[CONTACT US](#)
[SUPPORT](#)
[SITE MAP](#)
PRODUCT SEARCH

TYPE NUMBER e.g.120-A-111

ARTICLE NUMBER e.g.20.874.002

PRODUCTS

CROSS-REFERENCE
Eurostyle Screw Terminal Strips for Panel / Chassis Mounting
TYPE 326 (-HDS)

14.5 mm spacing - 1 to 12 poles


[Distributor Stock Check](#)


Series	Download PDF	3D Model	Can plug with	How to order	Color specifications	Print
--------	--------------	----------	---------------	--------------	----------------------	-------



RoHS WEEE Pb free surface compliant

Description

- Standard version
- Recommended mounting hardware: M4 pan head screw (#8-32 pan head screw) or similar sized sheet metal screw, self-tapping screw or rivet.


Technical Data
Center to Center Spacing: 14.5 mm (0.571 in.)

Nominal Cross Section: 10 mm² (15497 mils²)

Wire Stripping Length: 9 mm (0.35 in.)

Application

The panel and chassis mounted series are ideal for connecting electrical control panels to external power sources, signal sources, other electrical panels and electrical loads of many types and sizes. The electrical panel's or electrical enclosure's internal components and circuitry are connected to their appropriate external electrical circuitry through these terminal blocks. The screw tightened connections result in high contact forces thus promoting safe wire secureness and retention, low electrical resistance and safe reusable connections. All wire retention screws are captive in their towers and they cannot fall out during transportation, installation and use. Wire protectors are available to protect small gauge stranded wires from screw damage. These terminal strips can be completely enclosed within the enclosures or be placed at an enclosure opening with one side accessible for external cabling and the other for internal wiring. They can be specially marked to your specifications.


Dimensions: mm (in.)

Length of Connector (L)

L = No. of Poles x Center to Center Spacing - 3 mm

When locating connector, allow 0.5 mm clearance around it for process-induced variations.
Approval Information

UL File No.E69841



CSA File No.LR24322



Rating	Current(A)	Voltage(V)	Application group	AWG
UL	50	300	B,D	14-8
CSA	55	300	B	14-8
CSA	10	300	D,E	14-8

* UL 300V / C and 600 V / B,C,D: if mounted on a suitable insulated surface, on standoffs, or equivalent means to maintain spacing from live parts to the mounting surface.

Screw Tightening Torque:

UL: 10.0 lbf·in

CSA: 1.2 Nm

International Approvals:

Material
Molding: Polyamide, self extinguishing to UL 94, V-0, color off-white

Temperature limits:
Short Time: 140°C (284°F)

Continuous: RTI 105°C (221°F)

Low Limit: -40°C (-40°F)

Comparative Tracking Index: CTI≥600V

Oxygen Index Rating: 33%

Terminal Body: Nickel plated copper alloy

Wire Protector: Stainless steel strip

Screw: M4, Slotted head, zinc plated blue passivated, steel substrate

[Top of page](#)

How to order

Item — **326 (-HDS)**

Options

- ☐ CN: Consecutive Numbering (hot stamped numbers)
- ☐ SM: Special Marking (please provide sketch)
- ☐ G05: Gold Plating (5 micro inches)
- ☐ G30: Gold Plating (30 micro inches)
- ☐ S30: Silver Plating (30 micro inches)
- ☐ WS: Wire Stop (to control the wire insertion depth)

Note: Plated component for non HDS versions only: terminal body WS is for HDS versions only

Ordering Note: Series 300 Terminal Strips can be supplied in other colors. Please consult factory.



Request sample



Request quote

Quantity

1

Accessories

[BST Marking Strips for terminal strips.](#)

[Jumper Combs, Series 300-J.](#)

326

WIRE PROTECTOR:
with: - HDS

POLES:
01 to 12

/

Add to shopping cart

2008, WECO Electrical Connectors Inc.

ISO 9001 registered quality management system