





- 1 LOW-INSERTION FASTON TERMINALS, BASE P/N 63306, ARE USED IN THIS PRODUCT.
- 2 TIN PLATE PER .002032 [.000080] MIN
- 3 PRELIMINARY-NOT FOR PRODUCTION

STANDARD	2 TIN OVER NICKEL	2.79-4.32 [.110-.170] DIA	0.8-2.0 mm ² [18-14]	0.813 [.032]	3 521367-3			
STANDARD	2 TIN PLATE				521367-2			
STANDARD	PLAIN				521367-1			
PACKAGING	TERMINAL FINISH	INSULATION RANGE	WIRE SIZE	MATING TAB THK±0.025 [±.001]	PART NO			
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: mm [INCHES]  MATERIAL HOUSING - 6/6 V0 NYLON TERMINAL - BRASS		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.25 [.010] 4 PLC ± - ANGLES ± - FINISH HOUSING - NATURAL TERMINAL - SEE TABLE	DWN JR RUTH 15JAN01	TE Connectivity				
			CHK MS FEHER 15JAN01					
			APVD J HUMMEL 15JAN01	NAME ASSEMBLY, ULTRA-POD, RECEPTACLE, 6.35 [.250] SERIES				
			PRODUCT SPEC 108-1285					
			APPLICATION SPEC 114-2124					
			WEIGHT -					
			CUSTOMER DRAWING		SIZE A2	CAGE CODE 00779	DRAWING NO C-521367	RESTRICTED TO -
					SCALE 5:1	SHEET 1 of 1	REV A3	