

Nickel Thin Film Temperature Sensor

Nickel thin film elements are characterized by a relatively high temperature coefficient. Typical applications include bearing temperature monitoring, HVAC temperature monitoring, and stator winding temperature monitoring

Nominal Resistance R_0	Accuracy	Part Number
120 ohms at 0 °C	2 X DIN 43760	100 485-4

Specification	ANSI
Temperature Range	-60 °C to +250 °C
Temperature Coefficient	6720ppm/K
Lead wire material	Nickel
Protective coating	high-temperature epoxy
Self-heating	0,3K/mW in air
Response time	Water ($v = 0,2\text{m/sec.}$) $t_{0,9} = 0,3 \text{ sec.}$ Air ($v = 1\text{m/sec.}$) $t_{0,9} = 9 \text{ sec.}$
Operating Current, Maximum	5 mA


Polynomial of the resistive characteristic:

$$R(\vartheta) = R_0 \times (1 + 5,88 \times 10^{-3} \times \vartheta + 7,872 \times 10^{-6} \times \vartheta^2 + 4,71 \times 10^{-9} \times \vartheta^3)$$

Maximum permissible tolerance as a function of temperature (accuracy defined as 2 x DIN 43760):

$$\vartheta < 0^\circ\text{C}: F = \pm(0,8 + 0,056 \times \vartheta) \text{ } ^\circ\text{C}$$

$$\vartheta > 0^\circ\text{C}: F = \pm(0,8 + 0,014 \times \vartheta) \text{ } ^\circ\text{C}$$



All technical data serves as a guideline and does not guarantee any particular properties to the product.

Heraeus Sensor Technology USA

1901 Route 130
North Brunswick, NJ 08902
Phone 732-940-4400 Fax 732-940-4445
Email info.hst-us@heraeus.com
www.hst-us.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heraeus:](#)

[100485-4](#)