



### MATERIALS:

Body: Brass, White Bronze Plating  
 Center Contact: Gold Plated Beryllium copper  
 Dielectric : PTFE  
 Finish: Body – Tarnish resistant  
 Center Contact – Gold Plated  
 Marking: “POMONA 4956” located approximately as shown.

### RATINGS:

Operating Voltage: 1000 VRMS

Impedance: 50 Ohms

### ORDERING INFORMATION: Model 4956

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[4956](#)