


HARDWARE


QUICK ASSEMBLY BUMPER FOOT KIT

- **FASTER**
- **MORE ECONOMICAL TO ASSEMBLE THAN USING SCREW WITH NUTS**
- **NO TOOLS REQUIRED FOR ASSEMBLY**
- **ALLOWS ASSEMBLY "FROM OUTSIDE"**



KIT#	SNAP RIVET#	BUMPER#	HEIGHT	MOUNTING HOLE (±.002)	PCB THICKNESS
760-3511	770-6581-10	760-3502	.300	.125	.032
760-3512	770-6574-10	760-3502	.300	.125	.062
760-3513	770-6582-10	760-3502	.300	.125	.094
760-3514	770-6599-10	760-3543	.562	.163	.032
760-3515	770-6590-10	760-3543	.562	.163	.062
760-3516	770-6589-10	760-3509	.375	.163	.032/.062
760-3517	770-6599-10	760-3509	.375	.163	.094
760-3519	770-6590-10	760-3509	.375	.163	.125


NEW BUMPER KIT



PART NUMBER	CHASSIS MTG. HOLE "E"	PANEL THK. "H"	BUMPER HEIGHT "C"	MAJOR OUTSIDE DIAMETER "A"	MINOR OUTSIDE DIAMETER "D"
770-6600	.122-.126	.031-.071	.22	.056	.053
770-6603		.031-.071			
770-6604		.071-.111	.17	.83	.79
770-6605		.114-.146			
770-6606	.161-.165	.150-.189			
770-6613		.024-.039			
770-6614		.039-.079		.59	.55
770-6615		.079-.118			
770-6618	.200-.205	.031-.047	.24		
770-6607		.031-.071			
770-6608		.075-.110		.83	.79
770-6609		.114-.157			
770-6610	.161-.165	0-.031	.31		
770-6611		.031-.079			
770-6612		.083-.118			
770-7430	.161-.165	.024-.039			
770-7431		.039-.079			
770-7432		.079-.118	.35	.59	.55
770-7433	.200-.205	.032-.047			
770-7434		.047-.087			

SNAP RIVETS

MATERIAL: NYLON 6 , COLOR: BLACK



PART NO.	FIG. NO.	G HOLD DIA.	EXTRACT. FORCE LB.	F THICK.	A	B	C	D	E
770-6575-10				.039-.079			.13		
770-6576-10	1	.102-.106	11.0 MIN.	.079-.118	.197	.055	.17	.102	.18
770-6577-10				.134-.169			.22		.24
770-6578-10				.039-.079			.14		.20
770-6579-10	1	.122-.126	17.6 MIN.	.079-.118	.252	.063	.18	.118	.24
770-6580-10				.118-.157			.22		.28
770-6581-10				.157-.197			.26		.35
770-6574-10				.197-.236			.30		.35
770-6582-10				.217-.256			.31		.35
770-6583-10				.083-.118			.18		.24
770-6584-10	2	.142-.146	26.4 MIN.	.118-.157	.252	.063	.22	.138	.28
770-6585-10				.177-.217			.28		.35
770-6586-10				.098-.138			.20		.28
770-6587-10	2	.161-.165	44.0 MIN.	.138-.177	.315	.071	.24	.157	.28
770-6588-10				.177-.217			.28		.35
770-6589-10				.217-.256			.31		.43
770-6590-10				.295-.335			.39		
770-6591-10				.059-.098			.18		.26
770-6592-10				.098-.138			.22		
770-6593-10				.138-.177			.26		
770-6594-10	3	.201-.205	55.0 MIN.	.177-.217	.354	.087	.30	.197	.33
770-6595-10				.217-.256			.33		.41
770-6596-10				.256-.295			.37		.47
770-6597-10				.295-.335			.41		.35
770-6598-10	2	.240-.244	66.0 MIN.	.098-.157	.472	.098	.24	.236	

CONCORD

FOR ADDITIONAL SIZES AND MATERIAL, CONTACT FACTORY