



## Surround Audio Processor for Mobile Applications

### ■ GENERAL DESCRIPTION

The **NJM2705** is the surround audio processor for mobile applications.

It regenerates the 3D surround sound with extremely narrow space two speakers (2SP mode), headphone surround with normal headphone (HP mode) and reverberation sound with only one speaker (1SP mode).

It includes mode control switches for surround function and standby function and realizes low consumption power design by standby function.

In addition to SSOP16, ultra small and thin packages FFP16 (Flip-Chip Fine Package) and PCSP16 (Plastic Chip Size Package) is applied.

It is suitable for cellular phone, PDA and portable game.


### ■ PACKAGE OUTLINE



**NJM2705PB1**



**NJM2705SD3**




**NJM2705V**

### ■ FEATURES

- Operating Voltage 1.8 to 6V
- Operating Current 0.7mA typ. at Active mode  
1μA max. at Standby mode
- Low Output Noise 10μVrms typ  
(2SP/HP/1SP mode, VR : max.)
- Variable Surround Effect by external resistor  
(Adjustable for speaker and headphone independently.)
- Standby Function
- Internal Mode Control Switch
- Bipolar Technology
- Package Outline FFP16, PCSP16, SSOP16


### ■ BLOCK DIAGRAM



# NJM2705


## ■ PIN CONFIGURATION

FFP16 (Top View)




- |          |          |
|----------|----------|
| 1. LIN   | 9. LMON  |
| 2. RIN   | 10. PS   |
| 3. LOUT  | 11. SW2  |
| 4. ROUT  | 12. SW1  |
| 5. NFSPR | 13. STBY |
| 6. NFHPR | 14. V+   |
| 7. NFSPL | 15. GND  |
| 8. NFHPL | 16. VREF |

PCSP16 (Top View)



- |         |           |
|---------|-----------|
| 1. ROUT | 9. SW1    |
| 2. LOUT | 10. SW2   |
| 3. RIN  | 11. PS    |
| 4. LIN  | 12. LMON  |
| 5. VREF | 13. NFHPL |
| 6. GND  | 14. NFSPL |
| 7. V+   | 15. NFHPR |
| 8. STBY | 16. NFSPR |

SSOP16 (Top View)



- |          |           |
|----------|-----------|
| 1. NFHPR | 9. V+     |
| 2. NFSPR | 10. STBY  |
| 3. ROUT  | 11. SW1   |
| 4. LOUT  | 12. SW2   |
| 5. RIN   | 13. PS    |
| 6. LIN   | 14. LMON  |
| 7. VREF  | 15. NFHPL |
| 8. GND   | 16. NFSPL |

## ■ABSOLUTE MAXIMUM RATING (Ta=25°C)

| PARAMETER                   | SYMBOL           | RATINGS                                     | UNIT |
|-----------------------------|------------------|---------------------------------------------|------|
| Supply Voltage              | V <sup>+</sup>   | 7                                           | V    |
| Power Dissipation           | P <sub>D</sub>   | (FFP16) 400<br>(PCSP16) TBD<br>(SSOP16) 300 | mW   |
| Operating Temperature Range | T <sub>opr</sub> | -20 to +75                                  | °C   |
| Storage Temperature Range   | T <sub>stg</sub> | -40 to +125                                 | °C   |

## ■OPERATING VOLTAGE

| PARAMETER         | SYMBOL         | TEST CONDITION | MIN | TYP | MAX | UNIT |
|-------------------|----------------|----------------|-----|-----|-----|------|
| Operating Voltage | V <sup>+</sup> | -              | 1.8 | 3.0 | 6.0 | V    |

## ■ELECTRICAL CHARACTERISTICS (V<sup>+</sup>=3V, Ta=25°C unless otherwise specified)

| ELECTRICAL CHARACTERISTICS (V <sub>CC</sub> = 5V, I <sub>A</sub> = 20 mA unless otherwise specified) |                  |           |                |   |            |         |          |          |     |      |     |      |
|------------------------------------------------------------------------------------------------------|------------------|-----------|----------------|---|------------|---------|----------|----------|-----|------|-----|------|
| PARAMETER                                                                                            | SYMBOL           |           | TEST CONDITION |   |            |         |          |          | MIN | TYP  | MAX | UNIT |
|                                                                                                      |                  |           | INPUT          |   | OUT<br>PUT | MODE    | SP<br>VR | HP<br>VR |     |      |     |      |
|                                                                                                      |                  |           | L              | R |            |         |          |          |     |      |     |      |
| Operating<br>Current                                                                                 | I <sub>CC</sub>  | No Signal | 0              | 0 | -          | Active  |          |          | -   | 450  | 700 | μA   |
|                                                                                                      |                  |           | 0              | 0 | -          | Standby |          |          | -   | 0.1  | 1.0 |      |
| Reference<br>Voltage                                                                                 | V <sub>ref</sub> | No Signal | 0              | 0 | -          | -       |          |          | 1.0 | 1.15 | 1.3 | V    |

## ●AC CHARACTERISTICS

(V<sup>+</sup>=3V, Ta=25°C, V<sub>IN</sub>=-20dBV(100mVrms), f=1kHz, R<sub>L</sub>=10kΩ, unless otherwise specified)

| PARAMETER                | SYMBOL            |                                        | TEST CONDITION       |                      |            |        |          |          | MIN            | TYP            | MAX           | UNIT           |
|--------------------------|-------------------|----------------------------------------|----------------------|----------------------|------------|--------|----------|----------|----------------|----------------|---------------|----------------|
|                          |                   |                                        | INPUT                |                      | OUT<br>PUT | MODE   | SP<br>VR | HP<br>VR |                |                |               |                |
|                          |                   |                                        | L                    | R                    |            |        |          |          |                |                |               |                |
| Maximum<br>Input Voltage | V <sub>IM1</sub>  | f=1kHz<br>THD=1%                       | V <sub>IN</sub><br>0 | 0<br>V <sub>IN</sub> | L<br>R     | Bypass | -        | -        | -              | -2.0<br>(790)  | -             | dBV<br>(mVrms) |
|                          | V <sub>IM2</sub>  | f=100Hz<br>THD=1%                      | V <sub>IN</sub><br>0 | 0<br>V <sub>IN</sub> | L<br>R     | 2SP    | MAX      | -        | -              | -16.0<br>(160) | -             |                |
|                          | V <sub>IM3</sub>  | f=100Hz<br>THD=1%                      | V <sub>IN</sub><br>0 | 0<br>V <sub>IN</sub> | L<br>R     | HP     | -        | MAX      | -              | -16.0<br>(160) | -             |                |
|                          | V <sub>IM4</sub>  | f=100Hz<br>THD=1%                      | V <sub>IN</sub>      | 0                    | L          | 1SP    | MAX      | -        | -              | -16.0<br>(160) | -             |                |
|                          | V <sub>IM5</sub>  | f=100Hz<br>THD=1%                      | 0                    | V <sub>IN</sub>      | L          | 1SP    | MAX      | -        | -              | -14.5<br>(190) | -             |                |
|                          | V <sub>IM6</sub>  | V <sup>+</sup> =1.8V,f=1kHz<br>THD=1%  | V <sub>IN</sub><br>0 | 0<br>V <sub>IN</sub> | L<br>R     | Bypass | -        | -        | -10.5<br>(300) | -8.5<br>(380)  | -             |                |
|                          | V <sub>IM7</sub>  | V <sup>+</sup> =1.8V,f=100Hz<br>THD=1% | V <sub>IN</sub><br>0 | 0<br>V <sub>IN</sub> | L<br>R     | 2SP    | MAX      | -        | -24.5<br>(60)  | -22.5<br>(75)  | -             |                |
|                          | V <sub>IM8</sub>  | V <sup>+</sup> =1.8V,f=100Hz<br>THD=1% | V <sub>IN</sub><br>0 | 0<br>V <sub>IN</sub> | L<br>R     | HP     | -        | MAX      | -24.5<br>(60)  | -22.5<br>(75)  | -             |                |
|                          | V <sub>IM9</sub>  | V <sup>+</sup> =1.8V,f=100Hz<br>THD=1% | V <sub>IN</sub>      | 0                    | L          | 1SP    | MAX      | -        | -24.5<br>(60)  | -22.5<br>(75)  | -             |                |
|                          | V <sub>IM10</sub> | V <sup>+</sup> =1.8V,f=100Hz<br>THD=1% | 0                    | V <sub>IN</sub>      | L          | 1SP    | MAX      | -        | -23.0<br>(70)  | -21.0<br>(90)  | -             |                |
| Output Noise             | V <sub>NO1</sub>  | R <sub>G</sub> =0Ω<br>A-Weighted       | 0                    | 0                    | L<br>R     | Bypass | -        | -        | -              | -112<br>(25)   | -106<br>(5.0) | dBV<br>(μVrms) |
|                          | V <sub>NO2</sub>  | R <sub>G</sub> =0Ω<br>A-Weighted       | 0                    | 0                    | L<br>R     | 1SP    | MAX      | -        | -              | -100<br>(10)   | -94<br>(20)   |                |
|                          | V <sub>NO3</sub>  | R <sub>G</sub> =0Ω<br>A-Weighted       | 0                    | 0                    | L<br>R     | HP     | -        | MAX      | -              | -100<br>(10)   | -94<br>(20)   |                |
|                          | V <sub>NO4</sub>  | R <sub>G</sub> =0Ω<br>A-Weighted       | 0                    | 0                    | L          | 1SP    | MAX      | -        | -              | -100<br>(10)   | -94<br>(20)   |                |

# NJM2705

## ●AC CHARACTERISTICS

( $V^+=3V$ ,  $T_a=25^\circ C$ ,  $V_{IN}=-20dBV(100mVrms)$ ,  $f=1kHz$ ,  $R_L=10k\Omega$ , unless otherwise specified)

| PARAMETER                 | SYMBOL             |         | TEST CONDITION       |                      |            |        |          |          | MIN   | TYP   | MAX  | UNIT |
|---------------------------|--------------------|---------|----------------------|----------------------|------------|--------|----------|----------|-------|-------|------|------|
|                           |                    |         | INPUT                |                      | OUT<br>PUT | MODE   | SP<br>VR | HP<br>VR |       |       |      |      |
|                           |                    |         | L                    | R                    |            |        |          |          |       |       |      |      |
| Total Harmonic Distortion | THD1               | f=1kHz  | V <sub>IN</sub><br>0 | 0<br>V <sub>IN</sub> | L<br>R     | Bypass | -        | -        | -     | 0.02  | 0.05 | %    |
|                           | THD2               | f=1kHz  | V <sub>IN</sub><br>0 | 0<br>V <sub>IN</sub> | L<br>R     | 2SP    | MAX      | -        | -     | 0.1   | 0.5  |      |
|                           | THD3               | f=1kHz  | V <sub>IN</sub><br>0 | 0<br>V <sub>IN</sub> | L<br>R     | HP     | -        | MAX      | -     | 0.1   | 0.5  |      |
|                           | THD4               | f=1kHz  | V <sub>IN</sub><br>0 | 0<br>V <sub>IN</sub> | L<br>R     | 1SP    | MAX      | -        | -     | 0.1   | 0.5  |      |
| BYPASS Gain               | G <sub>VBYP</sub>  | f=1kHz  | V <sub>IN</sub><br>0 | 0<br>V <sub>IN</sub> | L<br>R     | Bypass | -        | -        | -1.0  | 0.0   | 1.0  | dB   |
| Surround Gain             | G <sub>VSUR1</sub> | f=100Hz | V <sub>IN</sub><br>0 | 0<br>V <sub>IN</sub> | L<br>R     | 2SP    | MAX      | -        | 12.5  | 14.5  | 16.5 | dB   |
|                           | G <sub>VSUR2</sub> | f=100Hz | V <sub>IN</sub><br>0 | 0<br>V <sub>IN</sub> | L<br>R     | 2SP    | MIN      | -        | 0.5   | 2.5   | 4.5  |      |
|                           | G <sub>VSUR3</sub> | f=100Hz | V <sub>IN</sub><br>0 | 0<br>V <sub>IN</sub> | L<br>R     | HP     | -        | MAX      | 12.5  | 14.5  | 16.5 |      |
|                           | G <sub>VSUR4</sub> | f=100Hz | V <sub>IN</sub><br>0 | 0<br>V <sub>IN</sub> | L<br>R     | HP     | -        | MIN      | 0.5   | 2.5   | 4.5  |      |
|                           | G <sub>VSUR5</sub> | f=100Hz | V <sub>IN</sub>      | 0                    | L          | 1SP    | MAX      | -        | 6.5   | 8.5   | 10.5 |      |
|                           | G <sub>VSUR6</sub> | f=100Hz | 0                    | V <sub>IN</sub>      | L          | 1SP    | MAX      | -        | 2.0   | 4.0   | 6.0  |      |
|                           | G <sub>VSUR7</sub> | f=100Hz | V <sub>IN</sub>      | 0                    | L          | 1SP    | MIN      | -        | -5.5  | -3.5  | -1.5 |      |
|                           | G <sub>VSUR8</sub> | f=100Hz | 0                    | V <sub>IN</sub>      | L          | 1SP    | MIN      | -        | -12.0 | -10.0 | -8.0 |      |

## ●CONTROL CHARACTERISTICS ( $V^+=3V$ , $T_a=25^\circ C$ unless otherwise specified)

| PARAMETER                   | SYMBOL     | TEST CONDITION       | MIN | TYP | MAX   | UNIT |
|-----------------------------|------------|----------------------|-----|-----|-------|------|
| MODE Select Control Voltage | $V_{MODE}$ | $V_{IN}$ =High Level | 1.2 | -   | $V^+$ | V    |
|                             |            | $V_{IN}$ =Low Level  | 0.0 | -   | 0.3   |      |

## ■SWITCH FUNCTION

### SURROUND FUNCTION SW

| MODE     | SW1     | SW2     | NOTES                                                          |
|----------|---------|---------|----------------------------------------------------------------|
| Bypass   | L, OPEN | L, OPEN | Input Through                                                  |
| 2SP mode | L, OPEN | H       | Surround mode for narrow space two speakers                    |
| HP mode  | H       | L, OPEN | Surround mode for Headphone                                    |
| 1SP mode | H       | H       | Surround mode for monaural speaker (Surround signal from LOUT) |

### STANDBY SW




| MODE    | STBY    | NOTES            |
|---------|---------|------------------|
| Standby | L, open | IC is non-active |
| Active  | H       | IC is active     |

## ■TERMINAL DESCRIPTION

| PIN No.          |                      |                    | SYMBOL                           | FUNCTION                                                                 | EQUIVALENT CIRCUIT | Voltage |
|------------------|----------------------|--------------------|----------------------------------|--------------------------------------------------------------------------|--------------------|---------|
| FFP<br>16        | PCSP<br>16           | SSOP<br>16         |                                  |                                                                          |                    |         |
| 1<br>2           | 4<br>3               | 5<br>6             | LIN<br>RIN                       | Lch Input<br>Rch Input                                                   |                    | 1.15V   |
| 3<br>4<br>9      | 2<br>1<br>12         | 4<br>3<br>14       | LOUT<br>ROUT<br>LMON             | Lch Output<br>Rch Output<br>Filter terminal                              |                    | 1.15V   |
| 5<br>6<br>7<br>8 | 16<br>15<br>14<br>13 | 2<br>1<br>16<br>15 | NFSPR<br>NFHPR<br>NFSPL<br>NFHPL | Filter terminal<br>Filter terminal<br>Filter terminal<br>Filter terminal |                    | 1.15V   |
| 10               | 11                   | 13                 | PS                               | Filter terminal                                                          |                    | 1.15V   |


# NJM2705

## ■TERMINAL DESCRIPTION


| PIN No.   |            |            | SYMBOL     | FUNCTION                                   | EQUIVALENT CIRCUIT                                                                   | Voltage |
|-----------|------------|------------|------------|--------------------------------------------|--------------------------------------------------------------------------------------|---------|
| FFP<br>16 | PCSP<br>16 | SSOP<br>16 |            |                                            |                                                                                      |         |
| 11<br>12  | 10<br>9    | 12<br>11   | SW2<br>SW1 | Mode control switch<br>Mode control switch |    | 0V      |
| 13        | 8          | 10         | STBY       | Standby switch                             |   | 0V      |
| 14        | 7          | 9          | V+         | Power Supply                               | —                                                                                    | V+      |
| 15        | 6          | 8          | GND        | GND                                        | —                                                                                    | 0V      |
| 16        | 5          | 7          | VREF       | Reference voltage                          |  | 1.15V   |

## APPLICATION CIRCUIT (FFP16)

### 1) 2SP mode, HP mode





### 2) 1SP mode, HP mode



Surround signal is outputted from LOUT terminal at 1SP mode.

\_\_\_\_\_




Surround signal is outputted from LOUT terminal at 1SP mode.




## APPLICATION CIRCUIT (SSOP16)

### 1) 2SP mode, HP mode









### 2) 1SP mode, HP mode



Surround signal is outputted from LOUT terminal at 1SP mode.


TYPICAL CHARACTERISTICS



## TYPICAL CHARACTERISTICS


Maximum Input Voltage vs. Operating Voltage (BYPASS)

$f=1\text{kHz}$ ,  $R_L=10\text{k}\Omega$ ,  $\text{THD}=1\%$ ,  $T_a=25^\circ\text{C}$




Maximum Input Voltage vs. Operating Voltage (2SP)

$T_a=25^\circ\text{C}$ ,  $f=100\text{Hz}$ ,  $SP\_VR=MAX$ ,  $R_L=10\text{k}\Omega$ ,  $\text{THD}=1\%$




Maximum Input Voltage vs. Operating Voltage (HP)

$T_a=25^\circ\text{C}$ ,  $f=100\text{Hz}$ ,  $HP\_VR=MAX$ ,  $R_L=10\text{k}\Omega$ ,  $\text{THD}=1\%$




Maximum Input Voltage vs. Temperature (1SP)

$T_a=25^\circ\text{C}$ ,  $f=100\text{Hz}$ ,  $SP\_VR=MAX$ ,  $R_L=10\text{k}\Omega$ ,  $\text{THD}=1\%$




Maximum Input Voltage vs. Temperature (BYPASS)

$V+=3\text{V}$ ,  $f=1\text{kHz}$ ,  $R_L=10\text{k}\Omega$ ,  $\text{THD}=1\%$



Maximum Input Voltage vs. Temperature (2SP)


$V+=3\text{V}$ ,  $f=100\text{Hz}$ ,  $R_L=10\text{k}\Omega$ ,  $SP\_VR=MAX$ ,  $\text{THD}=1\%$



## TYPICAL CHARACTERISTICS


**Maximum Input Voltage vs. Temperature (HP)**

V+=3V, f=100Hz, RL=10k $\Omega$   
HP\_VR=MAX, THD=1%




**Maximum Input Voltage vs. Temperature (1SP)**

V+=3V, f=100Hz, RL=10k $\Omega$   
SP\_VR=MAX, THD=1%




**Output Noise Voltage vs. Temperature**

V+=3V, Rg=0 $\Omega$ , Vout=Lch  
SP\_VR=MAX, HP\_VR=MAX, FILTER=A-Weighted




**Output Noise Voltage vs. Temperature**

V+=3V, Rg=0 $\Omega$ , Vout=Rch  
SP\_VR=MAX, HP\_VR=MAX, FILTER=A-Weighted




**Total Harmonic Distortion vs. Input Voltage (BYPASS)**

V+=3V, Vin=Lch, f=1kHz, Vout=Lch  
RL=10k $\Omega$ , BW=10Hz-80kHz




**Total Harmonic Distortion vs. Input Voltage (2SP)**

V+=3V, Vin=Lch, f=100Hz, Vout=Lch  
RL=10k $\Omega$ , BW=10Hz-80kHz, SP\_VR=MAX




## TYPICAL CHARACTERISTICS


**Total Harmonic Distortion vs. Input Voltage (HP)**




**Total Harmonic Distortion vs. Input Voltage (1SP)**




**Frequency Response (BYPASS)**




**Frequency Response (2SP)**







**Frequency Response (2SP)**



**Phase vs. Frequency (2SP)**



TYPICAL CHARACTERISTICS



[CAUTION]  
The specifications on this databook are only given for information, without any guarantee as regards either mistakes or omissions. The application circuits in this databook are described only to show representative usages of the product and not intended for the guarantee or permission of any right including the industrial rights.