


Connecting cables
M12 to M12, LED
A-coded
male, straight -
female, angled



Ordering data

Male, straight - Female, angled	
PVC	1.5 m
PUR	1.5 m
PUR halogen-free	1.5 m
PUR halogen-free yellow	1.5 m
Resistant to welding beads	1.5 m
Note	

2 LEDs

3-pole

Type	Order No.
SAIL-M12GM12W-3L1.5V	1925410150
SAIL-M12GM12W-3L1.5U	9457790150
SAIL-M12GM12W-3L1.5Q	1926600150
SAIL-M12GM12W-3L1.5T	1004320150
Other versions on request	

2 LEDs

4-pole

Type	Order No.
SAIL-M12GM12W-4-2L1.5V	1925420150
SAIL-M12GM12W-4-2L1.5U	1906410150
SAIL-M12GM12W-4-2L1.5Q	1926610150
SAIL-M12GM12W-4-2L1.5T	1004310150
Other versions on request	

3 LEDs

4-pole

Type	Order No.
SAIL-M12GM12W-4-3L1.5V	1963930150
SAIL-M12GM12W-4-3L1.5U	1963910150
SAIL-M12GM12W-4-3L1.5Q	1232810150
SAIL-M12GM12W-4-3LW1.5QGE	1093060150
SAIL-M12GM12W-4-3LW1.5T	1020930150
Other versions on request	

Standard cable lengths

All cables listed under the ordering data have a length of 1.5 metres. The last four ordering digits must be changed when ordering other standard cable lengths.	1.5 m	xxxxxx0150
	3.0 m	xxxxxx0300
	5.0 m	xxxxxx0500
	10.0 m	xxxxxx1000

Technical data

Rated current	4 A
Protection class	IP 67
Core cross-section	0.34 mm²
Contact surface	gold-plated
Temperature range of housing	-25...+85 °C
Rated voltage	250 V (3- and 4-pole) / 125 V (5-pole)
(acc. to VDE standard 0110 ISO group C)	

Chapter W includes additional technical specifications for the cable

Dimensioned drawing

