





- | | | | | |
|-----------|--------|------------|------------|------------|
| LEAD FREE | 71.12 | [2.800] | 28 | 5-641313-8 |
| | 68.58 | [2.700] | 27 | 5-641313-7 |
| | 66.04 | [2.600] | 26 | 5-641313-6 |
| | 63.50 | [2.500] | 25 | 5-641313-5 |
| | 60.96 | [2.400] | 24 | 5-641313-4 |
| | 58.42 | [2.300] | 23 | 5-641313-3 |
| | 55.88 | [2.200] | 22 | 5-641313-2 |
| | 53.34 | [2.100] | 21 | 5-641313-1 |
| | 50.80 | [2.000] | 20 | 5-641313-0 |
| | 48.26 | [1.900] | 19 | 4-641313-9 |
| | 45.72 | [1.800] | 18 | 4-641313-8 |
| | 43.18 | [1.700] | 17 | 4-641313-7 |
| | 40.64 | [1.600] | 16 | 4-641313-6 |
| | 38.10 | [1.500] | 15 | 4-641313-5 |
| | 35.56 | [1.400] | 14 | 4-641313-4 |
| | 33.02 | [1.300] | 13 | 4-641313-3 |
| | 30.48 | [1.200] | 12 | 4-641313-2 |
| | 27.94 | [1.100] | 11 | 4-641313-1 |
| | 25.40 | [1.000] | 10 | 4-641313-0 |
| | 22.86 | [.900] | 9 | 3-641313-9 |
| 20.32 | [.800] | 8 | 3-641313-8 | |
| 17.78 | [.700] | 7 | 3-641313-7 | |
| 15.24 | [.600] | 6 | 3-641313-6 | |
| 12.70 | [.500] | 5 | 3-641313-5 | |
| 10.16 | [.400] | 4 | 3-641313-4 | |
| 7.62 | [.300] | 3 | 3-641313-3 | |
| 5.08 | [.200] | 2 | 3-641313-2 | |
| | DIM A | NO.OF POSN | ASSEMBLY | |
- | | | | | |
|-------|--------|------------|----------|------------|
| LEAD | 71.12 | [2.800] | 28 | 2-641313-8 |
| | 68.58 | [2.700] | 27 | 2-641313-7 |
| | 66.04 | [2.600] | 26 | 2-641313-6 |
| | 63.50 | [2.500] | 25 | 2-641313-5 |
| | 60.96 | [2.400] | 24 | 2-641313-4 |
| | 58.42 | [2.300] | 23 | 2-641313-3 |
| | 55.88 | [2.200] | 22 | 2-641313-2 |
| | 53.34 | [2.100] | 21 | 2-641313-1 |
| | 50.80 | [2.000] | 20 | 2-641313-0 |
| | 48.26 | [1.900] | 19 | 1-641313-9 |
| | 45.72 | [1.800] | 18 | 1-641313-8 |
| | 43.18 | [1.700] | 17 | 1-641313-7 |
| | 40.64 | [1.600] | 16 | 1-641313-6 |
| | 38.10 | [1.500] | 15 | 1-641313-5 |
| | 35.56 | [1.400] | 14 | 1-641313-4 |
| | 33.02 | [1.300] | 13 | 1-641313-3 |
| | 30.48 | [1.200] | 12 | 1-641313-2 |
| | 27.94 | [1.100] | 11 | 1-641313-1 |
| | 25.40 | [1.000] | 10 | 1-641313-0 |
| | 22.86 | [.900] | 9 | 641313-9 |
| 20.32 | [.800] | 8 | 641313-8 | |
| 17.78 | [.700] | 7 | 641313-7 | |
| 15.24 | [.600] | 6 | 641313-6 | |
| 12.70 | [.500] | 5 | 641313-5 | |
| 10.16 | [.400] | 4 | 641313-4 | |
| 7.62 | [.300] | 3 | 641313-3 | |
| 5.08 | [.200] | 2 | 641313-2 | |
| | DIM A | NO.OF POSN | ASSEMBLY | |

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG S. HOOVER 10-DEC-2004		 TE Connectivity	
		CHK D. BOSSI 10-DEC-2004			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 0.13 [.005] 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		NAME MTA-100 CONNECTOR ASSEMBLY, 26 AWG, TAPE MOUNTED, STANDARD	
		PRODUCT SPEC 108-1050 APPLICATION SPEC 114-1019		SIZE CAGE CODE DRAWING NO A1 00779 C-641313	
MATERIAL 		FINISH 		RESTRICTED TO WEIGHT SCALE: 6:1 SHEET 1 of 1 REV J	
		CUSTOMER DRAWING			