




NOTE (NOTES)


1 MATERIALI (MATERIALS):
CONTATTO: LEGA DI RAME, NICHELATO E DORATO / STAGNATO
BLOCCETTO: RESINA POLIESTERE CARICATA VETRO UL94 V-0
COLORE NERO PER P/N 281523 E 281524;
COLORE GRIGIO PER P/N 284709
ESPULSORE: RESINA POLIAMMIDICA CARICATA VETRO UL94 V-0
COLORE NERO PER P/N 281523 E 281524;
RESINA POLIESTERE CARICATA VETRO UL94 V-0
COLORE GRIGIO PER P/N 284709
(POST: COPPER ALLOY, GOLD DUPLEX PLATED OVER NICKEL)
HOUSING: GLASS FIBER FILLED PBT F.R.
COLOUR BLACK FOR P/N 281523 AND 281524;
COLOUR GREY FOR P/N 284709
LATCH: GLASS FIBER FILLED POLYAMIDE F.R.
COLOUR BLACK FOR P/N 281523 AND 281524;
GLASS FIBER FILLED PBT F.R.
COLOUR GREY FOR P/N 284709


2 QUESTA POLARIZZAZIONE NON E' ESISTENTE NEI CONNETTORI A 10 E 14 POSIZIONI (AT THIS SIDE OF CONNECTOR NO POLARIZATION ON 10 AND 14 POSITION VERSIONS)

3 AMMESSO IMBARCAMENTO (ADMITTED WARPING) $\pm 0,25/50$ PER 60 POSIZIONI (FOR 60 POSITIONS)

*** P/N OBSOLETI (OBSOLETE P/N)**

QUESTO CONNETTORE E' APPROVATO E CERTIFICATO
(THIS CONNECTOR IS APPROVED AND CERTIFIED.)



				(SEE TABLE) VEDERE TABELLA -	
FINITURA / COLORE (FINISH / COLOUR)		MATERIALE (MATERIAL)		NUMERO (PART NUMBER)	
CUSTOMER DWG. FOR REFERENCE ONLY			DISEGNO PER CLIENTE SOLO PER RIFERIMENTO		
S DRAWING IS UNPUBLISHED		RELEASE FOR PUBLICATION		19	
COPYRIGHT 1983 BY AMP INCORPORATED, HARRISBURG, PA ALL INTERNATIONAL RIGHTS RESERVED AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING					
TOLERANZE: SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES UNLESS OTHERWISE SPECIFIED)		DIAM. ISOLANTE (INS. DIA. RANGE) 		RANGO FILO (WIRE RANGE) 	
± 0,3				SCALA (SCALE) 	
ANGOLI (ANGLES) ± 2°		AMP AMP ITALIA S.p.A. Corso F.lli Cervi, 15 COLLEGGIO (TORINO)			
DATA 10/10/83 25 OTT 83 HARRIS (8 MAR 83)		DESCRIZIONE (DESCRIPTION) AMP LATCH PIN HEADER, MIL TYPE, WITH STAMPED/ROUNDED POST - 2,54 x 2,54 GRID - (RIGHT ANGLE VERS. WITH LATCH 14,55)			
LOC. SIZE		NUMERO (DWG NO)		REV.	FOGLIO (SHEET)
IA3		C - 281523 - ... 281524 - ...		G	1 (OF)

60	73,66	81,28	91,44	85,34	95,50	6-	-0	6-	-0	6-	-0*
50	60,96	68,58	78,74	72,64	82,80	5-	-0	5-	-0	5-	-0*
44	53,34	60,96	71,12	65,02	75,18	4-	-4	4-	-4*	4-	-4
40	48,26	55,88	66,04	59,94	70,10	4-	-0	4-	-0	4-	-0*
34	40,64	48,26	58,42	52,32	62,48	3-	-4	3-	-4	3-	-4*
26	30,48	38,10	48,26	42,16	52,32	2-	-6	2-	-6	2-	-6*
20	22,86	30,48	40,64	34,54	44,70	2-	-0	2-	-0	2-	-0*
16	17,78	25,40	35,56	29,46	39,62	1-	-6	1-	-6	1-	-6
14	15,24	22,86	33,02	26,92	37,08	1-	-4	1-	-4	1-	-4
10	10,16	17,78	27,94	21,84	32,00	1-284709-0		1-281523-0		1-281524-0*	
N° OF POS.		A	B	C	D	E	CONN. P/N (0,2mm Au DUPLEX) COL. GRIGIO	CONN. P/N (0,2mm Au DUPLEX) COL. NERO	CONN. P/N (0,76mm Au DUPLEX) COL. NERO		

DISTRIBUZIONE (PRINT DIST.)