








ORDER C-175474
METRIC
3-D ANGLE PROJECTION

FIG. 3.1

PRINT DIST
DIMENSIONS IN MILLIMETERS, DO NOT SCALE PRINT

8 7 6 5 4 3 2 1



注記:
1. 基板及びコネクタの n 数は、基準位置から数える。
(AMPマーク側が図号番号1番となる。)
△材料: ハウジング: ガラス入り66ナイロン
(UL 94V-0) 色、黒。
※コンタクト: 銅青銅。
※リテンションレグ: 黄銅。
△表面仕上げ:
※コンタクト: 全面1.3µm以上のニッケル下地メッキ
に接触部金メッキ(表参照) 脚部1µm以上の半田
メッキ。
※リテンションレグ: 1.3µm以上のニッケル下地メッキ
に2µm以上の半田メッキ。
△カードエッジコネクタとして使用する場合、かん合用基板
の厚さは、1.6であること。
NOTE
1. NUMBER "n" IS COUNTED FROM DATUM
(CIRCUIT NO. 1 IS "AMP" MARK SIDE.)
△ MATERIAL: HOUSING: 66 NYLON (GF) UL 94V-0, BLACK.
CONTACT: PHOSPHOR BRONZE.
RETENTION LEG: BRASS.
△ FINISH: CONTACT: AU AT CONTACT AREA (SEE TABLE), TIN LEAD AT TIME
OVER NI.
RETENTION LEG: TIN LEAD UNDER NI.

△ P.C. BOARD THK MUST BE 1.6 FOR CARD EDGE CONNECTOR

6-	-2		130	64	81.28	86.82	88.68	92.48	83.18
6-	-1		120	59	74.93	80.47	82.33	86.13	76.83
6-	-0		100	49	62.23	67.77	69.63	73.43	64.13
5-	-9		80	39	49.53	55.07	56.93	60.73	51.43
5-	-8		68	33	41.91	47.45	49.31	53.11	43.81
5-	-7		60	29	36.83	42.37	44.23	48.03	38.73
5-	-6		50	24	30.48	36.02	37.88	41.68	32.38
5-	-5		40	19	24.13	29.67	31.53	35.33	26.03
5-	-3		30	14	17.78	23.32	25.18	28.98	19.68
5-	-1	0.75µ	20	9	11.43	16.97	18.83	22.63	13.33
4-	-2		130	64	81.28	86.82	88.68	92.48	83.18
4-	-1		120	59	74.93	80.47	82.33	86.13	76.83
4-	-0		100	49	62.23	67.77	69.63	73.43	64.13
3-	-9		80	39	49.53	55.07	56.93	60.73	51.43
3-	-8		68	33	41.91	47.45	49.31	53.11	43.81
3-	-7		60	29	36.83	42.37	44.23	48.03	38.73
3-	-6		50	24	30.48	36.02	37.88	41.68	32.38
3-	-5		40	19	24.13	29.67	31.53	35.33	26.03
3-	-3		30	14	17.78	23.32	25.18	28.98	19.68
3-	-1	0.5µ	20	9	11.43	16.97	18.83	22.63	13.33
1-	-2		130	64	81.28	86.82	88.68	92.48	83.18
1-	-1		120	59	74.93	80.47	82.33	86.13	76.83
1-	-0		100	49	62.23	67.77	69.63	73.43	64.13
	-9		80	39	49.53	55.07	56.93	60.73	51.43
	-8		68	33	41.91	47.45	49.31	53.11	43.81
	-7		60	29	36.83	42.37	44.23	48.03	38.73
	-6		50	24	30.48	36.02	37.88	41.68	32.38
	-5		40	19	24.13	29.67	31.53	35.33	26.03
	-4		36	17	21.59	27.13	28.99	32.79	23.49
	-3		30	14	17.78	23.32	25.18	28.98	19.68
175474-1		0.2µ	20	9	11.43	16.97	18.83	22.63	13.33

REVISION RECORD				PRODUCT SPECIFICATION				AMP Tyco Electronics AMP Kawasaki, Japan			
E	REVISED	FJ00-1313-01	T.K.	108-5290	WIRE RANGE	INSULATION DIA	NAME	AMP CHAMP.050 CONNECTOR (B-T-B)			
D	REVISED	ECN FJ00-1045-93	T.N.Y.F.					RECEPTACLE CONNECTOR (HORIZONTAL WITH RETENTION LEG)			
C	REVISED	ECN J-1983	T.N.Y.F.					GENERAL TOLERANCE	SIZE	LOC	NUMBER
B	REVISED	ECN J-12511	T.N.Y.F.						C	J	C-175474
A	REVISED	ECN J-12103	H.K.Y.F.					SCALE	REV.	E	1 OF 1
O	RELEASED	ECN J-10612	S.I.Y.F.								
LTR	REVISION RECORD			OR	CHK	DATE	APP.	CUSTOMER DRAWING			