


# ROUND VINYL CAPS

**VINYL  
CAPS**

Round Vinyl Caps are used for a variety of applications including color coding, dust barriers, insulators, thread protectors, paint masking, and cosmetic decoration. They are resistant to weather, moisture, oxidation and petroleum products. In addition, they will not shred, crack, or split in normal applications.




| Catalog<br>Number | Dimensions |      |        |       |        |      | Standard<br>Color |
|-------------------|------------|------|--------|-------|--------|------|-------------------|
|                   | A          |      | B      |       | C      |      |                   |
|                   | inches     | mm   | inches | mm    | inches | mm   |                   |
| 3544              | 0.137      | 3.48 | 0.500  | 12.70 | 0.033  | 0.84 | Black             |
| 3545              | 0.187      | 4.75 | 0.500  | 12.70 | 0.038  | 0.97 | White             |
| 3546              | 0.250      | 6.35 | 0.625  | 15.88 | 0.043  | 1.09 | Red               |
| 3547              | 0.313      | 7.95 | 0.625  | 15.88 | 0.043  | 1.09 | Blue              |
| 3548              | 0.375      | 9.53 | 0.750  | 19.05 | 0.043  | 1.09 | Yellow            |

Additional sizes and colors available subject to minimum order quantities.

# VINYL GROMMETS

**GV**

Vinyl Grommets are inexpensive, flexible, and oil resistant. They have a high dielectric strength and outstanding aging qualities. The standard color is black.



Hardness Durometer: 60 +/- 5 Shore A  
Tensile Strength: 1400 psi  
Abrasive Resistance: Excellent  
Effect of Sunlight: Slight to None  
Hydro Carbon Solvent Resistance: Good  
Weak Acid Resistance: No Effect  
Burning Rate: Self Extinguishing

| Polyethylene<br>Catalog Number<br>Size | Dimensions |       |        |      |        |       |        |       |        |       | Standard<br>Package<br>pcs / pkg |
|----------------------------------------|------------|-------|--------|------|--------|-------|--------|-------|--------|-------|----------------------------------|
|                                        | A          |       | B      |      | C      |       | D      |       | E      |       |                                  |
|                                        | inches     | mm    | inches | mm   | inches | mm    | inches | mm    | inches | mm    |                                  |
| GV-1/4                                 | 0.125      | 3.18  | 0.063  | 1.60 | 0.344  | 8.74  | 0.188  | 4.78  | 0.250  | 6.35  | 100, 1000                        |
| GV-5/16                                | 0.188      | 4.78  | 0.063  | 1.60 | 0.438  | 11.13 | 0.219  | 5.56  | 0.313  | 7.95  | 100, 1000                        |
| GV-3/8                                 | 0.250      | 6.35  | 0.063  | 1.60 | 0.563  | 14.30 | 0.250  | 6.35  | 0.375  | 9.53  | 100, 1000                        |
| GV-7/16                                | 0.313      | 7.95  | 0.063  | 1.60 | 0.625  | 15.88 | 0.250  | 6.35  | 0.438  | 11.13 | 100, 1000                        |
| GV-1/2                                 | 0.375      | 9.53  | 0.063  | 1.60 | 0.625  | 15.88 | 0.250  | 6.35  | 0.500  | 12.70 | 100, 1000                        |
| GV-5/8                                 | 0.500      | 12.70 | 0.063  | 1.60 | 0.813  | 20.65 | 0.281  | 7.14  | 0.625  | 15.88 | 100, 500                         |
| GV-21/32                               | 0.391      | 9.93  | 0.125  | 3.18 | 0.844  | 21.44 | 0.375  | 9.53  | 0.656  | 16.66 | 100, 500                         |
| GV-7/8                                 | 0.625      | 15.88 | 0.063  | 1.60 | 1.125  | 28.58 | 0.281  | 7.14  | 0.875  | 22.23 | 100, 500                         |
| GV-1                                   | 0.688      | 17.48 | 0.063  | 1.60 | 1.313  | 33.35 | 0.375  | 9.53  | 1.000  | 25.40 | 100, 500                         |
| GV-1-3/8                               | 1.000      | 25.40 | 0.125  | 3.18 | 1.750  | 44.45 | 0.500  | 12.70 | 1.375  | 34.93 | 100, 250                         |