

Heavy-Duty Power Extension Cord, 15A, 14AWG (Left Angle IEC-320-C14 to IEC-320-C13), 10-ft.

MODEL NUMBER: **P005-010-14LA**



Description

Use Tripp Lite's P005-010-14LA in server applications that require a higher rated, heavier gauge cable, and in which space is in high demand. The left-angle C14 connector on this power cord is perfect for saving space in tight areas, such as in the back of your rack enclosure cabinet. When plugged in, it seats flush against the back of a device (e.g. PDU, UPS, etc.), providing space for your rack door to close, or additional room to organize a tight area. C13 to Left-Angle C14 connectors, 3 x 14 AWG conductors, 15A rating, 100-250V, SJT jacket. Tripp Lite Lifetime Limited Warranty.

Features

- Molded, Heavy-Duty Power Cable, 10 ft.
- IEC-60320-C13 to Left-Angle IEC-60320-C14 connectors
- Left-angle C14 connector is perfect for saving space in tight areas
- 14 AWG x 3C, 15A, 100-250V, SJT jacket
- RoHS Compliant
- UL Listed

Specifications

General Info	
Product Group	POWER CORDS
OVERVIEW	
Intended Application	Powering Devices
Cable Type	POWER
Model Type	Power Cords

Highlights

- 10 ft. C13 to Left-Angle C14 Power Cord
- 14 AWG x 3C, 15A, 100-250V, SJT
- UL Listed

Applications

The left-angle C14 connector on this power cord is perfect for saving space in tight areas, such as the back of your rack enclosure cabinet. When plugged in, it seats flush against the back of a device (e.g. PDU, UPS, etc.), providing space for your rack door to close, or additional room to organize a tight area.

Package Includes

- P005-010-14LA C13 to Left-Angle C14 Power Cord

INPUT	
Cable Length (ft.)	10
Cable Length (m)	3.05
UPC ASSIGNMENT	
Unit Carton UPC#	037332179944
PHYSICAL	
Color	Black
Style	Power Cables
CONNECTIONS	
Connector A	IEC-320-C14 - LEFT ANGLE
Connector B	IEC-320-C13
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.