

Technical drawing of a mechanical part showing two views: a top view and a side view.

Top View:

- Dimension **E**: Total width of the part.
- Dimension **F**: Length of the main body, labeled as **REF.** (Reference).
- Dimension **B**: Thickness of the main body, with a tolerance of $B \pm .01 (.25)$.

Side View:

- Dimension **D**: Height of the main body.
- Dimension **C**: Width of the circular feature, labeled as **REF.** (Reference).
- Dimension **A**: Height of the tapered end, with a tolerance of $A \pm .01 (.25)$.

PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE ^{lbs.} (N)	CROSS SECTION	WEIGHT ^{lbs.} /100 pcs. (g)
	MIN. ⁱⁿ (mm)	MAX. ⁱⁿ (mm)									
BT1M	.06 (1.5)	0.90 (23)	.036 (0.9)	.095 (2.4)	.110 (2.8)	.156 (4.0)	.172 (4.4)	4.0 (102)	18 (80)	MINIATURE	.05 (22)
BT1.5M	.06 (1.5)	1.5 (38)	.046 (1.2)	.095 (2.4)	.125 (3.2)	.156 (4.0)	.182 (4.6)	6.3 (160)	18 (80)	MINIATURE	.09 (43)
BT2M	.06 (1.5)	2.0 (51)	.046 (1.2)	.095 (2.4)	.125 (3.2)	.156 (4.0)	.182 (4.6)	7.9 (201)	18 (80)	MINIATURE	.12 (53)
BT4M	.06 (1.5)	4.00 (102)	.046 (1.2)	.095 (2.4)	.125 (3.2)	.156 (4.0)	.182 (4.6)	14.2 (361)	18 (80)	MINIATURE	.21 (93)

PANDUIT CORP. TINLEY PARK, ILLINOIS

DOME-TOP Barb Ty CABLE TIES
BT SERIES

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

SCALE NONE

DRAWING NO.
BT - 0037
SHEET 1 OF 3

DWG
A
SIZE

10	5/2/06	JABO		REMOVED STRAIGHT TIP REFERENCE & TIP STYLE COLUMN	0037	10			
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	