

# MM5Z2V4T1 SERIES

## Zener Voltage Regulators

### 100 mW SOD-523 Surface Mount

This series of Zener diodes is packaged in a SOD-523 surface mount package. They are designed to provide voltage regulation protection and are especially attractive in situations where space is at a premium. They are well suited for applications such as cellular phones, hand held portables, and high density PC boards.

#### Specification Features:

- Standard Zener Breakdown Voltage Range – 2.4 V to 75 V
- Steady State Power Rating of 100 mW
- Small Body Outline Dimensions:  
0.047" x 0.032" (1.20 mm x 0.80 mm)
- Low Body Height: 0.028" (0.7 mm)
- ESD Rating of Class 3 (>16 kV) per Human Body Model

#### Mechanical Characteristics:

**CASE:** Void-free, transfer-molded, thermosetting plastic  
Epoxy Meets UL 94 V-0

**LEAD FINISH:** 100% Matte Sn (Tin)

**MOUNTING POSITION:** Any

**QUALIFIED MAX REFLOW TEMPERATURE:** 260°C

Device Meets MSL 1 Requirements

#### MAXIMUM RATINGS


| Rating                                                             | Symbol         | Max            | Unit |
|--------------------------------------------------------------------|----------------|----------------|------|
| Total Device Dissipation FR-5 Board,<br>@ $T_A = 25^\circ\text{C}$ | $P_D$          | 100            | mW   |
| Junction and Storage<br>Temperature Range                          | $T_J, T_{stg}$ | -65 to<br>+150 | °C   |

Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.




**ON Semiconductor®**

<http://onsemi.com>



**SOD-523  
CASE 502  
PLASTIC**

#### MARKING DIAGRAM



XX = Specific Device Code  
d = Date Code

#### ORDERING INFORMATION

| Device     | Package | Shipping <sup>†</sup> |
|------------|---------|-----------------------|
| MM5ZxxxxT1 | SOD-523 | 3000/Tape & Reel      |

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

#### DEVICE MARKING INFORMATION


See specific marking information in the device marking column of the Electrical Characteristics tables starting on page 3 of this data sheet.

## MM5Z2V4T1 SERIES

### ELECTRICAL CHARACTERISTICS

( $T_A = 25^\circ\text{C}$  unless otherwise noted,  
 $V_F = 0.9\text{ V Max. @ } I_F = 10\text{ mA}$  for all types)

| Symbol       | Parameter                                           |
|--------------|-----------------------------------------------------|
| $V_Z$        | Reverse Zener Voltage @ $I_{ZT}$                    |
| $I_{ZT}$     | Reverse Current                                     |
| $Z_{ZT}$     | Maximum Zener Impedance @ $I_{ZT}$                  |
| $I_{ZK}$     | Reverse Current                                     |
| $Z_{ZK}$     | Maximum Zener Impedance @ $I_{ZK}$                  |
| $I_R$        | Reverse Leakage Current @ $V_R$                     |
| $V_R$        | Reverse Voltage                                     |
| $I_F$        | Forward Current                                     |
| $V_F$        | Forward Voltage @ $I_F$                             |
| $\Theta V_Z$ | Maximum Temperature Coefficient of $V_Z$            |
| C            | Max. Capacitance @ $V_R = 0$ and $f = 1\text{ MHz}$ |



# MM5Z2V4T1 SERIES

**ELECTRICAL CHARACTERISTICS** ( $T_A = 25^\circ\text{C}$  unless otherwise noted,  $V_F = 0.9\text{ V Max.}$  @  $I_F = 10\text{ mA}$  for all types)


| Device    | Device Marking | Zener Voltage (Note 1) |       |      |                   | Zener Impedance                      |                                   |     | Leakage Current                 |       | θV <sub>Z</sub><br>(mV/k)<br>@ I <sub>ZT</sub> |      | C<br>@ V <sub>R</sub> = 0<br>f = 1 MHz |
|-----------|----------------|------------------------|-------|------|-------------------|--------------------------------------|-----------------------------------|-----|---------------------------------|-------|------------------------------------------------|------|----------------------------------------|
|           |                | V <sub>Z</sub> (Volts) |       |      | @ I <sub>ZT</sub> | Z <sub>ZT</sub><br>@ I <sub>ZT</sub> | Z <sub>ZK</sub> @ I <sub>ZK</sub> |     | I <sub>R</sub> @ V <sub>R</sub> |       |                                                |      |                                        |
|           |                | Min                    | Nom   | Max  | mA                | Ω                                    | Ω                                 | mA  | μA                              | Volts | Min                                            | Max  | pF                                     |
| MM5Z2V4T1 | 00             | 2.2                    | 2.4   | 2.6  | 5                 | 100                                  | 1000                              | 1.0 | 50                              | 1.0   | -3.5                                           | 0    | 450                                    |
| MM5Z2V7T1 | 01             | 2.5                    | 2.7   | 2.9  | 5                 | 100                                  | 1000                              | 1.0 | 20                              | 1.0   | -3.5                                           | 0    | 450                                    |
| MM5Z3V0T1 | 02             | 2.8                    | 3.0   | 3.2  | 5                 | 100                                  | 1000                              | 1.0 | 10                              | 1.0   | -3.5                                           | 0    | 450                                    |
| MM5Z3V3T1 | 05             | 3.1                    | 3.3   | 3.5  | 5                 | 95                                   | 1000                              | 1.0 | 5                               | 1.0   | -3.5                                           | 0    | 450                                    |
| MM5Z3V6T1 | 06             | 3.4                    | 3.6   | 3.8  | 5                 | 90                                   | 1000                              | 1.0 | 5                               | 1.0   | -3.5                                           | 0    | 450                                    |
| MM5Z3V9T1 | 07             | 3.7                    | 3.9   | 4.1  | 5                 | 90                                   | 1000                              | 1.0 | 3                               | 1.0   | -3.5                                           | -2.5 | 450                                    |
| MM5Z4V3T1 | 08             | 4.0                    | 4.3   | 4.6  | 5                 | 90                                   | 1000                              | 1.0 | 3                               | 1.0   | -3.5                                           | 0    | 450                                    |
| MM5Z4V7T1 | 09             | 4.4                    | 4.7   | 5.0  | 5                 | 80                                   | 800                               | 1.0 | 3                               | 2.0   | -3.5                                           | 0.2  | 260                                    |
| MM5Z5V1T1 | 0A             | 4.8                    | 5.1   | 5.4  | 5                 | 60                                   | 500                               | 1.0 | 2                               | 2.0   | -2.7                                           | 1.2  | 225                                    |
| MM5Z5V6T1 | 0C             | 5.2                    | 5.6   | 6.0  | 5                 | 40                                   | 200                               | 1.0 | 1                               | 2.0   | -2.0                                           | 2.5  | 200                                    |
| MM5Z6V2T1 | 0E             | 5.8                    | 6.2   | 6.6  | 5                 | 10                                   | 100                               | 1.0 | 3                               | 4.0   | 0.4                                            | 3.7  | 185                                    |
| MM5Z6V8T1 | 0F             | 6.4                    | 6.8   | 7.2  | 5                 | 15                                   | 160                               | 1.0 | 2                               | 4.0   | 1.2                                            | 4.5  | 155                                    |
| MM5Z7V5T1 | 0G             | 7.0                    | 7.5   | 7.9  | 5                 | 15                                   | 160                               | 1.0 | 1                               | 5.0   | 2.5                                            | 5.3  | 140                                    |
| MM5Z8V2T1 | 0H             | 7.7                    | 8.2   | 8.7  | 5                 | 15                                   | 160                               | 1.0 | 0.7                             | 5.0   | 3.2                                            | 6.2  | 135                                    |
| MM5Z9V1T1 | 0K             | 8.5                    | 9.1   | 9.6  | 5                 | 15                                   | 160                               | 1.0 | 0.2                             | 7.0   | 3.8                                            | 7.0  | 130                                    |
| MM5Z10VT1 | 0L             | 9.4                    | 10    | 10.6 | 5                 | 20                                   | 160                               | 1.0 | 0.1                             | 8.0   | 4.5                                            | 8.0  | 130                                    |
| MM5Z11VT1 | 0M             | 10.4                   | 11    | 11.6 | 5                 | 20                                   | 160                               | 1.0 | 0.1                             | 8.0   | 5.4                                            | 9.0  | 130                                    |
| MM5Z12VT1 | 0N             | 11.4                   | 12    | 12.7 | 5                 | 25                                   | 80                                | 1.0 | 0.1                             | 8.0   | 6.0                                            | 10   | 130                                    |
| MM5Z13VT1 | 0P             | 12.4                   | 13.25 | 14.1 | 5                 | 30                                   | 80                                | 1.0 | 0.1                             | 8.0   | 7.0                                            | 11   | 120                                    |
| MM5Z15VT1 | 0T             | 14.3                   | 15    | 15.8 | 5                 | 30                                   | 80                                | 1.0 | 0.05                            | 10.5  | 9.2                                            | 13   | 110                                    |
| MM5Z16VT1 | 0U             | 15.3                   | 16.2  | 17.1 | 2                 | 40                                   | 80                                | 1.0 | 0.05                            | 11.2  | 10.4                                           | 14   | 105                                    |
| MM5Z18VT1 | 0W             | 16.8                   | 18    | 19.1 | 2                 | 45                                   | 80                                | 1.0 | 0.05                            | 12.6  | 12.4                                           | 16   | 100                                    |
| MM5Z20VT1 | 0Z             | 18.8                   | 20    | 21.2 | 2                 | 55                                   | 100                               | 1.0 | 0.05                            | 14.0  | 14.4                                           | 18   | 85                                     |
| MM5Z22VT1 | 10             | 20.8                   | 22    | 23.3 | 2                 | 55                                   | 100                               | 1.0 | 0.05                            | 15.4  | 16.4                                           | 20   | 85                                     |
| MM5Z24VT1 | 11             | 22.8                   | 24.2  | 25.6 | 2                 | 70                                   | 120                               | 1.0 | 0.05                            | 16.8  | 18.4                                           | 22   | 80                                     |
| MM5Z27VT1 | 12             | 25.1                   | 27    | 28.9 | 2                 | 80                                   | 300                               | 1.0 | 0.05                            | 18.9  | 21.4                                           | 25.3 | 70                                     |
| MM5Z30VT1 | 14             | 28                     | 30    | 32   | 2                 | 80                                   | 300                               | 1.0 | 0.05                            | 21.0  | 24.4                                           | 29.4 | 70                                     |
| MM5Z33VT1 | 18             | 31                     | 33    | 35   | 2                 | 80                                   | 300                               | 1.0 | 0.05                            | 23.2  | 27.4                                           | 33.4 | 70                                     |
| MM5Z36VT1 | 19             | 34                     | 36    | 38   | 2                 | 90                                   | 500                               | 1.0 | 0.05                            | 25.2  | 30.4                                           | 37.4 | 70                                     |
| MM5Z39VT1 | 20             | 37                     | 39    | 41   | 2                 | 130                                  | 500                               | 1.0 | 0.05                            | 27.3  | 33.4                                           | 41.2 | 45                                     |
| MM5Z43VT1 | 21             | 40                     | 43    | 46   | 1                 | 150                                  | 500                               | 1.0 | 0.05                            | 30.1  | 37.6                                           | 46.6 | 40                                     |
| MM5Z47VT1 | 1A             | 44                     | 47    | 50   | 1                 | 170                                  | 500                               | 1.0 | 0.05                            | 32.9  | 42.0                                           | 51.8 | 40                                     |
| MM5Z51VT1 | 1C             | 48                     | 51    | 54   | 1                 | 180                                  | 500                               | 1.0 | 0.05                            | 35.7  | 46.6                                           | 57.2 | 40                                     |
| MM5Z56VT1 | 1D             | 52                     | 56    | 60   | 1                 | 200                                  | 500                               | 1.0 | 0.05                            | 39.2  | 52.2                                           | 63.8 | 40                                     |
| MM5Z62VT1 | 1E             | 58                     | 62    | 66   | 1                 | 215                                  | 500                               | 1.0 | 0.05                            | 43.4  | 58.8                                           | 71.6 | 35                                     |
| MM5Z68VT1 | 1F             | 64                     | 68    | 72   | 1                 | 240                                  | 500                               | 1.0 | 0.05                            | 47.6  | 65.6                                           | 79.8 | 35                                     |
| MM5Z75VT1 | 1G             | 70                     | 75    | 79   | 1                 | 255                                  | 500                               | 1.0 | 0.05                            | 52.5  | 73.4                                           | 88.6 | 35                                     |

1. Zener voltage is measured with a pulse test current  $I_Z$  at an ambient temperature of  $25^\circ\text{C}$ .

# MM5Z2V4T1 SERIES

## PACKAGE DIMENSIONS

**SOD-523**  
CASE 502-01  
ISSUE A




### NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETER.
3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH THICKNESS. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL.

| DIM | MILLIMETERS |      |      | INCHES |        |        |
|-----|-------------|------|------|--------|--------|--------|
|     | MIN         | NOM  | MAX  | MIN    | NOM    | MAX    |
| A   | 1.10        | 1.20 | 1.30 | 0.043  | 0.047  | 0.051  |
| B   | 0.70        | 0.80 | 0.90 | 0.028  | 0.032  | 0.035  |
| C   | 0.50        | 0.60 | 0.70 | 0.020  | 0.024  | 0.028  |
| D   | 0.25        | 0.30 | 0.35 | 0.010  | 0.012  | 0.014  |
| J   | 0.07        | 0.14 | 0.20 | 0.0028 | 0.0055 | 0.0079 |
| K   | 0.15        | 0.20 | 0.25 | 0.006  | 0.008  | 0.010  |
| S   | 1.50        | 1.60 | 1.70 | 0.059  | 0.063  | 0.067  |

## SOLDERING FOOTPRINT



SCALE 10:1 (mm/inches)

**ON Semiconductor** and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## PUBLICATION ORDERING INFORMATION

**LITERATURE FULFILLMENT:**  
Literature Distribution Center for ON Semiconductor  
P.O. Box 61312, Phoenix, Arizona 85082-1312 USA  
**Phone:** 480-829-7710 or 800-344-3860 Toll Free USA/Canada  
**Fax:** 480-829-7709 or 800-344-3867 Toll Free USA/Canada  
**Email:** [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

**N. American Technical Support:** 800-282-9855 Toll Free  
USA/Canada

**Japan:** ON Semiconductor, Japan Customer Focus Center  
2-9-1 Kamimeguro, Meguro-ku, Tokyo, Japan 153-0051  
**Phone:** 81-3-5773-3850

**ON Semiconductor Website:** <http://onsemi.com>

**Order Literature:** <http://www.onsemi.com/litorder>

For additional information, please contact your local Sales Representative.

**MM5Z2V4T1/D**