

0-72VDC, 0-1.5A, Programmable DC Supply w/RS232 Interface Model 1787B



Models 1785B, 1786B, 1787B & 1788 are Programmable DC Power Supplies that offer new levels of "ease of use" and programmable functionality. Direct key in entry makes voltage and current selection fast, accurate and easy. In case calibration allows for simple, cost savings, uninterrupted operation.

- Sixteen user programmable preset outputs
- Controllable Output On/Off Switch
- 10mV/10mA setability resolution
- Closed case calibration
- Low ripple and noise
- Excellent temperature stability
- Serial interface cable and software included

Data Sheet

Models 1785B, 1786B, 1787B & 1788

Programmable DC Power Supplies

Models 1785B, 1786B, 1787B & 1788 are Programmable DC Power Supplies that offer new levels of "ease of use" and programmable functionality. Direct key in entry makes voltage and current selection fast, accurate and easy. In case calibration allows for simple, cost savings, uninterrupted operation.

- Sixteen user programmable preset outputs
- Controllable Output On/Off Switch
- 10mV/10mA setable resolution
- Closed case calibration
- Low ripple and noise
- Excellent temperature stability
- Serial interface cable and software included



Model 1788

Specifications				
	1785B	1786B	1787B	models 1788
Parameter				
Output Ratings, (0 °C - 40 °C)				
Voltage	0 ~18V	0 ~32V	0 ~72V	0 ~32V
Current	0 ~5A	0 ~3A	0~1.5V	0~6A
Load Regulation, ±(% of output +offset)	<0.01% + 3mV , Model 1788 = <0.02% + 5mV			
Voltage				
Current				
Line Regulation, ±(% of output +offset)	<0.1% + 3mV			
Voltage				
Current				
Ripple, (20Hz ~20MHz)	≤ 1mVrms/3mVp-p			
Voltage				
Current				