

# EMI2180

## Common Mode Filter with ESD Protection

### Functional Description

The EMI2180 is an industry first Common Mode Filter tuned to MHL speed (CMF) with integrated ESD protection. Differential signaling I/Os can now have both common mode filtering and ESD protection in one package, instead of using separate devices for each function. In addition, traditional common mode chokes are coil-based, while the EMI2180 is silicon-based. This enables the EMI2180 to have a smaller footprint and profile. The EMI2180 protects against ESD pulses up to  $\pm 15$  kV contact per the IEC61000-4-2 standard.

The EMI2180 is particularly well-suited for protecting systems using high-speed differential ports such as MHL, MHL to USB interface corresponding ports in removable storage, digital camcorders, DVD-RW drives; and other applications where ESD protection are required in a small footprint package.

The EMI2180 is available in a RoHS-compliant, WDFN-8 package.

### Features

- Single Integrated Package for Common Mode Filter (CMF) and ESD Protection for MHL High Speed Data Lines
- High Differential Mode Bandwidth Cutoff Frequency for Best Signal Integrity
- Low Profile with Small Footprint in WDFN6 1.6 x 2.0 mm Package
- Provides ESD Protection to IEC61000-4-2 Level 4,  $\pm 15$  kV Contact Discharge
- Low Channel Input Capacitance
- These Devices are Pb-Free and are RoHS Compliant

### Applications

- I/O Ports, Display, MHL in Mobile Phones, Wireless Handsets and Cameras
- MHL to USB Interface
- High-Speed Differential Data Lines





Figure 1. EMI2180 Electrical Schematic




**ON Semiconductor®**

<http://onsemi.com>



**WDFN6  
CASE 511BV**

### MARKING DIAGRAM




2M = Specific Device Code

M = Date Code

▪ = Pb-Free Package

(\*Note: Microdot may be in either location)

### PIN CONNECTIONS



(Top View)

### ORDERING INFORMATION

| Device       | Package         | Shipping†          |
|--------------|-----------------|--------------------|
| EMI2180MTTBG | WDFN6 (Pb-Free) | 3000 / Tape & Reel |

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

## EMI2180

### PIN FUNCTION DESCRIPTION

| Pin Name | Pin No.   | Type | Description                            |
|----------|-----------|------|----------------------------------------|
| MHL_In+  | 1         | I/O  | CMF Channel 1+ to Connector (External) |
| MHL_In-  | 2         | I/O  | CMF Channel 1- to Connector (External) |
| MHL_Out+ | 6         | I/O  | CMF Channel 1+ to ASIC (Internal)      |
| MHL_Out- | 5         | I/O  | CMF Channel 1- to ASIC (Internal)      |
| VCC      | 4         | VCC  | Supply Protection (External)           |
| NC       | 3         | NC   | No Connect                             |
| GND      | Belly Pad | GND  | GND                                    |

### ABSOLUTE MAXIMUM RATINGS (T<sub>A</sub> = 25°C unless otherwise noted)

| Parameter                                                                          | Symbol | Value       | Unit |
|------------------------------------------------------------------------------------|--------|-------------|------|
| Operating Temperature Range                                                        | Top    | -40 to +85  | °C   |
| Storage Temperature Range                                                          | Tstg   | -65 to +150 | °C   |
| DC Voltage at any channel input                                                    | Vdc    | -0.5 to 5.5 | V    |
| ESD Discharge IEC61000-4-2 Contact Discharge                                       | Vpp    | ±15         | kV   |
| Maximum Lead Temperature for Soldering Purposes<br>(1/8" from Case for 10 seconds) | TL     | 260         | °C   |


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

**ELECTRICAL CHARACTERISTICS** ( $T_A = 25^\circ\text{C}$  unless otherwise noted)


| Symbol     | Parameter                                                                                                                                                                                                 | Test Conditions                                                       | Min                  | Typ | Max | Unit          |
|------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------|----------------------|-----|-----|---------------|
| $I_{LEAK}$ | Channel Leakage Current                                                                                                                                                                                   | $T_A = 25^\circ\text{C}$ , $V_{IN} = 5\text{ V}$ , $V_N = 0\text{ V}$ |                      |     | 1.0 | $\mu\text{A}$ |
| $V_F$      | Channel Negative Voltage                                                                                                                                                                                  | $I_F = 10\text{ mA}$ , $T_A = 25^\circ\text{C}$                       | 0.1                  |     | 1.5 | V             |
| $C_{ID}$   | Channel ID Capacitance (Pin 4 to GND)                                                                                                                                                                     | $T_A = 25^\circ\text{C}$ , At 1 MHz, $V_N = 0\text{ V}$               |                      | 0.8 | 1.3 | pF            |
| $C_{IN}$   | Channel Input Capacitance (Pins 1, 2 to GND)                                                                                                                                                              | $T_A = 25^\circ\text{C}$ , At 1 MHz, $V_N = 0\text{ V}$               |                      | 2.0 |     | pF            |
| $R_{CH}$   | Channel Resistance (Pins 1–6 and 2–5)                                                                                                                                                                     | $T_A = 25^\circ\text{C}$ , At 1 MHz, $V_N = 0\text{ V}$               |                      | 3.5 | 5.0 | $\Omega$      |
| $f_{3dB}$  | Differential Mode (Sdd21) Cut-off Frequency                                                                                                                                                               | 50 $\Omega$ Source and Load Termination                               |                      | 4.0 |     | GHz           |
| $f_{ATTN}$ | Common Mode (Scc21) Stop Band Attenuation                                                                                                                                                                 | @ 75 MHz                                                              |                      | 3   |     | dB            |
|            |                                                                                                                                                                                                           | @ 500 MHz                                                             |                      | 10  |     | dB            |
|            |                                                                                                                                                                                                           | @ 1 GHz ~ 3 GHz                                                       |                      | 15  |     | dB            |
| $f_{ATTN}$ | Mode-to-Mode Conversion (Sdc21, Scd21)                                                                                                                                                                    | up to 6 GHz                                                           |                      | 40  | 35  | dB            |
| $V_{ESD}$  | In-system ESD Withstand Voltage<br>a) Contact discharge per IEC 61000-4-2 standard, Level 4 ( <b>External Pins</b> )<br>b) Contact discharge per IEC 61000-4-2 standard, Level 1 ( <b>Internal Pins</b> ) | (Notes 1 and 2)                                                       | $\pm 15$<br>$\pm 12$ |     |     | kV            |
| $V_{RWM}$  | Reverse Working Voltage                                                                                                                                                                                   | (Note 3)                                                              |                      |     | 5.0 | V             |
| $V_{BR}$   | Breakdown Voltage                                                                                                                                                                                         | $I_T = 1\text{ mA}$ , (Note 4)                                        | 5.6                  |     | 9.0 | V             |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

1. Standard IEC61000-4-2 with  $C_{Discharge} = 150\text{ pF}$ ,  $R_{Discharge} = 330\text{ }\Omega$ ,  $V_N$  grounded.
2. These measurements performed with no external capacitor.
3. TVS devices are normally selected according to the working peak reverse voltage ( $V_{RWM}$ ), which should be equal or greater than the DC or continuous peak operating voltage level
4.  $V_{BR}$  is measured at pulse test current  $I_T$ .

**TYPICAL CHARACTERISTICS**

**Figure 2. Differential Mode Attenuation vs. Frequency**



**Figure 3. Common Mode Attenuation vs. Frequency**

## TRANSMISSION LINE PULSE (TLP) MEASUREMENTS

Transmission Line Pulse (TLP) provides current versus voltage (I-V) curves in which each data point is obtained from a 100 ns long rectangular pulse from a charged transmission line. A simplified schematic of a typical TLP system is shown in Figure 4. TLP I-V curves of ESD protection devices accurately demonstrate the product's ESD capability because the 10 s of amps current levels and under 100 ns time scale match those of an ESD event. This is illustrated in Figure 5 where an 8 kV IEC61000-4-2 current waveform is compared with TLP current pulses at 8 and 16 A. A TLP curve shows the voltage at which the device turns on as well as how well the device clamps voltage over a range of current levels. Typical TLP I-V curves for the EMI2180 are shown in Figure 6.




Figure 4. Simplified Schematic of a Typical TLP System




Figure 5. Comparison Between 8 kV IEC61000-4-2 and 8 A and 16 A TLP Waveforms




Figure 6. Positive and Negative TLP Waveforms

## ESD VOLTAGE CLAMPING

For sensitive circuit elements it is important to limit the voltage that an IC will be exposed to during an ESD event to as low a voltage as possible. The ESD clamping voltage is the voltage drop across the ESD protection diode during an ESD event per the IEC61000-4-2 waveform. Since the IEC61000-4-2 was written as a pass/fail spec for larger systems such as cell phones or laptop computers it is not clearly defined in the spec how to specify a clamping voltage at the device level. ON Semiconductor has developed a way to examine the entire voltage waveform across the ESD protection diode over the time domain of an ESD pulse in the form of an oscilloscope screenshot, which can be found on the datasheets for all ESD protection diodes. For more information on how ON Semiconductor creates these screenshots and how to interpret them please refer to On Semiconductor Application Notes AND8307/D and AND8308/D.

## IEC61000-4-2 Spec.

| Level | Test Voltage (kV) | First Peak Current (A) | Current at 30 ns (A) | Current at 60 ns (A) |
|-------|-------------------|------------------------|----------------------|----------------------|
| 1     | 2                 | 7.5                    | 4                    | 2                    |
| 2     | 4                 | 15                     | 8                    | 4                    |
| 3     | 6                 | 22.5                   | 12                   | 6                    |
| 4     | 8                 | 30                     | 16                   | 8                    |






Figure 7. Diagram of ESD Test Setup

Figure 8. 8 x 20  $\mu$ s Pulse Waveform

## EMI2180




Figure 9. ESD Clamping Voltage +8 kV per IEC6100-4-2 (external to internal pin)






Figure 10. ESD Clamping Voltage -8 kV per IEC6100-4-2 (external to internal pin)




**WDFN6 1.6x2.0, 0.5P**  
**CASE 511BV**  
**ISSUE O**

DATE 17 MAY 2012




**RECOMMENDED  
MOUNTING FOOTPRINT**



DIMENSIONS: MILLIMETERS

\*For additional information on our Pb-Free strategy and soldering details, please download the **onsemi** Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.




**NOTES:**

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSION b APPLIES TO PLATED TERMINAL AND IS MEASURED BETWEEN 0.15 AND 0.20 mm FROM THE TERMINAL TIP.
4. COPLANARITY APPLIES TO THE EXPOSED PAD AS WELL AS THE TERMINALS.

| MILLIMETERS |          |      |
|-------------|----------|------|
| DIM         | MIN      | MAX  |
| A           | 0.60     | 0.80 |
| A1          | 0.00     | 0.05 |
| A3          | 0.20 REF |      |
| b           | 0.20     | 0.40 |
| D           | 1.60 BSC |      |
| D2          | 1.10     | 1.30 |
| E           | 2.00 BSC |      |
| E2          | 0.95     | 1.15 |
| e           | 0.50 BSC |      |
| K           | 0.20     | ---  |
| L           | 0.15     | 0.35 |
| L1          | ---      | 0.10 |

**GENERIC  
MARKING DIAGRAM\***



XX = Specific Device Code

M = Date Code

■ = Pb-Free Package

(Note: Microdot may be in either location)

\*This information is generic. Please refer to device data sheet for actual part marking.

Pb-Free indicator, "G" or microdot "■", may or may not be present.

|                         |                             |                                                                                                                                                                                     |
|-------------------------|-----------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>DOCUMENT NUMBER:</b> | <b>98AON80928E</b>          | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| <b>DESCRIPTION:</b>     | <b>WDFN6, 1.6X2.0, 0.5P</b> | <b>PAGE 1 OF 1</b>                                                                                                                                                                  |

**onsemi** and **onsemi** are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)