








SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	G±0.25
09	30.81	24.99	16.96	16.79	10.96	5.90
15	39.14	33.32	25.18	25.12	19.18	5.90
25	53.03	47.04	39.12	38.84	33.12	5.70
37	69.32	63.50	55.68	55.30	49.68	5.70



PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)



4 = Performance level PL3 ≥ 200 OPERATIONS —
6 = Performance level PL1 ≥ 500 OPERATIONS —

V = SCREWLOCK Threaded UNC 4.40 sellers

SHELL	LEAD FREE PART NUMBER	TIN LEAD PART NUMBER	DESIGNATIONS
09	D09P24A6GV00LF	D09P24A6GV00	HEADER 9 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
15	D15P24A6GV00LF	D15P24A6GV00	HEADER 15 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
25	D25P24A6GV00LF	D25P24A6GV00	HEADER 25 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
37	D37P24A*GV00LF	D37P24A*GV00	HEADER 37 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.

4 = Performance level PL3 ≥ 200 OPERATIONS —
6 = Performance level PL1 ≥ 500 OPERATIONS —

SHELL	LEAD	FREE PART NUMBER	TIN LEAD PART NUMBER	DESIGNATIONS
09	D09P24A*GI00LF	D09P24A*GI00	HEADER 9 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.	
15	D15P24A*GI00LF	D15P24A*GI00	HEADER 15 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.	
25	D25P24A*GI00LF	D25P24A*GI00	HEADER 25 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.	
37	D37P24A*GI00LF	D37P24A*GI00	HEADER 37 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.	

I = SCREWLOCK Threaded M3

4 = Performance level PL3 ≥ 200 OPERATIONS —
6 = Performance level PL1 ≥ 500 OPERATIONS —

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0000

European Views

www.fciconnect.com				surface		tolerance std		projection		mm	
				ISO 1302		ISO 406 ISO 1101					
				TOLERANCES UNLESS OTHERWISE SPECIFIED						Scale	
Dr	JARRY	1995/08/11	ANGULAR	LINEAR		0.X	±0.1	size	A3	2	
Eng	PESSON	1995/08/11				0.XX	±0.1	ECN	110-0059		
Chr	NIRMAL GEORGE	2010-02-23	0.XX	±2		0.XXX	±0.1				
Appr	SUDHIR VARMA	2010-02-23	Product family				D-SUB		Spec ref -		



Copyright FCI.