


## TRANSZORB® Transient Voltage Suppressors



Case Style 1.5KE



RoHS  
COMPLIANT

### FEATURES

- Glass passivated chip junction
- Available in unidirectional and bidirectional
- 1500 W peak pulse power capability with a 10/1000  $\mu$ s waveform, repetitive rate (duty cycle): 0.01 %
- Excellent clamping capability
- Very fast response time
- Low incremental surge resistance
- AEC-Q101 qualified available
- Solder dip 275 °C max. 10 s, per JESD 22-B106
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?999912](http://www.vishay.com/doc?999912)

### TYPICAL APPLICATIONS

Use in sensitive electronics protection against voltage transients induced by inductive load switching and lighting on ICs, MOSFET, signal lines of sensor units for consumer, computer, industrial, automotive, and telecommunication.

### MECHANICAL DATA

**Case:** molded epoxy body over passivated junction  
Molding compound meets UL 94 V-0 flammability rating  
Base P/N-E3 - RoHS compliant, commercial grade  
Base P/NHE3\_X - RoHS compliant, and AEC-Q101 qualified  
("X" denotes revision code e.g. A, B, ...)

**Terminals:** matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 1A whisker test, HE3 suffix meets JESD 201 class 2 whisker test

#### Note

- 1.5KE250A to 1.5KE540A are commercial grade only
- Bidirectional is available from 1.5KE6.8CA to 1.5KE220CA only

**Polarity:** for unidirectional types the color band denotes cathode end, no marking on bidirectional types

| PRIMARY CHARACTERISTICS         |                               |
|---------------------------------|-------------------------------|
| $V_{BR}$ unidirectional         | 6.8 V to 540 V                |
| $V_{BR}$ bidirectional          | 6.8 V to 220 V                |
| $V_{WM}$ unidirectional         | 5.8 V to 459 V                |
| $V_{WM}$ bidirectional          | 5.8 V to 185 V                |
| $P_{PPM}$                       | 1500 W                        |
| $P_D$                           | 6.5 W                         |
| $I_{FSM}$ (unidirectional only) | 200 A                         |
| $T_J$ max.                      | 175 °C                        |
| Polarity                        | Unidirectional, bidirectional |
| Package                         | 1.5KE                         |

### DEVICES FOR BIDIRECTION APPLICATIONS

For bidirectional types, use CA suffix (e.g. 1.5KE220CA)  
Electrical characteristics apply in both directions.

| MAXIMUM RATINGS ( $T_A = 25$ °C unless otherwise noted)                                    |                |                |      |
|--------------------------------------------------------------------------------------------|----------------|----------------|------|
| PARAMETER                                                                                  | SYMBOL         | VALUE          | UNIT |
| Peak pulse power dissipation with a 10/1000 $\mu$ s waveform <sup>(1)</sup> (fig. 1)       | $P_{PPM}$      | 1500           | W    |
| Peak pulse current with a 10/1000 $\mu$ s waveform <sup>(1)</sup>                          | $I_{PPM}$      | See next table | A    |
| Power dissipation on infinite heatsink at $T_L = 75$ °C (fig. 5)                           | $P_D$          | 6.5            | W    |
| Peak forward surge current 8.3 ms single half sine-wave unidirectional only <sup>(2)</sup> | $I_{FSM}$      | 200            | A    |
| Maximum instantaneous forward voltage at 100 A for unidirectional only <sup>(3)</sup>      | $V_F$          | 3.5/5.0        | V    |
| Operating junction and storage temperature range                                           | $T_J, T_{STG}$ | -55 to +175    | °C   |

#### Notes

- (1) Non-repetitive current pulse, per fig. 3 and derated above  $T_A = 25$  °C per fig. 2
- (2) Measured on 8.3 ms single half sine-wave or equivalent square wave, duty cycle = 4 pulses per minute maximum
- (3)  $V_F = 3.5$  V for 1.5KE220A and below;  $V_F = 5.0$  V for 1.5KE250A and above



# 1.5KE6.8A thru 1.5KE540A, 1N6267A thru 1N6303A

[www.vishay.com](http://www.vishay.com)

Vishay General Semiconductor

## ELECTRICAL CHARACTERISTICS (T<sub>A</sub> = 25 °C unless otherwise noted)

| JEDEC®<br>TYPE<br>NUMBER | GENERAL<br>SEMICONDUCTOR<br>PART NUMBER | BREAKDOWN<br>VOLTAGE<br>V <sub>BR</sub> AT I <sub>T</sub> <sup>(1)</sup><br>(V) |      | TEST<br>CURRENT<br>I <sub>T</sub><br>(mA) | STAND-OFF<br>VOLTAGE<br>V <sub>WM</sub><br>(V) | MAXIMUM<br>REVERSE<br>LEAKAGE<br>AT V <sub>WM</sub><br>I <sub>D</sub> <sup>(4)</sup><br>(μA) | MAXIMUM<br>PEAK<br>PULSE<br>CURRENT<br>I <sub>PPM</sub> <sup>(2)</sup><br>(A) | MAXIMUM<br>CLAMPING<br>VOLTAGE<br>AT I <sub>PPM</sub><br>V <sub>C</sub> (V) | MAXIMUM<br>TEMPERATURE<br>COEFFICIENT<br>OF V <sub>BR</sub><br>(%/°C) |
|--------------------------|-----------------------------------------|---------------------------------------------------------------------------------|------|-------------------------------------------|------------------------------------------------|----------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------|-----------------------------------------------------------------------------|-----------------------------------------------------------------------|
|                          |                                         | MIN.                                                                            | MAX. |                                           |                                                |                                                                                              |                                                                               |                                                                             |                                                                       |
| 1N6267A                  | (+)-1.5KE6.8A                           | 6.45                                                                            | 7.14 | 10                                        | 5.80                                           | 1000                                                                                         | 143                                                                           | 10.5                                                                        | 0.057                                                                 |
| 1N6268A                  | (+)-1.5KE7.5A                           | 7.13                                                                            | 7.88 | 10                                        | 6.40                                           | 500                                                                                          | 133                                                                           | 11.3                                                                        | 0.061                                                                 |
| 1N6269A                  | (+)-1.5KE8.2A                           | 7.79                                                                            | 8.61 | 10                                        | 7.02                                           | 200                                                                                          | 124                                                                           | 12.1                                                                        | 0.065                                                                 |
| 1N6270A                  | (+)-1.5KE9.1A                           | 8.65                                                                            | 9.55 | 1.0                                       | 7.78                                           | 50                                                                                           | 112                                                                           | 13.4                                                                        | 0.068                                                                 |
| 1N6271A                  | (+)-1.5KE10A                            | 9.50                                                                            | 10.5 | 1.0                                       | 8.55                                           | 10                                                                                           | 103                                                                           | 14.5                                                                        | 0.073                                                                 |
| 1N6272A                  | (+)-1.5KE11A                            | 10.5                                                                            | 11.6 | 1.0                                       | 9.40                                           | 5.0                                                                                          | 96.2                                                                          | 15.6                                                                        | 0.075                                                                 |
| 1N6273A                  | (+)-1.5KE12A                            | 11.4                                                                            | 12.6 | 1.0                                       | 10.2                                           | 5.0                                                                                          | 89.8                                                                          | 16.7                                                                        | 0.078                                                                 |
| 1N6274A                  | (+)-1.5KE13A                            | 12.4                                                                            | 13.7 | 1.0                                       | 11.1                                           | 5.0                                                                                          | 82.4                                                                          | 18.2                                                                        | 0.081                                                                 |
| 1N6275A                  | (+)-1.5KE15A                            | 14.3                                                                            | 15.8 | 1.0                                       | 12.8                                           | 1.0                                                                                          | 70.8                                                                          | 21.2                                                                        | 0.084                                                                 |
| 1N6276A                  | (+)-1.5KE16A                            | 15.2                                                                            | 16.8 | 1.0                                       | 13.6                                           | 1.0                                                                                          | 66.7                                                                          | 22.5                                                                        | 0.086                                                                 |
| 1N6277A                  | (+)-1.5KE18A                            | 17.1                                                                            | 18.9 | 1.0                                       | 15.3                                           | 1.0                                                                                          | 59.5                                                                          | 25.2                                                                        | 0.089                                                                 |
| 1N6278A                  | (+)-1.5KE20A                            | 19.0                                                                            | 21.0 | 1.0                                       | 17.1                                           | 1.0                                                                                          | 54.2                                                                          | 27.7                                                                        | 0.090                                                                 |
| 1N6279A                  | (+)-1.5KE22A                            | 20.9                                                                            | 23.1 | 1.0                                       | 18.8                                           | 1.0                                                                                          | 49.0                                                                          | 30.6                                                                        | 0.092                                                                 |
| 1N6280A                  | (+)-1.5KE24A                            | 22.8                                                                            | 25.2 | 1.0                                       | 20.5                                           | 1.0                                                                                          | 45.2                                                                          | 33.2                                                                        | 0.094                                                                 |
| 1N6281A                  | (+)-1.5KE27A                            | 25.7                                                                            | 28.4 | 1.0                                       | 23.1                                           | 1.0                                                                                          | 40.0                                                                          | 37.5                                                                        | 0.096                                                                 |
| 1N6282A                  | (+)-1.5KE30A                            | 28.5                                                                            | 31.5 | 1.0                                       | 25.6                                           | 1.0                                                                                          | 36.2                                                                          | 41.4                                                                        | 0.097                                                                 |
| 1N6283A                  | (+)-1.5KE33A                            | 31.4                                                                            | 34.7 | 1.0                                       | 28.2                                           | 1.0                                                                                          | 32.8                                                                          | 45.7                                                                        | 0.098                                                                 |
| 1N6284A                  | (+)-1.5KE36A                            | 34.2                                                                            | 37.8 | 1.0                                       | 30.8                                           | 1.0                                                                                          | 30.1                                                                          | 49.9                                                                        | 0.099                                                                 |
| 1N6285A                  | (+)-1.5KE39A                            | 37.1                                                                            | 41.0 | 1.0                                       | 33.3                                           | 1.0                                                                                          | 27.8                                                                          | 53.9                                                                        | 0.100                                                                 |
| 1N6286A                  | (+)-1.5KE43A                            | 40.9                                                                            | 45.2 | 1.0                                       | 36.8                                           | 1.0                                                                                          | 25.3                                                                          | 59.3                                                                        | 0.101                                                                 |
| 1N6287A                  | (+)-1.5KE47A                            | 44.7                                                                            | 49.4 | 1.0                                       | 40.2                                           | 1.0                                                                                          | 23.1                                                                          | 64.8                                                                        | 0.101                                                                 |
| 1N6288A                  | (+)-1.5KE51A                            | 48.5                                                                            | 53.6 | 1.0                                       | 43.6                                           | 1.0                                                                                          | 21.4                                                                          | 70.1                                                                        | 0.102                                                                 |
| 1N6289A                  | (+)-1.5KE56A                            | 53.2                                                                            | 58.8 | 1.0                                       | 47.8                                           | 1.0                                                                                          | 19.5                                                                          | 77.0                                                                        | 0.103                                                                 |
| 1N6290A                  | (+)-1.5KE62A                            | 58.9                                                                            | 65.1 | 1.0                                       | 53.0                                           | 1.0                                                                                          | 17.6                                                                          | 85.0                                                                        | 0.104                                                                 |
| 1N6291A                  | (+)-1.5KE68A                            | 64.6                                                                            | 71.4 | 1.0                                       | 58.1                                           | 1.0                                                                                          | 16.3                                                                          | 92.0                                                                        | 0.104                                                                 |
| 1N6292A                  | (+)-1.5KE75A                            | 71.3                                                                            | 78.8 | 1.0                                       | 64.1                                           | 1.0                                                                                          | 14.6                                                                          | 104                                                                         | 0.105                                                                 |
| 1N6293A                  | (+)-1.5KE82A                            | 77.9                                                                            | 86.1 | 1.0                                       | 70.1                                           | 1.0                                                                                          | 13.3                                                                          | 113                                                                         | 0.105                                                                 |
| 1N6294A                  | (+)-1.5KE91A                            | 86.5                                                                            | 95.5 | 1.0                                       | 77.8                                           | 1.0                                                                                          | 12.0                                                                          | 125                                                                         | 0.106                                                                 |
| 1N6295A                  | (+)-1.5KE100A                           | 95.0                                                                            | 105  | 1.0                                       | 85.5                                           | 1.0                                                                                          | 10.9                                                                          | 137                                                                         | 0.106                                                                 |
| 1N6296A                  | (+)-1.5KE110A                           | 105                                                                             | 116  | 1.0                                       | 94.0                                           | 1.0                                                                                          | 9.9                                                                           | 152                                                                         | 0.107                                                                 |
| 1N6297A                  | (+)-1.5KE120A                           | 114                                                                             | 126  | 1.0                                       | 102                                            | 1.0                                                                                          | 9.1                                                                           | 165                                                                         | 0.107                                                                 |
| 1N6298A                  | (+)-1.5KE130A                           | 124                                                                             | 137  | 1.0                                       | 111                                            | 1.0                                                                                          | 8.4                                                                           | 179                                                                         | 0.107                                                                 |
| 1N6299A                  | (+)-1.5KE150A                           | 143                                                                             | 158  | 1.0                                       | 128                                            | 1.0                                                                                          | 7.2                                                                           | 207                                                                         | 0.106                                                                 |
| 1N6300A                  | (+)-1.5KE160A                           | 152                                                                             | 168  | 1.0                                       | 136                                            | 1.0                                                                                          | 6.8                                                                           | 219                                                                         | 0.108                                                                 |
| 1N6301A                  | (+)-1.5KE170A                           | 162                                                                             | 179  | 1.0                                       | 145                                            | 1.0                                                                                          | 6.4                                                                           | 234                                                                         | 0.108                                                                 |
| 1N6302A                  | (+)-1.5KE180A                           | 171                                                                             | 189  | 1.0                                       | 154                                            | 1.0                                                                                          | 6.1                                                                           | 246                                                                         | 0.108                                                                 |
| 1N6303A                  | (+)-1.5KE200A                           | 190                                                                             | 210  | 1.0                                       | 171                                            | 1.0                                                                                          | 5.5                                                                           | 274                                                                         | 0.108                                                                 |
| -                        | (+)-1.5KE220A                           | 209                                                                             | 231  | 1.0                                       | 185                                            | 1.0                                                                                          | 4.6                                                                           | 328                                                                         | 0.108                                                                 |
| -                        | 1.5KE250A                               | 237                                                                             | 263  | 1.0                                       | 214                                            | 1.0                                                                                          | 4.4                                                                           | 344                                                                         | 0.110                                                                 |
| -                        | 1.5KE300A                               | 285                                                                             | 315  | 1.0                                       | 256                                            | 1.0                                                                                          | 3.6                                                                           | 414                                                                         | 0.110                                                                 |
| -                        | 1.5KE350A                               | 333                                                                             | 368  | 1.0                                       | 300                                            | 1.0                                                                                          | 3.1                                                                           | 482                                                                         | 0.110                                                                 |
| -                        | 1.5KE400A                               | 380                                                                             | 420  | 1.0                                       | 342                                            | 1.0                                                                                          | 2.7                                                                           | 548                                                                         | 0.110                                                                 |
| -                        | 1.5KE440A                               | 418                                                                             | 462  | 1.0                                       | 376                                            | 1.0                                                                                          | 2.5                                                                           | 602                                                                         | 0.110                                                                 |
| -                        | 1.5KE480A                               | 456                                                                             | 504  | 1.0                                       | 408                                            | 1.0                                                                                          | 2.28                                                                          | 658                                                                         | 0.110                                                                 |
| -                        | 1.5KE510A                               | 485                                                                             | 535  | 1.0                                       | 434                                            | 1.0                                                                                          | 2.15                                                                          | 698                                                                         | 0.110                                                                 |
| -                        | 1.5KE540A                               | 513                                                                             | 567  | 1.0                                       | 459                                            | 1.0                                                                                          | 2.03                                                                          | 740                                                                         | 0.110                                                                 |

### Notes

- (1) Pulse test: t<sub>p</sub> ≤ 50 ms
- (2) Surge current waveform per fig. 3 and derate per fig. 2
- (3) All terms and symbols are consistent with ANSI/IEEE CA62.35
- (4) For bidirectional types with V<sub>R</sub> 10 V and less the I<sub>D</sub> limit is doubled
- (+) Underwriters laboratory recognition for the classification of protectors (QVGQ2) under the UL standard for safety 497B and file number E136766 for both unidirectional and bidirectional devices



| THERMAL CHARACTERISTICS ( $T_A = 25^\circ\text{C}$ unless otherwise noted) |                 |       |                    |
|----------------------------------------------------------------------------|-----------------|-------|--------------------|
| PARAMETER                                                                  | SYMBOL          | VALUE | UNIT               |
| Typical thermal resistance, junction to ambient                            | $R_{\theta JA}$ | 75    | $^\circ\text{C/W}$ |
| Typical thermal resistance, junction to lead                               | $R_{\theta JL}$ | 15.4  |                    |

| ORDERING INFORMATION (Example)     |                 |                        |               |                                  |
|------------------------------------|-----------------|------------------------|---------------|----------------------------------|
| PREFERRED PIN                      | UNIT WEIGHT (g) | PREFERRED PACKAGE CODE | BASE QUANTITY | DELIVERY MODE                    |
| 1.5KE6.8A-E3/54                    | 0.968           | 54                     | 1400          | 13" diameter paper tape and reel |
| 1.5KE6.8AHE3_B/C <sup>(1)(2)</sup> | 0.968           | C                      | 1400          | 13" diameter paper tape and reel |

#### Notes

(1) AEC-Q101 qualified

(2) Applied for 1.5KE6.8AHE3\_B to 1.5KE220AHE3\_B, and 1.5KE6.8CAHE3\_B to 1.5KE220CAHE3\_B

### RATINGS AND CHARACTERISTICS CURVES ( $T_A = 25^\circ\text{C}$ unless otherwise noted)



Fig. 1 - Peak Pulse Power Rating Curve



Fig. 3 - Pulse Waveform



Fig. 2 - Pulse Power or Current vs. Initial Junction Temperature



Fig. 4 - Typical Junction Capacitance




Fig. 5 - Power Derating Curve




Fig. 6 - Maximum Non-Repetitive Forward Surge Current  
Unidirectional only




Fig. 7 - Incremental Clamping Voltage Curve (Unidirectional)




Fig. 8 - Incremental Clamping Voltage Curve (Unidirectional)




Fig. 9 - Incremental Clamping Voltage Curve (Bidirectional)



Fig. 10 - Incremental Clamping Voltage Curve (Bidirectional)




Fig. 11 - Instantaneous Forward Voltage Characteristics Curve



Fig. 12 - Typical Transient Thermal Impedance

## PACKAGE OUTLINE DIMENSIONS in inches (millimeters)



## APPLICATION NOTES

- This series of Silicon Transient Suppressors is used in applications where large voltage transients can permanently damage voltage-sensitive components.
- The TVS diode can be used in applications where induced lightning on rural or remote transmission lines presents a hazard to electronic circuitry (ref: R.E.A. specification P.E. 60).
- This Transient Voltage Suppressor diode has a pulse power rating of 1500 W for 1 ms. The response time of TVS diode clamping action is effectively instantaneous ( $1 \times 10^{-9}$  s bi-directional); therefore, they can protect integrated circuits, MOS devices, hybrids, and other voltage sensitive semiconductors and components. TVS diodes can also be used in series or parallel to increase the peak power ratings.



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.