

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

78216-1001

Status:

Active

Overview:


Impact™ Backplane Connector and Cable Assembly System

Description:

Impact™ 5 Pair, Vertical Power Receptacle, Press-Fit, LCP, Glass Filled UL94-V0, Black, Lead-Free

Documents:	
3D Model	Product Specification PS-78213-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	Backplane Connectors
Series	78216
Application	Conventional, Mezzanine, Orthogonal Midplane
Application Tooling Documents	TM-622018799
Component Type	Power Receptacle
Overview	Impact™ Backplane Connector and Cable Assembly System
Product Name	Impact™
Style	N/A
UPC	883906511500
Physical	
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	3.219/g
Number of Columns	N/A
Number of Pairs	5
Number of Rows	2
Orientation	Vertical
PC Tail Length	2.50mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	5.20mm
Pitch - Termination Interface	2.00mm, 3.20mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to PCB	No
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55°C to +85°C



EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

78216Series

Mates With

78351 Impact™ Right Angle Header, 78446 Impact™ Vertical Headers

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Press-In Tool for 5-Pair Assemblies	0622018667
Impact™ Backplane Press-In Tool	0622018875
Removal Tool for 6-Pair Vertical Power Header and Receptacle	0621008200

Termination Interface: Style

Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact

25A

Data Rate

N/A

Shield Type

N/A

Shielded

No

Voltage - Maximum

250V

Material Info

Reference - Drawing Numbers

Product Specification

PS-78213-001

Sales Drawing

SD-78216-002

This document was generated on 12/09/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[78216-1001](#)