



Thermally-Enhanced High Power RF LDMOS FET 200 W, 50 V, 960 – 1600 MHz

Description

The PTVA102001EA is a 200-watt LDMOS FET intended for use in power amplifier applications in the 960 to 1600 MHz frequency band. Features include high gain and thermally-enhanced package with bolt-down flange. Manufactured with Infineon's advanced LDMOS process, this device provides excellent thermal performance and superior reliability.

PTVA102001EA
Package H-36265-2



Features

- Input matched
- Capable of handling 10:1 VSWR @50 V, 200 W (CW) output power
- Integrated ESD protection
- Low thermal resistance
- Pb-free and RoHS compliant

RF Characteristics

Pulsed RF Performance (tested in Infineon production test fixture)

$V_{DD} = 50\text{ V}$, $I_{DQ} = 100\text{ mA}$, $P_{OUT} = 200\text{ W}$, $f = 1090\text{ MHz}$, 300 μs pulse width, 10% duty cycle

Characteristic	Symbol	Min	Typ	Max	Unit
Gain	G_{ps}	17	18.5	—	dB
Drain Efficiency	η_D	56	59.5	—	%

All published data at $T_{CASE} = 25^\circ\text{C}$ unless otherwise indicated

ESD: Electrostatic discharge sensitive device—observe handling precautions!

RF Characteristics

Typical RF Performance (not subject to production test, verified by design/characterization in Infineon test fixture)

$V_{DD} = 50\text{ V}$, $I_{DQ} = 100\text{ mA}$, Input signal ($t_r = 5\text{ ns}$, $t_f = 6.5\text{ ns}$), $T_{CASE} = 25^\circ\text{C}$, class AB test

Mode of Operation	f (MHz)	IRL (dB)	P _{1dB}			P _{3dB}			P _{droop (pulse)} @ 200 W	t _r (ns)	t _f (ns)
			Gain (dB)	Eff (%)	P _{OUT} (W)	Gain (dB)	Eff (%)	P _{OUT} (W)			
300 μs , 10% Duty Cycle	1030	-10	18.5	60	204	16.5	62	240	0.10	6.0	7.9
1 ms, 10% Duty Cycle	1030	-10	18.3	60	200	16.3	62	235	0.20	—	—
20 ms, 10% Duty Cycle	1030	-10	18.2	59	195	16.2	61	225	0.25	—	—
16 ms, 50% Duty Cycle	1030	-10	18.2	58	190	16.2	60	215	0.30	—	—

DC Characteristics

Characteristic	Conditions	Symbol	Min	Typ	Max	Unit
Drain-Source Breakdown Voltage	$V_{GS} = 0\text{ V}$, $I_{DS} = 10\text{ mA}$	$V_{(BR)DSS}$	105	—	—	V
Drain Leakage Current	$V_{DS} = 50\text{ V}$, $V_{GS} = 0\text{ V}$	I_{DSS}	—	—	1	μA
	$V_{DS} = 111\text{ V}$, $V_{GS} = 0\text{ V}$	I_{DSS}	—	—	10	μA
Gate Leakage Current	$V_{GS} = 10\text{ V}$, $V_{DS} = 0\text{ V}$	I_{GSS}	—	—	1	μA
On-State Resistance	$V_{GS} = 10\text{ V}$, $V_{DS} = 0.1\text{ V}$	$R_{DS(on)}$	—	0.34	—	Ω
Operating Gate Voltage	$V_{DS} = 50\text{ V}$, $I_{DQ} = 100\text{ mA}$	V_{GS}	3.1	3.35	3.5	V

Maximum Ratings

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DSS}	105	V
Gate-Source Voltage	V_{GS}	-6 to +12	V
Operating Voltage	V_{DD}	0 to +55	V
Junction Temperature	T_J	225	$^\circ\text{C}$
Storage Temperature Range	T_{STG}	-65 to +150	$^\circ\text{C}$

Thermal Characteristics



$T_{CASE} = 70^\circ\text{C}$, 167 W (CW), 50 V, $I_{DQ} = 100\text{ mA}$, 1030 MHz

Characteristic	Symbol	Value	Unit
Thermal Resistance	$R_{\theta JC}$	0.70	$^\circ\text{C/W}$





Ordering Information

Type and Version	Order Code	Package Description	Shipping
PTVA102001EA V1 R0	PTVA102001EAV1R0XTMA1	H-36265-2, bolt-down	Tape & Reel, 50 pcs
PTVA102001EA V1 R2	PTVA102001EAV1R2XTMA1	H-36265-2, bolt-down	Tape & Reel, 250 pcs





Typical RF Performance (data taken in production test fixture)







Typical RF Performance (cont.)







Typical RF Performance (cont.)




Typical RF Performance (cont.)



Typical RF Performance (cont.)



Load Pull Performance



Pulsed CW signal: 16 μ s pulse width, 10% duty cycle, class AB, $V_{DD} = 50$ V, $I_{DQ} = 90$ mA

		P3dB				
		Maximum Power				
Freq [MHz]	Z_{IN} [Ω]	P_{OUT} [dBm]	P_{OUT} [W]	P_G [dB]	PAE Eff [%]	Z_{OUT} [Ω]
960	$0.97 - j4.50$	54.99	315	16.56	59.8	$2.04 - j0.34$
1030	$1.25 - j5.26$	54.59	288	15.63	57.5	$2.26 - j0.43$
1090	$1.80 - j5.85$	54.53	284	15.64	58.9	$1.77 - j0.33$
1150	$2.37 - j7.11$	54.53	284	15.23	57.0	$2.04 - j0.65$
1200	$2.51 - j6.97$	54.31	270	15.13	55.3	$2.09 - j0.67$
1300	$4.92 - j7.48$	54.55	285	14.70	56.4	$1.80 - j0.99$
1400	$10.54 - j3.45$	54.41	276	14.27	55.7	$1.43 - j1.28$
1500	$7.87 - j0.31$	54.36	273	13.62	53.1	$1.66 - j1.93$
1600	$3.97 - j1.99$	54.19	262	13.10	52.3	$1.49 - j2.21$

Pulsed CW signal: 16 μ s pulse width, 10% duty cycle, class AB, $V_{DD} = 50$ V, $I_{DQ} = 90$ mA

		P3dB				
		Maximum Efficiency				
Freq [MHz]	Z_{IN} [Ω]	P_{OUT} [dBm]	P_{OUT} [W]	P_G [dB]	PAE Eff [%]	Z_{OUT} [Ω]
960	$0.97 - j4.50$	53.57	228	18.32	70.0	$1.73 + j1.19$
1030	$1.25 - j5.26$	53.42	220	17.35	67.2	$1.63 + j0.98$
1090	$1.80 - j5.85$	53.38	218	17.14	67.3	$1.50 + j0.72$
1150	$2.37 - j7.11$	53.47	222	16.82	65.8	$1.41 + j0.42$
1200	$2.51 - j6.97$	52.40	174	17.04	65.4	$1.08 + j0.60$
1300	$4.92 - j7.48$	53.17	207	16.41	65.5	$1.17 - j0.02$
1400	$10.54 - j3.45$	52.99	199	15.95	63.4	$0.85 - j0.61$
1500	$7.87 - j0.31$	53.17	208	15.20	60.8	$1.01 - j1.19$
1600	$3.97 - j1.99$	53.15	207	14.51	58.5	$0.94 - j1.66$

Load Pull Performance (cont.)

Pulsed CW signal: 16 μ s pulse width, 10% duty cycle, class AB, $V_{DD} = 50$ V, $I_{DQ} = 90$ mA


Freq [MHz]	Z_{IN} [Ω]	P3dB				
		Z Optimized				
		P_{OUT} [dBm]	P_{OUT} [W]	P_G [dB]	PAE Eff [%]	Z_{OUT} [Ω]
960	$0.97 - j4.50$	54.51	282	17.55	67.5	$1.94 + j0.54$
1030	$1.25 - j5.26$	54.18	262	16.79	65.1	$1.85 + j0.51$
1090	$1.80 - j5.85$	54.17	261	16.54	65.3	$1.71 + j0.28$
1150	$2.37 - j7.11$	54.12	258	16.28	63.9	$1.65 + j0.04$
1200	$2.51 - j6.97$	53.78	239	16.23	62.9	$1.48 + j0.06$
1300	$4.92 - j7.48$	53.99	251	15.79	62.3	$1.54 - j0.32$
1400	$10.54 - j3.45$	53.89	245	15.34	62.0	$1.07 - j0.84$
1500	$7.87 - j0.31$	53.86	243	14.71	59.5	$1.22 - j1.43$
1600	$3.97 - j1.99$	53.71	235	14.09	57.5	$1.05 - j1.82$

See next page for reference circuit information

Reference Circuit, 1030 – 1090 MHz

Reference Circuit Assembly

DUT	PTVA102001EA
Test Fixture Part No.	LTN/PTVA102001EA V1
PCB	Rogers 6006, 0.635 mm [0.025"] thick, 2 oz. copper, $\epsilon_r = 6.15$



Reference circuit assembly diagram (not to scale)

Reference Circuit (cont.)

Components Information

Component	Description	Manufacturer	P/N
Input			
C101	Capacitor, 10 μ F	TDK Corporation	C5750X5R1H106K230KA
C102, C103, C104	Capacitor, 1000 pF	Panasonic Electronic Components	ECJ-1VB1H102K
C105, C107	Capacitor, 39 pF	ATC	ATC100B390KW500XB
C106	Capacitor, 1 μ F	TDK Corporation	C4532X7R2A105M230KA
C108	Capacitor, 3.6 pF	ATC	ATC100B3R6CW500XB
R101	Resistor, 5.6 Ω	Panasonic Electronic Components	ERJ-8RQJ5R6V
R102, R107	Resistor, 10 Ω	Panasonic Electronic Components	ERJ-8GEYJ100V
R103	Resistor, 1.3K Ω	Panasonic Electronic Components	ERJ-3GEYJ132V
R104	Resistor, 1.2K Ω	Panasonic Electronic Components	ERJ-3GEYJ122V
R105	Resistor, 2000 Ω	Panasonic Electronic Components	ERJ-8GEYJ202V
R106	Resistor, 1000 Ω	Panasonic Electronic Components	ERJ-8GEYJ102V
S1	Transistor	Infineon Technologies	BCP56
S2	Voltage Regulator	Texas Instruments	LM78L05ACM
S3	Potentiometer, 2k Ω	Bourns Inc.	3224W-1-202E
Output			
C201, C211	Capacitor, 10 μ F	TDK Corporation	C5750X5R1H106K230KA
C202, C205, C209	Capacitor, 39 pF	ATC	ATC100B390KW500XB
C203, C204	Capacitor, 1 μ F	TDK Corporation	C4532X7R2A105M230KA
C206	Capacitor, 22 μ F	Cornell Dubilier Electronics (CDE)	SEK220M100ST
C207	Capacitor, 10 μ F	Cornell Dubilier Electronics (CDE)	SEK100M100ST
C208	Capacitor, 100 μ F	Cornell Dubilier Electronics (CDE)	SK101M100ST
C210	Capacitor, 6800 μ F	Panasonic Electronic Components	ECO-S2AP682EA
R201, R202	Resistor, 5.6 Ω	Panasonic Electronic Components	ERJ-8RQJ5R6V

Package Outline Specifications

Package H-36265-2




Diagram Notes—unless otherwise specified:

1. Interpret dimensions and tolerances per ASME Y14.5M-1994.
2. Primary dimensions are mm. Alternate dimensions are inches.
3. All tolerances ± 0.127 [0.005] unless specified otherwise.
4. Pins: D – drain; G – gate; S – source
5. Lead thickness: $0.10 + 0.051/-0.025$ mm [0.004 + 0.002/-0.001 inch].
6. Exposed metal plane on top and bottom of ceramic insulator.
7. Gold plating thickness: 1.14 ± 0.38 micron [45 ± 15 microinch].

Find the latest and most complete information about products and packaging at the Infineon Internet page
<http://www.infineon.com/rfpower>

Revision History


Revision	Date	Data Sheet Type	Page	Subjects (major changes at each revision)
01	2015-07-22	Advance	All	Data Sheet reflects advance specification for product development
02	2015-09-22	Production	All	Data Sheet reflects released product specification
02.1	2017-02-08	Production	2	Updated operating voltage and junction temperature
03	2017-08-17	Production	1 2 5 8, 9	Extend bandwidth to 1600 MHz New Thermal Characteristics table Remove duplicate graph Add load pull points

We Listen to Your Comments

Any information within this document that you feel is wrong, unclear or missing at all?
Your feedback will help us to continuously improve the quality of this document.
Please send your proposal (including a reference to this document) to:

highpowerRF@infineon.com

To request other information, contact us at:
+1 877 465 3667 (1-877-GO-LDMOS) USA
or +1 408 776 0600 International



Edition 2017-08-17

Published by
Infineon Technologies AG
85579 Neubiberg, Germany

© 2015 – 2017 Infineon Technologies AG
All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com/rfpower).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.