

EdgeBoard Connectors

Insulated Wire Pigtails and Solder Cups



Edgeboard connectors are available with insulated Teflon® stranded wire in gages ranging from #24 AWG to #30 AWG.

HOW TO ORDER - INSULATED WIRE PIGTAILS

Conn. Series	Shell Plating Table III*	Insert Material Table I*	Layout	Contact Type	Wire Gage (AWG)	Wire Type Table IV*	Wire Color Table IV*	Wire Length
MWEB	2 – Nickel 4 – Black Anodize 5 – Gold	L – LCP (Liquid Crystal Polymer)	92 128 184N	P – Pin S – Socket	4 - 24 6 - 26 8 - 28 0 - 30	E - Std K - Mil J - Space	1 - White 2 - Yellow 7 - 10 Color Rep.	Length in 1 Inch Increments
Sample Part Number:								
MWEB	2	L —	128	P —	6	E	7 —	18
* SEE INSIDE BACK COVER FOLD-OUT FOR COMPLETE INFORMATION								

HOW TO ORDER - SOLDER CUPS

Conn. Series	Shell Plating Table III*	Insert Material Table I*	Layout	Contact Type	Termination
MWEB	2 – Nickel 4 – Black Anodize 5 – Gold	L – LCP (Liquid Crystal Polymer)	92 128 184N	P – Pin S – Socket	S – Solder Cup
Sample Part Number:					
MWEB	2	L —	128	S	S
* SEE INSIDE BACK COVER FOLD-OUT FOR COMPLETE INFORMATION					