






SWITCH  
SCHEMATIC  
CIRCUIT LAYOUT



ISOMETRIC




PCB MOUNTING



## NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
- ▲ 4. CONTACT RATING: 0.5A @ 100VAC  
0.2A @ 250 VAC  
0.5A @ 25VDC
5. CONTACT MATERIAL: SILVER
6. ELECTRICAL LIFE: 200,000 Typical
7. MECHANICAL LIFE:  
1,000,000 CYCLES TYP.
8. OPERATING TEMP: -20°C TO +70°C
9. OPERATING FORCE: 200 ± 100 gf
10. CONTACT RESISTANCE:  
50 MILLI-OHM INITIAL TYP. MAX.
11. DIELECTRIC STRENGTH:  
1000 VAC FOR 1 MINUTE
12. TRAVEL TO MAKE: 2.20mm ± 0.2
13. 2002/95/EC (ROHS) COMPLIANT
14. ▲ DENOTES CRITICAL PARAMETER



TITLE ULP12OAP1QSSCL1NILNIL

|     |        |                        |         |     |
|-----|--------|------------------------|---------|-----|
| A   | 19817  | RELEASE FOR PRODUCTION | 4/06/11 | BGL |
| REV | PCR NO | DESCRIPTION            | DATE    | BY  |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 1.5:1

DATE 4/7/2011

DR BGL

DWG B800030

REV A