



(CONTACTS PER ROW)




1. INSULATOR MATERIAL: NYLON66, UL94V-0, COLOR:GREY (PANTONE 7528C).
2. CONTACT MATERIAL: BRASS.
3. CONTACT PLATING: TIN OVERALL.
4. CURRENT RATING: 3 AMPS.
5. VOLTAGE RATING: 250V AC/DC.
6. INSULATOR RESISTANCE: 1000 MEGOHMS MIN.
7. CONTACT RESISTANCE: 10 MILLIOHMS MAX.
8. DIELECTRIC WITHSTANDING VOLTAGE: 800V AC.
9. OPERATING TEMPERATURE: -25° C TO +85° C.
10. MATES WITH SWH204 SERIES DUAL ROW HOUSING.



UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MM[INCHES]
TOLERANCES:
ANGULAR: $\pm 5^\circ$
.X= $\pm .3$ [.01]
.XX= $\pm .15$ [.006]
.XXX= $\pm .050$ [.0020]
SURFACE FINISH: 63 Ra
REMOVE ALL BURRS AND SHARP EDGES .010 MAX

INTERPRET DIMENSIONS AND GEOMETRIC
TOLERANCING
PER: ANSI Y14.5M-1994

	DATE	NAME	 SULLINS CONNECTOR SOLUTIONS
DRAWN	7/17/2009	JH	
THE INFORMATION HEREIN CONTAINS PROPRIETARY INFORMATION OF SULLINS ELECTRONICS AND IS NOT TO BE REPRODUCED, USED OR DISCLOSED TO OTHERS FOR ANY PURPOSE EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY AN OFFICER OF SULLINS ELECTRONICS.			DESCRIPTION WAFER, 2mm CC, DUAL ROW, RA
PART NUMBER SWR204-NREN-D__-RA-GA			SIZE DWG. NO. REV C 11286 A
			SCALE: 5:1 SHEET 1 OF 1