





REVISIONS					
P	LTR	DESCRIPTION	DATE	DMN	APVD
H		REVISED PER 0G3B-0188-05	4/22/05	SS	GS
H1		REVISED PER ECO-09-020935	11SEP09	KK	AEG
J		REVISED PER ECO-17-011181	03AUG2017	RS	MZ

NOTES:

- 1 MATES WITH PLUG 207019-1.
- 2 CIRCUITS 1 THRU 8 COMMONED, 9 THRU 16 COMMONED, 17 THRU 24 COMMONED, 25 THRU 32 COMMONED AND 33 THRU 36 COMMONED TOGETHER.
- 3 ALL CURCUITS COMMONED TOGETHER.
- 4 TIN-LEAD OVER NICKEL PER QQ-N-290 OR COPPER PER MIL-C-14550.
- 5 0.76 μm (.000030) MIN GOLD PER MIL-G-45204 FOR A LENGTH OF 5.08 (.200) FROM MATING END, 3.81 μm (.000150) MIN TIN-LEAD PER MIL-T-10727 FOR A LENGTH OF 4.83 (.190) MIN. FROM OPPOSITE END, BOTH OVER 1.27 μm (.000050) MIN NICKEL PER QQ-N-290.
- 6 TIN OVER NICKEL PER QQ-N-290 OR COPPER PER MIL-C-14550.
- 7 0.76 μm (.000030) MIN GOLD PER MIL-G-45204 FOR A LENGTH OF 5.08 (.200) FROM MATING END, 3.81 μm (.000150) MIN TIN PER MIL-T-10727 FOR A LENGTH OF 4.83 (.190) MIN. FROM OPPOSITE END, BOTH OVER 1.27 μm (.000050) MIN NICKEL PER QQ-N-290.
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



OBSOLETE	Δ 7	(1) 36 POSITION	Δ 3	1-208062-1
	Δ 7	(1) 4 POSN AND (4) 8 POSN	Δ 2	1-208062-0
	Δ 6	(1) 36 POSITION	Δ 3	208062-9
OBSOLETE	Δ 6	(1) 4 POSN AND (4) 8 POSN	Δ 2	208062-8
	Δ 5	(1) 36 POSITION	Δ 3	208062-7
	Δ 5	(1) 4 POSN AND (4) 8 POSN	Δ 2	208062-6
	Δ 4	(1) 36 POSITION	Δ 3	208062-3
	Δ 4	(1) 4 POSN AND (4) 8 POSN	Δ 2	208062-1
		FINISH	BUS TYPE	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DMN: D. GELTZ 08/13/92	CHK: R. STONE 9-21-92	STE TE Connectivity	
0 PLC ± -	1 PLC ± -	APVD: -	NAME: -	COMMONING DEVICE ASSEMBLY, 36 POSITION, METRIMATE	
2 PLC ± 0.25[.010]	3 PLC ± -	PRODUCT SPEC: -	APPLICATION SPEC: -	SIZE: A1	CAGE CODE: 00779
4 PLC ± -	ANGLES ± -	WEIGHT: -	DRAWING NO: 208062	RESTRICTED TO: -	SCALE: 2:1
MATERIAL: SEE CALLOUTS	FINISH: SEE CALLOUTS	CUSTOMER DRAWING	SCALE: 2:1	SHEET: 1 of 1	REV: J