

Standard Computer Power Cord, 10A, 18AWG (NEMA 5-15P to Left Angle IEC-320-C13), 6-ft.

MODEL NUMBER: **P006-006-13LA**



Description

Tripp Lite's line of AC power cords offer PC users a solution to their power connectivity problems. This 6ft cable will replace the power cable on most computers and peripherals that have a removable power cord. Cable features an AC style plug (NEMA 5-15P) on one end and a computer style receptacle (IEC-320-C13) on the other end. Left Angle exit allows room for the power cable in tight situations, such as against a wall. UL Listed.

Features

- C13 Left Angle exit ideal for tight spaces
- 6-ft. replacement power cable for a PC, printer, monitor or any other device with like plugs
- Universal design
- Plug type - NEMA 5-15P (AC) to IEC-320-C13 (Device) Left Angle
- 18AWG (0.824mm²), SJT, 10A, 125V
- UL Listed

Specifications

SELECTOR	
Selector Type	CABLES
General Info	
Product Group	POWER CORDS
TAA Compliant	No
OVERVIEW	
Intended Application	Powering Devices

Highlights

- Plug type - NEMA 5-15P (AC) to IEC-320-C13 (Device) Left Angle
- 18AWG (0.824mm²), SJT, 10A, 125V
- UL Listed

Package Includes

- 6-ft. Universal AC Power Replacement Cord, NEMA 5-15P Plug to IEC-320-C13 Receptacle, Left Angle Exit



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Style	Power Cables
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.83
UPC ASSIGNMENT	
Unit Carton UPC#	037332156464
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	NEMA 5-15P
Connector B	IEC-320-C13 - LEFT ANGLE
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.