

Industrial Ethernet Switch - FL SWITCH SFN 16TX - 2891933

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Ethernet switch, 16 TP RJ45 ports, automatic detection of data transmission speed of 10 or 100 Mbps (RJ45), autocrossing function

Product description

Standard function Ethernet switch with 16 RJ45 ports. Provides automatic detection of data transmission speed of 10 or 100 Mbps (RJ45), autocrossing function, 12 V DC ... 48 V DC input voltage, redundant power supply capable with remote alarming.

Why buy this product

- ✓ Devices are available for standard temperature range (0°C ... +60°C) and wide temperature range (-40°C ... +75°C)
- ✓ 16 ports in narrow metal housing with redundant input voltage
- ✓ Auto negotiation and autocrossing detection simplifies installation and setup
- ✓ Security options with cable locking
- ✓ Local diagnostic indicators with LEDs
- ✓ RJ45 ports support a transmission speed of 10/100 Mbps; fiber optic ports support 100 Mbps



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 551588
Weight per Piece (excluding packing)	1037.0 g
Custom tariff number	85176200
Country of origin	Taiwan

Technical data

Dimensions

Width	70 mm
Height	135 mm
Depth	110 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 60 °C

Industrial Ethernet Switch - FL SWITCH SFN 16TX - 2891933

Technical data

Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Air pressure (operation)	86 kPa ... 108 kPa (up to 1500 m above mean sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (up to 3500 m above mean sea level)
Noise immunity	EN 61000-6-2

Interfaces

Interface 1	Ethernet (RJ45)
No. of ports	16 (RJ45 ports)
Connection method	RJ45
Note on connection method	Auto negotiation and autocrossing
Transmission physics	Ethernet in RJ45 twisted pair
Transmission speed	10/100 MBit/s
Transmission length	100 m (per segment)

Function

Basic functions	Unmanaged switch / auto negotiation, complies with IEEE 802.3, store-and-forward switching mode, includes alarm contacts
Status and diagnostic indicators	LEDs: U _{S1} , U _{S2} (redundant voltage supply), link and activity per port, voltage alarm

Network expansion parameters

Cascading depth	Network, linear, and star structure: any
Maximum conductor length ((twisted pair)	100 m

Supply voltage

Supply voltage	24 V DC (redundant)
Residual ripple	3.6 V _{PP} (within the permitted voltage range)
Supply voltage range	12 V DC ... 48 V DC
Typical current consumption	350 mA (at 24 V DC)
Max. current consumption	700 mA (at 12 V DC)

General

Mounting type	DIN rail
Type AX	Block design
Weight	870 g
Housing material	Aluminum
Noise emission	EN 61000-6-4

Conformity with EMC directives

Developed in acc. with standard	IEC 61000-6.2
---------------------------------	---------------

Industrial Ethernet Switch - FL SWITCH SFN 16TX - 2891933

Classifications

eCl@ss

eCl@ss 4.0	24010504
eCl@ss 4.1	24010504
eCl@ss 5.0	19030117
eCl@ss 5.1	19030117
eCl@ss 6.0	19170106
eCl@ss 7.0	19170106
eCl@ss 8.0	19170106

ETIM

ETIM 3.0	EC000734
ETIM 4.0	EC000734
ETIM 5.0	EC000734

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201410
UNSPSC 13.2	43201410

Approvals

Approvals

Approvals

UL Listed / cUL Listed / cULus Listed

Ex Approvals

UL Listed / cUL Listed / cULus Listed

Approvals submitted

Approval details

UL Listed 

Industrial Ethernet Switch - FL SWITCH SFN 16TX - 2891933

Approvals

cUL Listed 

cULus Listed 

Accessories

Accessories

End block

End clamp - E/NS 35 N - 0800886



End clamp, width: 9.5 mm, color: gray

Patch cable

Patch cable - FL CAT5 PATCH 0,3 - 2832250



Patch cable, CAT5, assembled, 0.3 m

Patch cable - FL CAT5 PATCH 0,5 - 2832263



Patch cable, CAT5, assembled, 0.5 m

Patch cable - FL CAT5 PATCH 1,0 - 2832276



Patch cable, CAT5, assembled, 1.0 m

Industrial Ethernet Switch - FL SWITCH SFN 16TX - 2891933

Accessories

Patch cable - FL CAT5 PATCH 1,5 - 2832221



Patch cable, CAT5, assembled, 1.5 m

Patch cable - FL CAT5 PATCH 2,0 - 2832289



Patch cable, CAT5, assembled, 2.0 m

Patch cable - FL CAT5 PATCH 3,0 - 2832292



Patch cable, CAT5, assembled, 3.0 m

Patch cable - FL CAT5 PATCH 5,0 - 2832580



Patch cable, CAT5, assembled, 5.0 m

Patch cable - FL CAT5 PATCH 7,5 - 2832616



Patch cable, CAT5, assembled, 7.5 m

Industrial Ethernet Switch - FL SWITCH SFN 16TX - 2891933

Accessories

Patch cable - FL CAT5 PATCH 10,0 - 2832629



Patch cable, CAT5, assembled, 10.0 m

Phoenix Contact 2014 © - all rights reserved
<http://www.phoenixcontact.com>