



Printed: Sep 23, 2011

PRODUCT NUMBER	SERIES NAME	PITCH
20020013-CXXXXXXLF	03-350	3.50 mm






N = Number of poles
 Dim A = $N \times 3.5 [0.138] + 0.80 [0.031]$
 Dim B = $(N - 1) \times 3.5 [0.138]$

Poles	Tolerance
2-4p	$\pm 0.10 [0.004]$
5-7p	$\pm 0.15 [0.006]$
8-12p	$\pm 0.20 [0.008]$
13-18p	$\pm 0.25 [0.010]$
19-24p	$\pm 0.30 [0.012]$


2p to 6p with wedge, above 7p
 without wedge (including 7p)

mat'l. code	surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK
ltr	ecn no	dr	date	title
D				TERMINAL BLOCK PLUGGABLE, PLUG, SIGNAL, W/O FLANGE FRONT SCREW
				sheet 2 of 5 size
				20020013 A4
				type
				CUSTOMER Drawing
sheet index	revision	sheet		

PRODUCT NUMBER	SERIES NAME	PITCH
20020013-DXXXXXXLF	03-381	3.81 mm



2p to 6p with wedge, above 7p
without wedge (including 7p)






N = Number of poles
Dim A = $N \times 3.81 [.150] + 0.80 [.031]$
Dim B = $(N-1) \times 3.81 [.150]$

Poles	Tolerance
2-6p	$\pm 0.15 [.006]$
7-12p	$\pm 0.20 [.008]$
13-17p	$\pm 0.25 [.010]$
18-24p	$\pm 0.30 [.012]$


mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family TERMINAL BLOCK
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
D					angles linear	MM [INCH]	TERMINAL BLOCK PLUGGABLE, PLUG, SIGNAL, W/O FLANGE FRONT SCREW
					X $\pm 1^\circ$	scale	dwg no
			dr	WENDY CHEN	051810		sheet 3 of 5
			enr	JASON HSU	051810		size
			chr	GARY HSIEH	051810		20020013
			appd	JOSEPH HSIA	051810		A4
sheet index	revision	sheet				type	CUSTOMER Drawing

PRODUCT NUMBER	SERIES NAME	PITCH
20020013-GXXXXXXLF	03-500	5.00 mm




N = Number of poles
 Dim A = $N \times 5.0$ [.197]
 Dim B = $(N-1) \times 5.0$ [.197]

Poles	Tolerance
2-7p	± 0.15 [.006]
8-12p	± 0.25 [.010]
13-18p	± 0.30 [.012]
19-24p	± 0.40 [.016]






mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK	
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title	
D					angles	X.±0.5	TERMINAL BLOCK	
					linear	X.X±0.3	PLUGGABLE, PLUG, SIGNAL, W/O FLANGE	
					X'±1"	X.XX±0.1	FRONT SCREW	
			dr	WENDY CHEN	051810	scale	sheet 4 of 5	
			enr	JASON HSU	051810	FCI	dwg no	
			chr	GARY HSIEH	051810		20020013	
			appd	JOSEPH HSIA	051810		A4	
sheet index	revision	sheet				type	CUSTOMER Drawing	

PRODUCT NUMBER	SERIES NAME	PITCH
20020013-HXXXXXXLF	03-508	5.08 mm



N = Number of poles
Dim A = $N \times 5.08$ [.200]
Dim B = $(N-1) \times 5.08$ [.200]

Poles	Tolerance
2-6p	± 0.15 [.006]
7-12p	± 0.25 [.010]
13-18p	± 0.30 [.012]
19-24p	± 0.40 [.016]



mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK
ltr	ecn	no	dr	date			title
D				angles	X.±0.5 X.X±0.3 X.XX±0.1	scale	TERMINAL BLOCK PLUGGABLE, PLUG, SIGNAL, W/O FLANGE FRONT SCREW
			dr	WENDY CHEN	051810	FCI	dwg no
			enr	JASON HSU	051810		sheet 5 of 5
			chr	GARY HSIEH	051810		20020013
			appd	JOSEPH HSIA	051810		A4
sheet index	revision sheet					type	CUSTOMER Drawing