

125-800 W Fan Heater with Thermostat *FLH Series*



Features

- Designed to prevent condensation or maintain minimum temperature in enclosures.
- Built in Thermostat. (-18 C to +38 C) (0 F to +100 F)
- Fan Auto/On switch with pilot light for Heat On indication
- 20 CFM airflow
- High temperature safety protection
- Aluminum alloy outer casing
- Connection via terminal block.

Part No.	Watts	Voltage	Hz	Overall Dimensions	Ship Wt.
				Height x Width x Depth	lbs
FLHTF125A115	125 W	120 V	60	5.5" x 4.0" x 5.3"	2.2
FLHTF125A230	105/125 W	220/240 V	50/60	5.5" x 4.0" x 5.3"	2.2
FLHTF200A115	200 W	120 V	60	5.5" x 4.0" x 5.3"	2.2
FLHTF200A230	165/200 W	220/240 V	50/60	5.5" x 4.0" x 5.3"	2.2
FLHTF400A115	400 W	120 V	60	7.5" x 4.0" x 5.3"	3
FLHTF400A230	335/400 W	220/240 V	50/60	7.5" x 4.0" x 5.3"	3
FLHTF800A115	800 W	120 V	60	7.5" x 4.0" x 5.3"	3
FLHTF800A230	670/800 W	220/240 V	50/60	7.5" x 4.0" x 5.3"	3

Data subject to change without notice