

MC10114

Triple Line Receiver

The MC10114 is a triple line receiver designed for use in sensing differential signals over long lines. An active current source and translated emitter follower inputs provide the line receiver with a common mode noise rejection limit of one volt in either the positive or the negative direction. This allows a large amount of common mode noise immunity for extra long lines.


Another feature of the MC10114 is that the OR outputs go to a logic low level whenever the inputs are left floating. The outputs are each capable of driving 50 ohm transmission lines.

This device is useful in high speed central processors, minicomputers, peripheral controllers, digital communication systems, testing and instrumentation systems. The MC10114 can also be used for MOS to MECL interfacing and it is ideal as a sense amplifier for MOS RAM's.

A V_{BB} reference is provided which is useful in making the MC10114 a Schmitt trigger, allowing single-ended driving of the inputs, or other applications where a stable reference voltage is necessary. See MECL Design Handbook (HB205) pages 226 and 228.

- $P_D = 145 \text{ mW typ/pkg}$
- $t_{pd} = 2.4 \text{ ns typ (Single Ended Input)}$
- $t_{pd} = 2.0 \text{ ns typ (Differential Input)}$
- $t_r, t_f = 2.1 \text{ ns typ (20\%–80\%)}$


LOGIC DIAGRAM



* V_{BB} to be used to supply bias to the MC10114 only and bypassed (when used) with 0.01 μF to 0.1 μF capacitor to ground (0 V). V_{BB} can source < 1.0 mA.

When the input pin with the bubble goes positive, its respective output pin with bubble goes positive.

DIP PIN ASSIGNMENT



Pin assignment is for Dual-in-Line Package.


For PLCC pin assignment, see the Pin Conversion Tables on page 18 of the ON Semiconductor MECL Data Book (DL122/D).



ON Semiconductor

<http://onsemi.com>

MARKING DIAGRAMS



A = Assembly Location
 WL = Wafer Lot
 YY = Year
 WW = Work Week

ORDERING INFORMATION

Device	Package	Shipping
MC10114L	CDIP-16	25 Units / Rail
MC10114P	PDIP-16	25 Units / Rail
MC10114FN	PLCC-20	46 Units / Rail

MC10114

ELECTRICAL CHARACTERISTICS

Characteristic	Symbol	Pin Under Test	Test Limits							Unit
			-30°C		+25°C			+85°C		
			Min	Max	Min	Typ	Max	Min	Max	
Power Supply Drain Current	I _E	8		39		28	35		39	mAdc
Input Current	I _{inH}	4		70			45		45	μAdc
	I _{CBO}	4		1.5			1.0		1.0	μAdc
Output Voltage Logic 1	V _{OH}	2 3	-1.060 -1.060	-0.890 -0.890	-0.960 -0.960		-0.810 -0.810	-0.890 -0.890	-0.700 -0.700	Vdc
Output Voltage Logic 0	V _{OL}	2 3	-1.890 -1.890	-1.675 -1.675	-1.850 -1.850		-1.650 -1.650	-1.825 -1.825	-1.615 -1.615	Vdc
Threshold Voltage Logic 1	V _{OHA}	2 3	-1.080 -1.080		-0.980 -0.980			-0.910 -0.910		Vdc
Threshold Voltage Logic 0	V _{OLA}	2 3		-1.655 -1.655			-1.630 -1.630		-1.595 -1.595	Vdc
Reference Voltage	V _{BB}	11	-1.420	-1.280	-1.350		-1.230	-1.295	-1.150	Vdc
Common Mode Rejection Test	V _{OH}	2 3	-1.060 -1.060	-0.890 -0.890	-0.960 -0.960		-0.810 -0.810	-0.890 -0.890	-0.700 -0.700	Vdc
	V _{OL}	2 3	-1.890 -1.890	-1.675 -1.675	-1.850 -1.850		-1.650 -1.650	-1.825 -1.825	-1.615 -1.615	Vdc
Switching Times (50Ω Load)			Min	Max	Min	Typ	Max	Min	Max	ns
Propagation Delay	t ₄₊₂₊	2	1.0	4.4	1.0	2.4	4.0	0.9	4.3	
	t ₄₋₂₋	2	1.0	4.4	1.0	2.4	4.0	0.9	4.3	
	t ₄₊₃₋	3	1.0	4.4	1.0	2.4	4.0	0.9	4.3	
	t ₄₋₃₊	3	1.0	4.4	1.0	2.4	4.0	0.9	4.3	
Rise Time (20 to 80%)	t ₂₊	2	1.5	3.8	1.5	2.1	3.5	1.5	3.7	
	t ₃₊	3	1.5	3.8	1.5	2.1	3.5	1.5	3.7	
Fall Time (20 to 80%)	t ₂₋	2	1.5	3.8	1.5	2.1	3.5	1.5	3.7	
	t ₃₋	3	1.5	3.8	1.5	2.1	3.5	1.5	3.7	

ELECTRICAL CHARACTERISTICS (continued)

@ Test Temperature −30°C +25°C +85°C			TEST VOLTAGE VALUES (Volts)						
			V _{IHmax}	V _{ILmin}	V _{IHAmin}	V _{ILAm} ax	V _{BB}		
			−0.890	−1.890	−1.205	−1.500	From Pin 11		
			−0.810	−1.850	−1.105	−1.475			
			−0.700	−1.825	−1.035	−1.440			
Characteristic	Symbol	Pin Under Test	TEST VOLTAGE APPLIED TO PINS LISTED BELOW					Unit	
			V _{IHmax}	V _{ILmin}	V _{IHAmin}	V _{ILAm} ax	V _{BB}		
Power Supply Drain Current	I _E	8		4, 9, 12			5, 10, 13	mAdc	
Input Current	I _{inH}	4	4	9, 12			5, 10, 13	μAdc	
	I _{inL}	4		9, 12			5, 10, 13	μAdc	
Output Voltage	Logic 1	V _{OH}	2 3	4 9, 12	9, 12 4		5, 10, 13 5, 10, 13	Vdc	
Output Voltage	Logic 0	V _{OL}	2 3	9, 12 4	4 9, 12		5, 10, 13 5, 10, 13	Vdc	
Threshold Voltage	Logic 1	V _{OHA}	2 3	9, 12	9, 12	4	5, 10, 13 5, 10, 13	Vdc	
Threshold Voltage	Logic 0	V _{OLA}	2 3	9, 12	9, 12	4	5, 10, 13 5, 10, 13	Vdc	
Reference Voltage		V _{BB}	11				5, 10, 13	Vdc	
Common Mode Rejection Test	V _{OH}	2 3						Vdc	
	V _{OL}	2 3						Vdc	
Switching Times	(50Ω Load)					Pulse In	Pulse Out	ns	
Propagation Delay	t ₄₊₂₊	2				4	2		5, 10, 13
	t _{4−2−}	2				4	2		5, 10, 13
	t _{4+3−}	3				4	3		5, 10, 13
	t _{4−3+}	3				4	3		5, 10, 13
Rise Time	(20 to 80%)	t ₂₊	2			4	2		5, 10, 13
		t ₃₊	3			4	3		5, 10, 13
Fall Time	(20 to 80%)	t _{2−}	2			4	2		5, 10, 13
		t _{3−}	3			4	3		5, 10, 13

ELECTRICAL CHARACTERISTICS (continued)

@ Test Temperature			TEST VOLTAGE VALUES (Volts)					(V _{CC}) Gnd
			V _{IHH} *	V _{ILH} *	V _{IHL} *	V _{ILL} *	V _{EE}	
			−30°C	+0.110	−0.890	−1.890	−2.890	−5.2
			+25°C	+0.190	−0.850	−1.810	−2.850	−5.2
			+85°C	+0.300	−0.825	−1.700	−2.825	−5.2
Characteristic	Symbol	Pin Under Test	TEST VOLTAGE APPLIED TO PINS LISTED BELOW					(V _{CC}) Gnd
			V _{IHH} *	V _{ILH} *	V _{IHL} *	V _{ILL} *	V _{EE}	
Power Supply Drain Current	I _E	8					8	1, 16
Input Current	I _{inH}	4					8	1, 16
	I _{inL}	4					8, 4	1, 16
Output Voltage Logic 1	V _{OH}	2					8	1, 16
		3					8	1, 16
Output Voltage Logic 0	V _{OL}	2					8	1, 16
		3					8	1, 16
Threshold Voltage Logic 1	V _{OHA}	2					8	1, 16
		3					8	1, 16
Threshold Voltage Logic 0	V _{OLA}	2					8	1, 16
		3					8	1, 16
Reference Voltage	V _{BB}	11					8	1, 16
Common Mode Rejection Test	V _{OH}	2	4	5			8	1, 16
		3			5	4	8	1, 16
	V _{OL}	2		5			8	1, 16
		3	4		5	4	8	1, 16
Switching Times (50Ω Load)							−3.2 V	+2.0 V
Propagation Delay	t ₄₊₂₊	2					8	1, 16
	t _{4−2−}	2					8	1, 16
	t _{4+3−}	3					8	1, 16
	t _{4−3+}	3					8	1, 16
Rise Time (20 to 80%)	t ₂₊	2					8	1, 16
	t ₃₊	3					8	1, 16
Fall Time (20 to 80%)	t _{2−}	2					8	1, 16
	t _{3−}	3					8	1, 16

* V_{IHH} = Input Logic 1 level shifted positive one volt for common mode rejection tests

V_{ILH} = Input Logic 0 level shifted positive one volt for common mode rejection tests

V_{IHL} = Input Logic 1 level shifted negative one volt for common mode rejection tests


V_{ILL} = Input Logic 0 level shifted negative one volt for common mode rejection tests

Each MECL 10,000 series circuit has been designed to meet the dc specifications shown in the test table, after thermal equilibrium has been established. The circuit is in a test socket or mounted on a printed circuit board and transverse air flow greater than 500 linear fpm is maintained. Outputs are terminated through a 50-ohm resistor to −2.0 volts. Test procedures are shown for only one gate. The other gates are tested in the same manner.

MC10114

PACKAGE DIMENSIONS


PLCC-20
FN SUFFIX
PLASTIC PLCC PACKAGE
CASE 775-02
ISSUE C



DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.385	0.395	9.78	10.03
B	0.385	0.395	9.78	10.03
C	0.165	0.180	4.20	4.57
E	0.090	0.110	2.29	2.79
F	0.013	0.019	0.33	0.48
G	0.050 BSC		1.27 BSC	
H	0.026	0.032	0.66	0.81
J	0.020	---	0.51	---
K	0.025	---	0.64	---
R	0.350	0.356	8.89	9.04
U	0.350	0.356	8.89	9.04
V	0.042	0.048	1.07	1.21
W	0.042	0.048	1.07	1.21
X	0.042	0.056	1.07	1.42
Y	---	0.020	---	0.50
Z	2 °	10 °	2 °	10 °
G1	0.310	0.330	7.88	8.38
K1	0.040	---	1.02	---


MC10114

PACKAGE DIMENSIONS



- NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
 2. CONTROLLING DIMENSION: INCH.
 3. DIMENSION L TO CENTER OF LEAD WHEN FORMED PARALLEL.
 4. DIMENSION F MAY NARROW TO 0.76 (0.030) WHERE THE LEAD ENTERS THE CERAMIC BODY.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.750	0.785	19.05	19.93
B	0.240	0.295	6.10	7.49
C	---	0.200	---	5.08
D	0.015	0.020	0.39	0.50
E	0.050 BSC		1.27 BSC	
F	0.055	0.065	1.40	1.65
G	0.100 BSC		2.54 BSC	
H	0.008	0.015	0.21	0.38
K	0.125	0.170	3.18	4.31
L	0.300 BSC		7.62 BSC	
M	0°	15°	0°	15°
N	0.020	0.040	0.51	1.01



- NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
 2. CONTROLLING DIMENSION: INCH.
 3. DIMENSION L TO CENTER OF LEADS WHEN FORMED PARALLEL.
 4. DIMENSION B DOES NOT INCLUDE MOLD FLASH.
 5. ROUNDED CORNERS OPTIONAL.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.740	0.770	18.80	19.55
B	0.250	0.270	6.35	6.85
C	0.145	0.175	3.69	4.44
D	0.015	0.021	0.39	0.53
F	0.040	0.70	1.02	1.77
G	0.100 BSC		2.54 BSC	
H	0.050 BSC		1.27 BSC	
J	0.008	0.015	0.21	0.38
K	0.110	0.130	2.80	3.30
L	0.295	0.305	7.50	7.74
M	0°	10°	0°	10°
S	0.020	0.040	0.51	1.01

Notes

ARCHIVE
DEVICE NOT RECOMMENDED FOR NEW DESIGN

ARCHIVE
RECOMMENDED FOR NEW DESIGN

ON Semiconductor and  are trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer.

PUBLICATION ORDERING INFORMATION

Literature Fulfillment:

Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: ONlit@hibbertco.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

JAPAN: ON Semiconductor, Japan Customer Focus Center
4-32-1 Nishi-Gotanda, Shinagawa-ku, Tokyo, Japan 141-0031
Phone: 81-3-5740-2700
Email: r14525@onsemi.com

ON Semiconductor Website: <http://onsemi.com>

For additional information, please contact your local Sales Representative.