










1. MATERIALS:
HOUSING - PBT. GLASS FILLED UL94V-0 BLACK
TERMINAL - COPPER ALLOY
2. FINISHES
PLATING 3 - 15µin (0.38µm) SELECTIVE GOLD IN CONTACT AREA
AND 75µin (1.88µm) TIN IN IDT AREA OVER 50µin (1.25µm)
NICKEL OVERALL.
PLATING 4 - 30µin (0.76µm) SELECTIVE GOLD IN CONTACT AREA
AND 75µin (1.88µm) TIN IN IDT AREA OVER 50µin (1.25µm)
NICKEL OVERALL.
PLATING 5 - 2µin (0.05µm) SELECTIVE GOLD IN CONTACT AREA
AND 75µin (1.88µm) TIN IN IDT AREA OVER 50µin (1.25µm)
NICKEL OVERALL.
3. PRODUCT SPEC PS-87568-004 APPLIES.
4. FOR ILLUSTRATION PURPOSES, 12 CKT IS SHOWN.
5. PART MATES WITH ALL MILLIGRID HEADERS WITH MATING LENGTH (H5)
BETWEEN 2.50mm AND 4.20mm WITH THE RIGHT KEYING OPTION.
6. PART IS DESIGNED FOR 1.00mm PITCH FLAT CABLE, 7 STRANDS,
AWG #28, UL2651 AND UL2678.
7. ALL OTHER CIRCUIT SIZES, CONTACT FACTORY.
8. STRAIN RELIEF TO BE PURCHASED SEPERATELY.
REFER TO SD-87569-008.
9. PACKAGING SPECIFICATION :PK-87568-0001.


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
EC NO: 749397 DRWN: SUAIFR CHK'D: SUAIFR APPR: MRAMAKRISHNA	2023/05/12 2023/05/12 2023/05/13	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION UNITS		SCALE		molex[®]					
					MM		NTS							
			MM	INCH	DRWN BY		DATE		MGRID 2MM DUAL ROW IDT RECEPTACLE					
		4 PLACES	±	±	AGARWAL		1997/08/05							
		3 PLACES	±	±	CHK'D BY		DATE							
		2 PLACES	± 0.15	±	SQUEK		1997/09/03							
		1 PLACES	±	±	APPR BY		DATE							
		0 PLACES	±	±	MLONG		2009/11/13							
		ANGULAR TOL ± 3.0			DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES		MATERIAL NUMBER		CUSTOMER	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			A3				87568		SEE TABLE		GENERAL MARKET	
DOCUMENT NUMBER									DOC TYPE		DOC PART		SHEET NUMBER	
H5	REV						SD-87568-003		PSD		001		1 OF 3	




87568-**4*
POLARIZATION ONLY
(APPLICABLE FOR 14 TO 50CKT)



87568-**9*
POLARIZATION AND RAMP LOCKING
(APPLICABLE FOR 14 TO 50 CKT)




87568-**6*
NO POLARIZATION/RAMP FEATURE
(APPLICABLE FOR 10 TO 50 CKT)





87568-**7*
SINGLE RAMP LOCKING ONLY
(APPLICABLE FOR 10 TO 12 CKT)

ENGINEERING NUMBER	CKT. SIZE	A	B	C	D	E
87568-10**	10	16.65	8.00	14.90	11.65	10.55
87568-12**	12	18.65	10.00	16.90	13.65	12.55
87568-14**	14	20.65	12.00	18.90	15.65	14.55
87568-16**	16	22.65	14.00	20.90	17.65	16.55
87568-20**	20	26.65	18.00	24.90	21.65	20.55
87568-22**	22	28.65	20.00	26.90	23.65	22.55
87568-24**	24	30.65	22.00	28.90	25.65	24.55
87568-26**	26	32.65	24.00	30.90	27.65	26.55
87568-30**	30	36.65	28.00	34.90	31.65	30.55
87568-32**	32	38.65	30.00	36.90	33.65	32.55
87568-34**	34	40.65	32.00	38.90	35.65	34.55
87568-36**	36	42.65	34.00	40.90	37.65	36.55
87568-40**	40	46.65	38.00	44.90	41.65	40.55
87568-44**	44	50.65	42.00	48.90	45.65	44.55
87568-50**	50	56.65	48.00	54.90	51.65	50.55



- 4 - WITH POLARIZATION ONLY FOR 14-50 CKT
6 - WITHOUT POLARIZATION AND RAMP LOCKING
7 - WITH SINGLE RAMP LOCKING ONLY FOR 10 & 12 CKT
9 - WITH POLARIZATION AND RAMP LOCKING 14 - 50 CKT
10-12 CIRCUIT SIZE HAS ONLY ONE RAMP FOR LOCKING (OPTIONAL)
14-50 CIRCUIT SIZE HAS BOTH POLARIZATION AND RAMP LOCKING (OPTIONAL)

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
EC NO: 749397 DRWN: SUAIFR CHK'D: SUAIFR APPR: MRAMAKRISHNA	2023/05/12 2023/05/12 2023/05/13	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION UNITS		SCALE		molex®						
		MM		INCH		NTS									
		4 PLACES	±	±	DRWN BY		DATE		MGRID 2MM DUAL ROW IDT RECEPTACLE						
		3 PLACES	±	±	AGARWAL		1997/08/05								
		2 PLACES	± 0.15	±	CHK'D BY		DATE								
		1 PLACES	±	±	SQUEK		1997/09/03								
		0 PLACES	±	±	APPR BY		DATE		PRODUCT CUSTOMER DRAWING						
		ANGULAR TOL ± 3.0			MLONG		2009/11/13								
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES		MATERIAL NUMBER		CUSTOMER		
					A3				87568		SEE TABLE		GENERAL MARKET		
H5		REV					DOCUMENT NUMBER		DOC TYPE		DOC PART		SHEET NUMBER		
							SD-87568-003		PSD		001		2 OF 3		



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
EC NO: 749397 DRWN: SUAIFR CHK'D: SUAIFR REV / APPR: MRAMAKRISHNA	2023/05/12 2023/05/12 2023/05/13	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS	SCALE	molex®							
			MM	INCH	DRWN BY					DATE			
		4 PLACES	±	±	AGARWAL					1997/08/05			
		3 PLACES	±	±	CHK'D BY					DATE			
		2 PLACES	±	0.15	±					SQUEK	1997/09/03		
		1 PLACES	±	±	APPR BY	DATE	PRODUCT CUSTOMER DRAWING						
		0 PLACES	±	±	MLONG	2009/11/13							
		ANGULAR TOL ± 3.0		DRAWING SIZE	THIRD ANGLE PROJECTION								
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3		SERIES		MATERIAL NUMBER		CUSTOMER			
		H5		REV			87568	SEE TABLE		GENERAL MARKET			
		RELEASE STATUS		P1	RELEASE DATE		2023/05/13	01:47:28		DOCUMENT NUMBER		DOC TYPE	DOC PART
								SD-87568-003		PSD	001	3 OF 3	