




1	0.76µm [.000030] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH 1.27µm[.000050] MIN MATTE TIN PLATE IN WIRE CRIMP AREA, BOTH OVER 0.76µm [.000030] MIN NICKEL PER QQ-N-290.
2	1.27µm [.000050] MIN TIN-LEAD PER MIL-T-10727 OVER 0.76µm [.000030] MIN NICKEL PER QQ-N-290.
3	0.76µm [.000030] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH A UNIFORM GRADIENT TO 0.25µm [.000010] MIN GOLD PER MIL-G-45204 ON THE REMAINDER OVER 0.76µm [.000030] NICKEL PER QQ-N-290.
4	0.38µm [.000015] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH 1.27µm[.000050] MIN MATTE TIN PLATE IN WIRE CRIMP AREA, BOTH OVER 0.76µm [.000030] MIN NICKEL PER QQ-N-290.
5	1.27µm [.000050] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH GOLD FLASH ON REMAINDER OVER 1.90µm [.000075] MIN NICKEL PER QQ-N-290.
6	GOLD PLATING NOT REQUIRED IN THIS AREA
7	WIRE RANGE 24-20 AWG. INSULATION RANGE 1.02[.040]-2.03[.080].
8	0.38µm [.000015] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN, 1.27µm [.000050] MIN TIN-LEAD PER MIL-T-10727 FOR A LENGTH OF 5.69 [.224] MIN ON OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL PER QQ-N-290 ON ENTIRE CONTACT.
9	1.27µm [.000050] MIN TIN PER MIL-T-10727 OVER 0.76µm [.000030] MIN NICKEL PER QQ-N-290.
10	OBsolete PARTS: OBsolete CIS STREAMLINING PER D.RENAUD/D.SINISI

10	OBSOLETE	SMALL PACK	9	BRASS	2-66104-9 OR 3-66104-0	2-66105-0
		STANDARD	9	BRASS	2-66104-9 OR 3-66104-0	1-66105-9
		SMALL PACK	1	BRASS	66104-4	1-66105-8
		SMALL PACK	4	BRASS	66104-3	1-66105-7
		SMALL PACK	2	BRASS	66104-2	1-66105-6
	OBSOLETE	SMALL PACK	3	BRASS	66104-1	1-66105-5
		STANDARD	8	BRASS	2-66104-6	1-66105-4
		STANDARD	1	PHOSPHOR BRONZE	2-66104-3	1-66105-3
		STANDARD	2	PHOSPHOR BRONZE	2-66104-2	1-66105-2
		STANDARD	5	BRASS	1-66104-6	1-66105-0
	STANDARD	1	BRASS	66104-4	66105-4	
	STANDARD	4	BRASS	66104-3	66105-3	
	STANDARD	2	BRASS	66104-2	66105-2	
	STANDARD	3	BRASS	66104-1	66105-1	
	PACKAGING TYPE	BODY FINISH	MATERIAL	STRIP P/N REF	PART NO	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.SIPE 06/01/92	TE Connectivity						
DIMENSIONS: mm [INCHES]		CHK W.LENKER 6-11-92							
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD G.STEINHAUER 7-8-92		NAME			
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC					
MATERIAL SEE CALLOUTS		FINISH SEE CALLOUTS		APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
				—		A2	00779	C-66105	—
				CUSTOMER DRAWING		SCALE 8:1	SHEET 1 of 1	REV J1	