

TOSHIBA Bipolar Linear Integrated Circuit Silicon Monolithic

TA8083AF


Dual DC Motor Driver

The TA8083AF contains two motor driver circuits with a current capacity of 0.5 A for directly driving bidirectional DC motors. Inputs DI1 A/B and DI2 A/B are combined to select one of forward, reverse, stop, and brake modes. Since the inputs are TTL-compatible, this IC can be controlled directly from a CPU or other control system.

In addition, the IC has a low standby current function, a self-diagnostic function, and various detection functions.


Features

- 0.5 A bidirectional DC motor driver
- Incorporating two circuits (power supply, self-diagnostic, and detection functions provided for each channel)
- Low standby current: 0.1 mA (max)
- Self-diagnostic output: short-circuit mode (1.1 A typ.)
- Operating supply voltage range: VCC = 8 V to 16 V
- Detection functions: overheating, overcurrent, and overvoltage
- Built-in counter-electromotive-force absorption diodes
- HSOP 20-pin power flat package



Weight: 0.79 g (typ.)

Block Diagram and Pin Assignment



Note: Some functional blocks, circuits, or constants are omitted or simplified in the block diagram to clarify the descriptions of the relevant features.

Pin Description

Pin No.		Symbol		Description
CH1	CH2	CH1	CH2	
1 3	20 18	DI1A DI1B	DI2A DI2B	Input pin. The signal from this pin controls the output state. (See Truth Table 1.)
4	17	L·G1	L·G2	Ground terminal for Logic portion.
5	16	DG1	DG2	Self-diagnosis output pin. (See Table 2, Truth Table & Timing Chart.) NPN transistor open-collector output. When output becomes overcurrent, set to on; duty 97% on (low). At normal operation or at the time of STOP, set to open (high).
6	15	M (+) 1	M (+) 2	Connects to the DC motor. Both the sink and the source have a current capacity of 0.5 A. Features overcurrent detection function to temporarily protect the IC from destruction at load short, ground fault, or direct connection to high power. (See section on Multiple Detections below.) Features diodes for absorbing counter-electromotive force, which are built into both V_{CC} and Gnd sides.
7	14	P·G1	P·G2	Ground terminal for output portion.
9	12	M (-) 1	M (-) 2	A motor is connected between this pin and the M (+) pin. This pin has a function equivalent to that of the M (+) pin, and is controlled by input to the DIA and DIB pins.
10	11	V_{CC1}	V_{CC2}	Power supply pin. This pin has a function to turn off the output when the applied voltage exceeds 30 V.
2, 8, 13, 19		NC		Not connected pin. (Electrically, this pin is completely open.)

Truth Table 1: Input/Output


Input		Output		Operation Mode
DI1/2A	DI1/2B	M (+) 1/2	M (-) 1/2	
H	H	L	L	Brake
L	H	L	H	Reverse (CCW)
H	L	H	L	Forward (CW)
L	L	OFF (high impedance)		Stop (standby)

Truth Table 2: Self-Diagnosis

Input		Output		DIAG
DI1/2A	DI1/2B	Mode	Load	
H	H	Brake	Normal	H
			Short	L*
L/H	H/L	CCW/CW	Normal	H
			Short	L*
L	L	Stop	—	H

*: See Timing Chart

Self-Diagnosis Timing Chart




Note: Timing charts may be simplified to clarify the descriptions of features and operations.

Description of Multidetection Operation

The TA8083AF has functions for detecting, overvoltage (VSD), overcurrent (ISD), and overheating (TSD).

These functions temporarily protect the IC (and, in some cases, the motor load) from deterioration or destruction due to power-related overstress.

The three functions work independently, and each function is explained below.



Note 1: These functions are intended to protect the IC from instantaneous faults, including output short circuits, and are not designed to protect the IC from all types of fault.

Note 2: If the IC is used beyond the maximum ratings, it may be damaged before the detection circuits are activated.

Note 3: These functions are not activated if the operating voltage is less than 8 V. In this range, short-circuiting the output can cause damage to the IC.

1. Overvoltage detection (VSD)

- **Basic operation**

When the voltage supplied to the VCC pin is up to the VSD detection voltage, the output is controlled by the input signals. However, when the VCC voltage exceeds the detection voltage, the output enters high-impedance state regardless of the input signals.

- **Detailed explanation**

The VSD voltage is detected by an internal zener diode. If the input voltage is higher than the zener voltage, a signal to turn off the output transistors is sent to the control logic. If it is lower than the zener voltage, the logic is controlled by the input signals from DIA and DIB.

2. Overheat detection (TSD)

- **Basic operation**

When the junction (chip) temperature is up to the TSD detection temperature, the output is controlled by the input signals. When it exceeds the TSD detection temperature, the output enters high-impedance state regardless of the input signals.

- **Detailed explanation**

The temperature is detected by monitoring the VF of a diode on the chip. When the diode VF is lower than the internal reference voltage, an output transistor-off instruction is issued to the control logic. When it is higher than the internal reference voltage, the logic is controlled by the input signals from DIA and DIB.

3. Overcurrent detection (ISD)

- **Basic operation**

When the output current (M (+) or M (-), I_{sink} or I_{source}) is up to the ISD detection current, the output is controlled by the input signals. When it exceeds the detection current, the output assumes a switching waveform, as shown in Figure 1.




Figure 1: Basic Operation

- **Detailed explanation**

The output current is detected by monitoring the sense resistance. One detection circuit connects to one of the circuits (CH1 or CH2) and leads to the short-circuit protection circuit. When a current exceeding the ISD detection current flows through one of the four output transistors, the short-circuit detection circuit is activated. This circuit contains a timer. When an overcurrent condition continues for 10 μ s (typically), the detection circuit places the output in high-impedance mode and, 290 μ s (typically) later, returns the IC to ON mode. The switching-waveform output is repeated until the overcurrent condition is no longer present.

- **Caution for application**

The overcurrent detection is intended to protect the IC temporarily from overcurrent conditions due to short circuits. If an overcurrent condition continues after the output transistors move to switching mode, damage can occur due to overstress. To prevent this, a system must be configured so that the IC is switched into standby mode immediately after an overcurrent condition is detected by the DIAG output. In this case, the time that it takes to detect an overcurrent fault caused by short circuit to output (or to supply or ground) and to place the IC in the standby mode should be within one second.

Maximum Ratings (Ta = 25°C)

Characteristic	Symbol	Rating	Unit
Power supply voltage	V _{CC}	30	V
	V _{CC}	60 (1 s)	
Input voltage	V _{IN}	-0.3~V _{CC} + 0.3	V
Output current	I _O ·AVE	0.5	A
	I _O ·PEAK	0.8	
Power dissipation	P _D	2	W
Operating temperature	T _{opr}	-40~110	°C
Storage temperature	T _{stg}	-55~150	°C

Note 1: The absolute maximum ratings of a semiconductor device are a set of specified parameter values which must not be exceeded during operation, even for an instant.

If any of these levels is exceeded during operation, the device's electrical characteristics may be irreparably altered and the reliability and lifetime of the device can no longer be guaranteed, possibly causing damage to any other equipment with which it is used. Applications using the device should be designed such that the maximum ratings will never be exceeded in any operating conditions.

Ensuring that the parameter values remain within these specified ranges during device operation will help to ensure that the integrity of the device is not compromised.

Note2: P_D: on Board condition. (50 × 50 × 1.6 mm 50% Cu)

HSOP20-P-450-1.00 Thermal Resistance Data (Ta = 25°C)

Characteristic	Test Condition	Rating	Unit
R _θ j-a	—	125	°C/W
R _θ j-c	—	13	°C/W
PD1	Infinite radiation board	9.6	W
PD2	50 × 50 × 1.0 mm iron board mounted	3.2	W
PD3	50 × 50 × 1.6 mm 50% Cu mounted	2.0	W
PD4	No radiation board	1.0	W

Electrical Characteristics

(Unless otherwise specified, $V_{CC} = 8\text{~}16\text{ V}$, $T_C = -40\text{~}110^\circ\text{C}$.)

Characteristic	Symbol	Pin	Test Circuit	Test Condition	Min	Typ.	Max	Unit
Power supply current	I_{CC1}	V_{CC1}/V_{CC2}	—	CH1 + CH2: Stop	—	—	0.1	mA
	I_{CC2}		—	CH1 or CH 2: CW or CCW	—	23	34	
	I_{CC3}		—	CH1 + CH 2: CW or CCW	—	45	68	
	I_{CC4}		—	CH1 + CH 2: Brake	—	20	32	
Input voltage	V_{IL}	DI1A/B/ DI2A/B	—		—	—	0.8	V
	V_{IH}		—		2.0	—	—	
Input current	I_{IL}	DI1A/B/ DI2A/B	—	$V_{IN} = 0.4\text{ V}$	—	10	20	μA
	I_{IH}		—	$V_{IN} = 5\text{ V}$	—	300	600	
Output saturation voltage	$V_{sat\ (total)1}$	$M (+)/(-) 1/\text{ }M (+)/(-) 2$	—	$I_O = 0.4\text{ A}$, $T_C = 25^\circ\text{C}$	—	1.8	2.5	V
	$V_{sat\ (total)2}$		—	$I_O = 0.4\text{ A}$, $T_C = 110^\circ\text{C}$	—	1.7	2.4	
			—	$I_O = 0.7\text{ A}$, $T_C = 25^\circ\text{C}$	—	2.5	3.6	
			—	$I_O = 0.7\text{ A}$, $T_C = 110^\circ\text{C}$	—	2.5	3.6	
Output leakage current	I_{LEAK-U}	$M (+)/(-) 1/\text{ }M (+)/(-) 2$	—	$V_{OUT} = 0\text{ V}$	-10	—	—	μA
	I_{LEAK-L}		—	$V_{OUT} = V_{CC}$	—	—	10	
Diode forward voltage	V_F-U	$M (+)/(-) 1/\text{ }M (+)/(-) 2$	—	$I_F = 0.7\text{ A}$	—	2.0	—	V
	V_F-L		—		—	2.0	—	
Output voltage	V_{OL}	DIAG 1/2	—	$I_{OL} = 3\text{ mA}$	—	—	0.5	V
Output leakage current	I_{LEAK}	DIAG 1/2	—	$V_{OUT} = V_{CC}$	—	—	10	μA
Overcurrent detection	I_{SD}		—		0.8	1.1	1.5	A
Overheat detection	T_{SD}		—		—	150	—	$^\circ\text{C}$
Overvoltage detection	V_{SD}		—		—	30	—	V
Transfer delay time	t_{pLH}		—	—	—	1	10	μs
	t_{pHL}		—		—	1	10	

Note: The parameter values above are guaranteed in the operating voltage range of 8 V to 16 V. If the guaranteed range is exceeded, the performance of the IC must be tested thoroughly in its application. It is the customer's responsibility to evaluate the use of the IC.


Notes on Use

This IC is an electrostatic-sensitive device. Handle with care.

Reference data for electrostatic discharge (ESD) resistance



- MM (EJAJ: $R = 0\ \Omega/C = 200\text{ pF}$): $\pm 200\text{ V}$ (max)
- HBM (MIL: $R = 1.5\text{ k}\Omega/C = 200\text{ pF}$): $\pm 1\text{ kV}$ (max)

I/O Equivalent Circuit




Note: The equivalent circuit diagrams may be simplified or some parts of them may be omitted for explanatory purposes.

Reference Characteristics



Application Circuit




Caution for Wiring

- Note 1: The capacitor C1 is for absorbing noise, etc.
- Note 2: Connect each capacitor as close to the IC as possible.
- Note 3: Ensure that the IC is mounted correctly. Failing to do so may result in the IC or target equipment being damaged.
- Note 4: The application circuit shown above is not intended to guarantee mass production. A thorough evaluation is required when designing an application circuit for mass production.

Package Dimensions

HSOP20-P-450-1.00

Unit : mm



Weight: 0.79 g (typ.)

RESTRICTIONS ON PRODUCT USE

030619EBA

- The information contained herein is subject to change without notice.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA for any infringements of patents or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of TOSHIBA or others.
- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property.
In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- The products described in this document are subject to the foreign exchange and foreign trade laws.
- TOSHIBA products should not be embedded to the downstream products which are prohibited to be produced and sold, under any law and regulations.