

THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS					
HB		—		P	LTR	DESCRIPTION	DATE	DWN	APVD
					E	REMOVED THE RIB ON THE BASE TO CASE ECO-15-011310	04-Dec-15	YS.HHL	C
					E1	NEW ADD PN ECO-17-004477	22-Jan-18	WQ.Y	K.T





Diagram dimension	Tolerance
0.99mm max.	±0.1mm
1 - 2.99mm	±0.2mm
3mm min.	±0.3mm




FIGURE FOR PRINTED CIRCUIT BOARD PROCESSING
(BOTTOM VIEW)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -

MATERIAL	FINISH
-	-

DWN	Hu.XieLi
CHK	Mak.Simon
APVD	Mingjung.Ho
PRODUCT SPEC	-
APPLICATION SPEC	-
WEIGHT	-
CUSTOMER DRAWING	-

TE Connectivity	
OJE CUSTOMER DRAWING(OJE-SS-LMH2)	
SIZE	A3
CAGE CODE	00779
DRAWING NO	1721261
RESTRICTED TO	-
SCALE	5:1
SHEET	1 of 2
REV	E1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APV
HB	—		—	SEE SHEET 1	—	—	

1721261-7	OJE-SS-112LMH2	12V	OJE-SS-112LMH2	g
1721261-6	OJE-SS-124LMH2	24V	OJE-SS-124LMH2	f
1721261-5	OJE-SS-112LMH2	12V	OJE-SS-112LMH2	e
1721261-4	OJE-SS-109LMH2	9V	OJE-SS-109LMH2	d
1721261-3	OJE-SS-106LMH2	6V	OJE-SS-106LMH2	c
1721261-2	OJE-SS-105LMH2	5V	OJE-SS-105LMH2	b
1721261-1	OJE-SS-103LMH2	3V	OJE-SS-103LMH2	a
TE PART NO	PART A	PART B	DESCRIPTION	TYPE

RELAY TYPE

11A

4. MARKING FROM INK TO LASER AND USING WELDED CONTACT

		EPOXY RESIN	SEAL (BASE & BOBBIN)	15
		JUW	MAGNETIC WIRE	14
UL94V-0		P.B.T	CASE	13
UL94V-0		P.B.T	BASE	12
UL94V-0		P.B.T	BOBBIN	11
	SOLDER DIP	C.P WIRE	COIL TERMINAL	10
UL94V-0		P.P.S	CARD	9
		AgSn0In0	MOVABLE CONTACT	8
		AgSn0In0	NO.CONTACT	7
		STEEL	HINGE SPRING	6
	SOLDER DIP	Cu ALLOY	NO.TERMINAL	5
	SOLDER DIP	Cu ALLOY	MOVABLE SPRING	4
	NIP	STEEL	CORE	3
	NIP	STEEL	ARMATURE	2
	NIP	STEEL	YOKE	1
INCOMPATIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN	Hu.XieLi		 TE Connectivity	INCOMPLIABILITY		TREATMENT	INTERNAL	DESCRIPTION	FILE	
DIMENSIONS: mm		CHK	Mok.Simon			NAME	OJE CUSTOMER DRAWING(OJE-SS-LMH2)					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	Mingjung.Ho									
		PRODUCT SPEC	—									
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		APPLICATION SPEC	—		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
MATERIAL		FINISH	WEIGHT	—		A300779		C= 1721261		—		
—		—	CUSTOMER DRAWING			SCALE 5:1		SHEET 2 OF 2		REV F		