


Reed Switch - Sub-Miniature - Normally Open Contacts
Part Number : GC2322
Product Data Sheet

PICTURE	DIMENSIONS
---------	------------


File Number E103299
RoHS Compliant

Drawings not to scale

All dimensions in mm (inches) nominal.

SPECIFICATION		
Contact Form		Normally Open
Contact Material		Rhodium
Switching Capacity	Max.	10 VA
Switching Voltage	Max.	150 VAC/DC
Switching Current	Max.	0.5 A
Carrying Current	Max.	1.0 A
Dielectric Strength	Min.	200 VDC
Contact Resistance	Max.	150 mOhms
Insulation Resistance	Min.	10 ¹⁰
Pull - In - Sensitivity		10 - 35 AT
Drop - Out - Sensitivity	Min.	5
Bounce Time	Max.	0.2 ms
Release Time	Max.	0.05 ms
Resonant Frequency	Typ.	5000 Hz
Operating Frequency	Max.	200 Hz
Vibration (10-1000Hz)		35 g
Shock (11 ms)		50
Capacitance	Typ.	0.7 pF
Operating Temperature Range		-40°C + 125°C
Test Coil	Type	1035

NOTE	Ordering Information
------	----------------------

- When cutting or bending switch leads it is important that the glass seal is not damaged. The cutting or bending point should be no closer than 3mm (.118in.) to the glass to metal seal and the lead should be supported between the cutting or bending point and the glass to metal seal.
- We offer a crop and form service for Reed Switches to be customized to your specification.

PART NUMBER 2322 10 35

- Type _____
- Minimum (AT) Sensitivity _____
- Maximum (AT) Sensitivity _____

Did you know we also sell?

Example:

 Type 2322 Standard Sensitivity. Pull-in sensitivity between 10-35 AT is PART NO: 2322 10 35
 Available in ranges of 5 AT e.g: 10-15, 15-20 etc.

Rev. No.	Revision Note	Date	Signature
2	Datasheet Redesign	26-05-06	NG



As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and the details of our full design and manufacturing service. All products are supplied to our standard conditions of sale unless otherwise agreed in writing.

Phone : (1) 973 777 6900
www.comus-intl.com
Fax: (1) 973 777 8405

©2006 Copyright Comus International Ltd, 454 Allwood Road, Clifton, New Jersey, 07012, USA.