



OUTLINE DRAWING

Dimensions in mm



H3

BLOCK DIAGRAM



PIN:

- ①Pin : RF INPUT
- ②Vcc1: 1st. DC SUPPLY
- ③Vcc2: 2nd. DC SUPPLY
- ④Vcc3: 3rd. DC SUPPLY
- ⑤Po : RF OUTPUT
- ⑥GND: FIN

ABSOLUTE MAXIMUM RATINGS (Tc=25°C unless otherwise noted)

Symbol	Parameter	Conditions	Ratings	Unit
Vcc	Supply voltage	ZG=ZL=50Ω	17	V
Icc	Total current	ZG=ZL=50Ω	15	A
P _{in} (max)	Input power	ZG=ZL=50Ω, Vcc1≤12.5V	600	mW
P _O (max)	Output power	ZG=ZL=50Ω, Vcc1≤12.5V	60	W
T _C (OP)	Operation case temperature	ZG=ZL=50Ω, Vcc1≤12.5V	-30 to +110	°C
T _{stg}	Storage temperature		-40 to +110	°C

Note. Above parameters are guaranteed independently.

ELECTRICAL CHARACTERISTICS (Tc=25°C unless otherwise noted)

Symbol	Parameter	Test conditions	Limits		Unit
			Min	Max	
f	Frequency range		400	450	MHz
P _O	Output power	Vcc=12.5V, P _{in} =300mW, ZG=ZL=50Ω	45		W
η _T	Total efficiency		35		%
2fo	2nd. harmonic			-30	dBc
3fo	3rd. harmonic			-30	dBc
p _{in}	Input VSWR			2.8	-
-	Load VSWR tolerance	Vcc=15.2V, P _O =45W(P _{in} :controlled) ZG=50Ω, Load VSWR=8:1 (All phase)	No degradation or destroy		-

Note. Above parameters, ratings, limits and test conditions are subject to change.