

1

2 3

4

5

6

PRODUCT NO.

52527-XXXX29

52527-XXXX24

SEE NOTE 4

NOTE:

1. THESE DIMENSIONS DEFINE THE CONNECTOR KEEP-OUT AREA.
2. THESE HOLES ARE USED BY CONNECTOR HOOK.
3. SUGGESTED TORQUE IS 3.0 IN-LBS min.
4. P/N CODE:

52527-X X X X 29 LF

NO THIS SUFFIX : Sn/Pb ON PCB INTERFACE
ADD THIS SUFFIX : PURE Sn ON PCB INTERFACE

PIN NUMBER

GUIDE POST

0 - WITHOUT POST

COLOR OF HOUSING AND TAIL-GUIDE

0- BLACK Obsolete

1- NATURAL

MOUNTING SCREW

0 - WITHOUT MOUNTING SCREW

1 - WITH MOUNTING SCREW (UNASSEMBLED) Obsolete

CONTACT PLATING

0 - GOLD FLASH

1 - 15 u" Au Obsolete

2 - 30 u" Au Obsolete

52527-X X X X 24 LF

NO THIS SUFFIX : Sn/Pb ON PCB INTERFACE
ADD THIS SUFFIX : PURE Sn ON PCB INTERFACE

PIN NUMBER

GUIDE POST

0 - WITHOUT POST

COLOR OF HOUSING AND TAIL-GUIDE

0- BLACK Obsolete

1- NATURAL

MOUNTING SCREW

0 - WITHOUT MOUNTING SCREW

1 - WITH MOUNTING SCREW (UNASSEMBLED) Obsolete

CONTACT PLATING

0 - GOLD FLASH

1 - 15 u" Au Obsolete

2 - 30 u" Au Obsolete

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY	 FCI FRAMATOME GROUP	
ltr	ecn no	dr	date	linear	0.0±	projection
E					0.00±	title
				angles	0°±	RECEPTACLE OF DVI VERTICAL TYPE
		dr	Benny Chen 01/13/00	MM/INCH	product family DVI	code
		enr	Benny Chen 01/13/00	scale	size dwg no	sheet
		chr	Paul Wang 01/13/00		A3	3 of 3
		appd	Paul Wang 01/13/00		52527	
sheet index	revision sheet					