






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
39±.010 .53±0.251			C	REVISED REDRAWN PER E.O. PI9388	13OCT2006	AM	RDR
			C1	REVISED PER ECO-14-015729	16OCT2014	JA	DM
			C2	REVISED PER ECO-14-018705	15DEC2014	JA	DM
			D	REVISED PER ECO-15-011302	11DEC2015	JA	DM



3 CONTACT PLATING: MATING SIDE AND PCB SIDE: TIN (ROHS COMPLIANT) OVER NICKEL.

2 HOUSING MATERIAL: PPS 40% GF (BLACK)

1. THIS RECEPTACLE MATES WITH HD16-9-96SX-XXXX (XXXX = ALL MODIFICATIONS)
CONSULT FACTORY FOR MODIFICATIONS

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES[mm]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±.005 [0.13]
4 PLC	±
ANGLES	±
FINISH	±

DWN	02JUN1986
CHK	T. SCARPETTA
APVD	JEFF ALBERS
PRODUCT SPEC	N/A
APPLICATION SPEC	N/A
WEIGHT	41.12g
Customer Drawing	

		TE Connectivity	
NAME RECEPTACLE, HEADER, FLANGE SHELL SIZE 9, 9 PIN, #16 SIZE HD10 SERIES			
SIZE A3	CAGE CODE 4AFU8	DRAWING NO G-HD10-9-96P-N005	RESTRICTED TO GEN
SCALE 2:1		SHEET 1 OF 1	REV D