


REV	DOCUMENT	CHANGED BY	CHECK
9	0038225	PRS 04APR08	BLR



RELEASE NO.	PR - 405
REPLACES	-

CHARACTERISTICS		ELECTRICAL DATA				DESIGN UNITS: INCH				DRAWN	VK	23 OCT 07		Honeywell					
OPERATING FORCE – – – – 7 OZ MAX		CONTACT ARRANGEMENT SPDT				TOLERANCES UNLESS NOTED:				CHECK	RJ	23 OCT 07							
RELEASE FORCE – – – – 2 OZ MIN		30 VOLTS DC RATING				NO PLACE X ± -				THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.				TITLE SWITCH - BASIC					
DIFFERENTIAL TRAVEL – – – .030 MAX						ONE PLACE .X ± 0.030													
OVERTRAVEL – – – – – .030 MIN		SEA LEVEL 50,000 FT				TWO PLACE .XX ± 0.015													
		INDUCTIVE 3 AMP 2.5 AMP				THREE PLACE .XXX ± 0.005													
		RESISTIVE 5 AMP 5 AMP				FOUR PLACE .XXXX ± -				INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY				SIZE	TYPE	DRAWING NAME		REV	
		MAXIMUM INRUSH 24 AMP				ANGLES ± -								B	I	111SM1-H58		9	
		APPROVALS	KEMA, CE	5A, 250V ~ T85 1E4		CE	THIRD ANGLE PROJECTION 				RASTER				SCALE	-	WEIGHT .006 LB MAX	SHEET	1 OF 1
			UL, CSA	5A, 250 VAC ~		SF					BRAND L4								