



NOTES

1. THIS PRODUCT IS CSA APPROVED.
2. THIS PRODUCT IS UL RECOGNIZED.
3. MATERIAL: POLYESTER 30% GLASS FILLED REINFORCED.
4. THIS PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
5. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 30 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6MM MINIMUM THICK CIRCUIT BOARD

rev	ecn no	dr	date	Spec ref	tolerance	projection	size	Scale
A	CONVERSION 05	KN	14-09-01	✓	1DEC+0.1 DEC 2DEC ± 0.10 2DEC ANGLES+1°HOEKEN			
B	DG05-0333	Kasor	16-09-05	Product family	MILLIPICS		ECN	
C	DG07-0011	Kasor	11-01-07	Plating/Finish		Model Name		
				Appr		Model Revision	REL Level	
				FCI	title	MILLIPAC 2/FEMALE BODY/TYPE L	dwg no	BSC201418004
					Pro/E file	catalog no	Rev.	C
						HM2R04P1LF	CUSTOMER	sheet 1 of 1