

"Contempra 2" Rack Frame Fan Tops

[4" Fan Top Panel](#) | [4" Wired Fan Top](#) | [10" Fan Top](#)



Top View



Bottom View

10" Fan Top



Top View




Bottom View




- **Use only with *Contempra 2* rack frames**
- Includes quantity 1 - 10", 550 CFM, 115 V 50/60 Hz. AC fan
- 35 watt motor
- Thermal protected motor
- Ball bearing construction, plastic blades (3)
- Diecast aluminum body fan
- Rotation is clockwise (looking down at the rotor - as pictured on the "Top View" - left)
- Airflow exhausts the rack (out the top as pictured on the left)
- C UL & UL recognized
- 5' cord and molded on plug
- Top & bottom finger guards included
- Pre-wired and assembled as shown above

As Pictured Above

| Part Number | Color | Paint Texture | Use With Rack Frame Depth | | Drawing File Size | | .zip File Size |
|--|---------------------|----------------------|---------------------------------|--|----------------------|--|----------------|
| C2T1923F10BK1 C2T1923F10CG1 | Black Gray/Beige | Textured Textured | 23.63" | | 214K | | 216K |
| C2T1931F10BK1 C2T1931F10CG1 | Black Gray/Beige | Textured Textured | 31.5" | | 213K | | 209K |
| C2T1936F10BK1 C2T1936F10CG1 | Black Gray/Beige | Textured Textured | 36" | | 212K | | 209K |




PART No. C2T1931F10



Fan Tops (C2 Series)


4.7" FAN TOP PANEL



- 14 gauge steel construction, finished in a rugged powder paint
- 4.7" fan top panel - fans not included (see next page)
- Quantity 4 or 6 openings depending on depth of rack
- Maximum flexibility - add fans, leave holes open (for cable access) or use covers (see next page)

| Part Number | | Panel Width | Rack Depth | Fan Holes |
|-----------------------------|-----------------------------|-------------|------------|-----------|
| Black Textured | Beige Textured | | | |
| C2T1923FBK1 | C2T1923FCG1 | 19 | 23.63 | 4 |
| C2T1931FBK1 | C2T1931FCG1 | 19 | 31.50 | 6 |
| C2T1936FBK1 | C2T1936FCG1 | 19 | 36.00 | 6 |

PRE-WIRED 4.7" EXHAUST FAN TOP



- Includes a quantity of 4 - long life, ball bearing, 4.7", 115 volt, 50/60 Hz. AC, 100 CFM fans (230 VAC fan tops available on special order)
- Available with or without thermostat
- Finger guards are punched into top panel and bottom of fan top
- Fans are pre-wired, installed and complete with 3 foot cord & plug

| Part Number | | Panel Width | Rack Depth | Thermostat |
|-------------------------------|-------------------------------|-------------|------------|------------|
| Black Textured | Beige Textured | | | |
| C2T1923F4BK1 | C2T1923F4CG1 | 19 | 23.63 | No |
| C2T1931F4BK1 | C2T1931F4CG1 | 19 | 31.50 | No |
| C2T1936F4BK1 | C2T1936F4CG1 | 19 | 36.00 | No |
| C2T1923F4TBK1 | C2T1923F4TCG1 | 19 | 23.63 | Yes |
| C2T1931F4TBK1 | C2T1931F4TCG1 | 19 | 31.50 | Yes |
| C2T1936F4TBK1 | C2T1936F4TCG1 | 19 | 36.00 | Yes |

PRE-WIRED 10" EXHAUST FAN TOP PANEL



Without Cable Access


- Includes quantity 1 - 10", 550 CFM, 115 V 50/60 Hz. AC fan 35 watt motor (230 VAC fan tops available on special order)
- Thermal protected motor
- Ball bearing construction, plastic blades (3)
- Diecast aluminum body fan
- Rotation is clockwise (looking down at the rotor - as pictured on the left)
- Airflow exhausts the rack (out the top as pictured on the left)
- C UL & UL recognized
- 5' cord and molded on plug
- Top & bottom finger guards included
- Pre-wired and assembled as shown, finished in a rugged powder paint
- Available either with or without 4 cable access holes (3.5") and covers

Without Cable Access Holes

| Part Number | | Panel Width | Rack Depth |
|-------------------------------|-------------------------------|-------------|------------|
| Black Textured | Beige Textured | | |
| C2T1923F10BK1 | C2T1923F10CG1 | 19 | 23.63 |
| C2T1931F10BK1 | C2T1931F10CG1 | 19 | 31.50 |
| C2T1936F10BK1 | C2T1936F10CG1 | 19 | 36.00 |

With Cable Access 3.5" Holes & Covers

| Part Number | | Panel Width | Rack Depth |
|---------------------------------|---------------------------------|-------------|------------|
| Black Textured | Beige Textured | | |
| C2T1923F10CEBK1 | C2T1923F10CECG1 | 19 | 23.63 |
| C2T1931F10CEBK1 | C2T1931F10CECG1 | 19 | 31.50 |
| C2T1936F10CEBK1 | C2T1936F10CECG1 | 19 | 36.00 |



With Cable Access

19" Rack Mount

Welded