






FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE NOTE 1



mat'l. code NOTE 3				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC			
ltr	ecn no	dr	date	tolerances unless otherwise specified				title			
A	v10434	RDS	6/05/91	angles	linear	.XX ±.01/.3		3 ROW R/A HEADER			
B	v12571	SAR	10/09/91			.XXX ±.005/.13		SOLDER TO BOARD, 2 G. P.			
C	v23813	MRC	1/06/93	σ±2°		.XXXX ±.0020/.051	scale 1:1	dwg no			
D	v40227	PDP	1/11/94	dr	D. SHEAFFER	6/05/91		sheet 1 of 2 size			
E	v90522	HTB	2/26/99	enr	S. CLARK	6/05/91		50121 A3			
F	v00262	JWS	1/26/00	chr	S. CLARK	6/05/91		type			
G	M06-0255	AEA	7/06/06	appd	S. CLARK	6/05/91		Product Customer Drawing			
sheet index	revision	G	G								
	sheet	1	2								


form: A3

PDM: Rev:G

STATUS: Released

Printed: May 13, 2011

SECTION U-U



Technical drawing of a mechanical part with dimensions and tolerances:

- Top dimensions: $.275^{+.000}_{-.005}$ [6.98 $^{+.00}_{-.12}$], $.22$ [5.5]
- Right side dimension: $.0580$ [1.473] C.L. OF FIRST ROW
- Bottom right dimension: $.025$ [.63] TYP.
- Bottom right feature: $\oplus .024/-.60$ (M) A (S) C
- Bottom dimensions: $.220$ [5.58] REF., $.555$ [14.10]

NOTES:

- PRODUCT NUMBERING CODE FOR
SELECT LOAD PART NUMBERS:
50121 - XXXXX

- ②. THIS PRODUCT IS CONFIGURED IN SIZES OF 30 THRU 150 COLUMNS IN INCREMENTS OF THREE.
i.e.: 30,33,36,39.....147,150.

- ③ HOUSING MATERIAL: GLASS AND MINERAL FILLED
HIGH TEMP. THERMOPLASTIC. FLAME RETARDANT
PER UL94V-0. COLOR: BLACK.
PIN MATERIAL: PHOS. BRONZE

- ④. PLATING OPTIONS:
1 = 30u"/.76u GOLD
3 = 50u"/1.27u GOLD
5 = 30u"/.76u GXT

- ⑤. TAIL LENGTH OPTIONS:
H = .180/4.57
J = .120/3.05

- ⑥. MANUFACTURE'S NAME, P/N, AND LOT CODE TO APPEAR ON THIS SURFACE PER BUS-12-108.

7. FOR DOCUMENTATION MENU, SEE SPEC. BUS-01-057.

form: A3